

## SCHOTTKY DIODES

### FEATURES

Plastic package has Underwriters Laboratory

Flammability Classification 94V-0

For surface mounted applications


Metal silicon junction, majority carrier conduction

Built-in strain relief, ideal for automated placement

Low power loss, high efficiency.

High forward surge current capability

### SS12---SS1200



Dimensions in inches and (millimeters)

DO-214AC (SMA)

### MECHANICAL DATA

SMA (DO-214AC) molded plastic body

leads solderable per MIL-STD-750, Method 2026

color band denotes cathode end

### MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%.

MDD Catalog Number	SYMBOLS	SS12	SS13	SS14	SS15	SS16	SS18	SS110	SS1150	SS1200	UNITS
Maximum repetitive peak reverse voltage	V <sub>RRM</sub>	20	30	40	50	60	80	100	150	200	VOLTS
Maximum RMS voltage	V <sub>RMS</sub>	14	21	28	35	42	56	70	105	140	VOLTS
Maximum DC blocking voltage	V <sub>DC</sub>	20	30	40	50	60	80	100	150	200	VOLTS
Maximum average forward rectified current at TL(see fig.1)	I <sub>(AV)</sub>	1.0								Amp	
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I <sub>FSM</sub>	30.0								Amps	
Maximum instantaneous forward voltage at 1.0A	V <sub>F</sub>	0.45	0.55	0.70	0.85	0.95					Volts
Maximum DC reverse current TA=25°C at rated DC blocking voltage TA=100°C	I <sub>R</sub>	0.5				0.2					mA
		10.0				5.0	2.0				
Typical junction capacitance (NOTE 1)	C <sub>J</sub>	110				90					pF
Typical thermal resistance (NOTE 2)	R <sub>θJA</sub>				88.0						°C/W
Operating junction temperature range	T <sub>J</sub>	-50 to +125				-50 to +150					°C
Storage temperature range	T <sub>STG</sub>	-50 to +150									°C

Note:1.Measured at 1MHz and applied reverse voltage of 4.0V D.C.

2.P.C.B. mounted with 0.2x0.2"(5.0x5.0mm) copper pad areas

## SS12---SS1200 Typical Characteristics

FIG.1-FORWARD CURRENT DERATING CURVE




Fig.2- MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




Fig.3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




Fig.4- TYPICAL REVERSE CHARACTERISTICS




Fig.5- TYPICAL JUNCTION CAPACITANCE




Fig.6- TYPICAL TRANSIENT THERMAL IMPEDANCE

