
FEATURES

- 3.3V, 5.0V, 12V and Adjustable Output Versions
- Adjustable Version Output Voltage Range
- Wide Input Voltage Range
- Guaranteed 1A Output Current
- 52kHz Fixed Frequency Internal Oscillator
- Voltage mode non-synchronous PWM control
- On/Off shutdown control input
- Thermal Shutdown and Current Limit Protection
- Moisture Sensitivity Level 3 for SMD packages

APPLICATION

- Simple High-Efficiency Step-Down(Buck) Regulator
- Efficient Pre-Regulator for Linear Regulators
- On-Card Switching Regulators
- Positive to Negative Converter(Buck-Boost)



ORDERING INFORMATION

Device	Package
LM2575GDP-X.X	SOP-8PP
LM2575GR-X.X	TO-263-5L
LM2575GT-X.X	TO-220-5L

X.X = Output Voltage = 3.3. 5.0, 12, ADJ

DESCRIPTION

The LM2575 series are monolithic ICs designed for a step-down DC/DC converter, capable of driving 1A load without an additional transistor. It saves a board space. The external shutdown function is controlled by a logic level and then the circuit comes into the standby mode. The internal compensation makes the feedback control with good line and load regulation characteristics without an external design. Regarding the protection functions – the thermal shutdown prevents circuit damage during the over temperature operation and the current limit is against overcurrent operation of the output switch. If the case for the current limiting occurs and VFB is down by 40% of the nominal output voltage, the switching frequency shall be reduced.

The fixed output voltage version includes 3.3V, 5V, 12V devices, while the adjustable version voltages range from 1.23V to 37V. The chips are available in a standard 5-lead TO-220, TO-263 and SOP-8PP package.

ABSOLUTE MAXIMUM RATINGS (Note 1)

Characteristic	Symbol	Value	Unit
Maximum Input Supply Voltage	V _{IN}	45	V
ON/OFF Pin Input Voltage	Von/off	-0.3 ≤ V ≤ 40, ≤ VIN	V
Feedback Pin Voltage	V_{FB}	-0.3 ≤ V ≤ 25, ≤ VIN	V
Output Voltage to Ground (Steady State)	V _{OUT}	-1	>
Storage Temperature Range	T _{STG}	-65 to +150	°C
Operating Temperature Range	TJ	150	°C


1A, 52KHz, Step-Down Switching Regulator

RECOMMENDED OPERATING CONDITIONS


CHARACTERISTIC	SYMBOL	MIN.	MAX.	UNIT
Supply Voltage	VIN	-	40	V
Load Current	Iload	-	1	Α
Junction Temperature	TJ	-40	125	${\mathbb C}$

Ordering Information

VOUT	Package	Order No.	Description	Status		
	SOP-8PP	LM2575GDP-ADJ	1A, Adjustable, 52kHz, On/off	Active		
ADJ	TO-263-5L	LM2575GR-ADJ	1A, Adjustable, 52kHz, On/off	Active		
TO-220-5L LM		LM2575GT-ADJ	1A, Adjustable, 52kHz, On/off	Active		
	SOP-8PP	LM2575GDP-3.3	1A, Fixed, 52kHz, On/off	Contact Us		
3.3V	TO-263-5L	LM2575GR-3.3	1A, Fixed, 52kHz, On/off	Contact Us		
TO	TO-220-5L	LM2575GT-3.3	1A, Fixed, 52kHz, On/off	Contact Us		
	SOP-8PP	LM2575GDP-5.0	1A, Fixed, 52kHz, On/off	Contact Us		
5.0V TO-263-5L		5.0V	TO-263-5L	LM2575GR-5.0	1A, Fixed, 52kHz, On/off	Active
	TO-220-5L	LM2575GT-5.0	1A, Fixed, 52kHz, On/off	Active		
SOP-8PP		LM2575GDP-12	1A, Fixed, 52kHz, On/off	Contact Us		
12V	TO-263-5L	LM2575GR-12	1A, Fixed, 52kHz, On/off	Contact Us		
	TO-220-5L	LM2575GT-12	1A, Fixed, 52kHz, On/off	Contact Us		



PIN CONFIGURATION




PIN DESCRIPTION

Package					
TO-263-5L	SOP-8PP	Symbol	Description		
TO-220-5L	30F-0FF				
1	1	VIN	This pin is the positive input supply for the LM2575 step-down switching regulator. In order to minimize voltage transients and to supply the switching currents needed by the regulator, a suitable input bypass capacitor must be present.		
2	2	VOUT	This is the emitter of the internal switch. The saturation voltage V _{SAT} of this output switch is typically 1.2V. It should be kept in mind that the PCB area connected to this pin should be kept to a minimum in order to minimize coupling to sensitive circuitry.		
3	5, 6, 7, 8	GND	Circuit ground pin. See the information about the printed circuit board layout.		
4	3	FEEDBACK	This pin senses regulated output voltage to complete the feedback loop. The signal is divided by the internal resistor divider network R1, R2 and applied to the non–inverting input of the internal error amplifier. In the adjustable version of the LM2575 switching regulator this pin is the direct input of the error amplifier and the resistor network R1, R2 is connected externally to allow programming of the output voltage.		
5	4	ON/OFF	It allows the switching regulator circuit to be shutdown using logic level signals, thus dropping the total input supply current to approximately 100uA.		


^{*} Exposed Pad of SOP-8PP package should be externally connected to GND.

TYPICAL APPLICATION

- Fixed Output Voltage Version



- Adjustable Output Voltage Version



1A, 52KHz, Step-Down Switching Regulator

ELECTRICAL CHARACTERISTICS

Specification with standard type face are for $T_J=25\,^{\circ}$ C, and those with **boldface type** apply over **full Operating Temperature Range**. Unless specified otherwise, $V_{IN}=12V$ for the 3.3V, 5V, and Adjustable versions and $V_{IN}=18V$ for the 12V version. $I_{LOAD}=0.2A$

Characteristic	Symbol	Test Condition		Min. (Note 3)	Typ. (Note 2)	Max. (Note 3)	Unit	
SYSTEM PARAMETERS (N	lote 4)			(Note 3)	(14016-2)	(Note 3)		
Efficiency		LM2575GX-ADJ	V _{IN} =15V, I _{LOAD} =1A		80		%	
		LM2575GX-3.3	V _{IN} =12V, I _{LOAD} =1A		75			
	η	LM2575GX-5.0	V _{IN} =12V, I _{LOAD} =1A		77			
		LM2575GX-12	V _{IN} =15V, I _{LOAD} =1A		85			
Output Voltage		LM2575GX-3.3	$5.1V \le V_{IN} \le 40V$ $0.2A \le I_{LOAD} \le 1A$	3.168 3.135	3.3	3.432 3.465		
	V _{OUT}	LM2575GX-5.0	$7V \le V_{IN} \le 40V$ $0.2A \le I_{LOAD} \le 1A$	4.800 4.750	5.0	5.200 5.250	V	
		LM2575GX-12	$15V \le V_{IN} \le 40V$ $0.2A \le I_{LOAD} \le 1A$	11.520	12	12.480 12.600	-	
Feedback Voltage	V _{FB}	LM2575GX-ADJ	$7V \le V_{\text{IN}} \le 40V$ $0.2A \le I_{\text{LOAD}} \le 1A$	1.193	1.23	1.267 1.280	V	
DEVICE PARAMETERS			O.E. (= ILOAD = 171	1.100	1	1.200	1	
Feedback Bias Current	I _{FB}	Adjustable Version		10	50	nA		
Ossillator Fraguency	E	(Note 5)			52	100 58	kHz	
Oscillator Frequency	Fosc	(Note 5)		42	52	63		
Saturation Voltage	V _{SAT}	I _{OUT} =1A, (Note 6, 7		1.2 1.3	1.4 1.5	V		
Max. Duty Cycle (ON)		(Note 7)		100				
Min. Duty Cycle (OFF)	DC	(Note 8)		0		%		
Current Limit	I _{CL}	Peak Current (Note		3.2		Α		
Output		V _{OUT} =0V (Note 6, 8)				-1	mA	
Leakage Current	IL.	V _{OUT} =-1V (Note 9)				-30	mA	
Quiescent Current	IQ	(Note 8)			5	8	mA	
					100	200		
Shutdown Current	Ishutdown Current Von/OFF=5V(OFF) (Note 9)				250	μА		
ON/OFF Control		•						
ON/OFF Pin Logic Input	V _{IH}	Low (Regulator ON	Low (Regulator ON)			0.6		
Threshold voltage	V _{IL}	High (Regulator Of	High (Regulator OFF)				V	
ON/OFF Pin Logic Input	I _H	V _{ON/OFF} =2.5V (regu		-0.1	5	uA		
current	IL	I _L V _{ONOFF} =0.5V (regulator ON)			0.01	-1		

1A, 52KHz, Step-Down Switching Regulator

LM2575

- **Note 1.** Absolute Maximum Rating indicate limits beyond which damage to the device may occur. Operating Ratings indicate condition for which the device is intended to be functional, but do not guarantee specific performance limits. For guaranteed specifications and test conditions, see the Electrical Characteristics.
- **Note 2:** Typical numbers are at 25° and represent the most likely norm.
- Note 3: All limits guaranteed at room temperature (standard type face) and at temperature extremes (bold type face).
- **Note 4:** External components such as the schottky diode, inductor, input and output capacitors, and voltage programming resistors can affect switching regulator system performance. When the LM2575 is used as shown in the typical circuit, system performance will be as shown in system parameters section of Electrical Characteristics.
- Note 5: The switching frequency is reduced when the second stage current limit is activated. The amount of reduction is determined by the severity of current over-load.
- Note 6: No diode, inductor or capacitor connected to output pin.
- Note 7: Feedback pin removed from output and connected to 0V to force the output transistor switch ON.
- **Note 8:** Feedback pin removed from output and connected to 12V for the 3.3V, 5V, and the ADJ version, and 15V for the 12V version, to force the output transistor switch OFF.

Note 9: VIN=40V.

TYPICAL OPERATING CHARACTERISTIC

T.B.D.




APPLICATION INFORMATION


- TYPICAL APPLICATION

As in any switching regulator, layout is very important. Rapidly switching currents associated with wiring inductance generate voltage transients which can cause problems. For minimal inductance and ground loops, the length of the wires should be kept as short as possible. Single-point grounding or ground plane construction should be used for best results. Keep the feedback wiring away from the inductor flux.

- Fixed Output Voltage Version



- Adjustable Output Voltage Version




[Figure 2]

*
$$V_{OUT} = V_{FB}(1 + \frac{R1}{R2})$$
, Where $V_{FB}=1.23V$, R2 Between 1K and 5K, CFF=1nF


- PCB Layout

Proper layout of the switching power supplies is very important, and sometimes critical for proper function: poor layout design can result in poor line or load regulation and stability issues. Place the high-current paths (GND, IN and SW) very close to the device with short, direct, and wide traces. Place the input capacitor as close as possible to the IN and GND pins. Place the external feedback resistors next to the FB pin. Keep the switching node SW short and away from the feedback network. The circuit of below PCB layout is shown in Figure.

- Top Layout



- Bottom Layout



REVISION NOTICE

The version of this document is including preliminary information. Thus the description in this datasheet can be revised without any notice to describe its electrical characteristics properly. Its version also can be changed to a production level. Please contact us to get the latest version of datasheet.