



#### SUPERFAST RECOVERY RECTIFIERS

VOLTAGE 50~400 Volt **CURRENT** 1 Ampere

#### **FEATURES**

- · Plastic package has Underwriters Laboratory Flammability Classification 94V-O Flame Retardant Epoxy Molding Compound
- Exceeds environmental standards of MIL-S-19500/228
- · Super fast recovery times, high voltage
- Ultra thin profile package for space constrained utilization
- · Package suitable for automated handling
- Lead free in compliance with EU RoHS 2011/65/EU directive
- Green molding compound as per IEC61249 Std. . (Halogen Free)

#### **MECHANICAL DATA**

Case: SMAF Molded Plastic

Terminals: Solderable per MIL-STD-750, Method 2026

Polarity: Color band denotes cathode end Standard packaging: 12mm tape (EIA-481)

Weight: 0.0011 ounces, 0.0328 grams

Marking: Part number



Cathode Anode

### MAXIMUM RATINGS(TA=25°C unless otherwise noted)

PARAMETER		SYMBOL	EST1AF	EST1BF	EST1CF	EST1DF	EST1EF	EST1GF	UNIT
Maximum recurrent peak reverse voltage		VRRM	50	100	150	200	300	400	V
Maximum rms voltage		VRMS	35	70	105	140	210	280	V
Maximum dc blocking voltage		Vr	50	100	150	200	300	400	V
Maximum average forward rectified current		l F(AV)	1						Α
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load		İFSM	30					Α	
Maximum forward voltage at 1A		VF	0.95 1.25					25	V
Maximum dc reverse current at rated dc blocking voltage		IR	1					μА	
Typical junction capacitance	(Note 1)	Сл		2	20		16		pF
Maximum reverse recovery time	(Note 2)	T <sub>RR</sub>	25						nS
Typical thermal resistance	(Note 3) (Note 4)	Røjl Røja	20 150					°C/W	
Operating junction temperature range		TJ	-55 to + 150					°C	
Storage temperature range		Тѕтс	-55 to + 150					°C	


Note:1.Measured at 1 MHz and Applied Reverse Voltage of 4 Volts.

- 2.Reverse Recovery Test Conditions: IF=0.5A, IR=1A, Recover to 0.25A.
- 3. Mounted on a FR4 PCB, single-sided copper, with 10cm\*10cm copper pad area.
- 4. Mounted on a FR4 PCB, single-sided copper, mini pad.


SMAF Unit: inch(mm) .65) 0.044(1.10) 0.035(0.90) 0.193(4.90) 0.177(4.50) 0.038(0.95)







**Fig.1 Forward Current Derating Curve** 



**Fig.2 Typical Junction Capacitance** 




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Reverse Characteristics




Fig.5 Typical Forward Characteristics





Fig.6 Typical Forward Characteristics





### **MOUNTING PAD LAYOUT**



### **ORDER INFORMATION**

· Packing information

T/R - 10K per 13" plastic Reel

T/R - 3K per 7" plastic Reel





## Part No\_packing code\_Version

EST1AF\_R1\_00001 EST1AF\_R2\_00001

## For example:



	Version Code XXXXX					
Packing type	1 <sup>st</sup> Code	Packing size code	2 <sup>nd</sup> Code	HF or RoHS	1 <sup>st</sup> Code	2 <sup>nd</sup> ~5 <sup>th</sup> Code
Tape and Ammunition Box (T/B)	Α	N/A	0	HF	0	serial number
Tape and Reel (T/R)	R	7"	1	RoHS	1	serial number
Bulk Packing (B/P)	В	13"	2			
Tube Packing (T/P)	Т	26mm	X			
Tape and Reel (Right Oriented) (TRR)	S	52mm	Y			
Tape and Reel (Left Oriented) (TRL)	L	PANASERT T/B CATHODE UP (PBCU)	U			
FORMING	F	PANASERT T/B CATHODE DOWN (PBCD)	D			





# **Disclaimer**

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties
  of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation.
   Customers are responsible in comprehending the suitable use in particular applications.
   Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.