

Inductors for decoupling circuits

Multilayer ferrite

MLZ series (for automotive)

MLZ1608 type

MLZ1608

1608 [0603 inch]*

* Dimensions Code JIS[EIA]

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

⚠ REMINDERS
 The storage period is less than 12 months. Be sure to follow the storage conditions (Temperature: 5 to 40°C, Humidity: 10 to 75% RH or less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
On not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C.
Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference.
Use a wrist band to discharge static electricity in your body through the grounding wire.
On not expose the products to magnets or magnetic fields.
On not use for a purpose outside of the contents regulated in the delivery specifications.
The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.
If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (electric trains, ships, etc.)

set forth in the each catalog, please contact us.

- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.



Inductors for decoupling circuits Multilayer ferrite

Product compatible with RoHS directive
Halogen-free
Compatible with lead-free solders
AEC-Q200

Overview of MLZ1608 type


FEATURES

- The MLZ Series include inductors for decoupling circuits that have top-class DC superimposition characteristics and low DC resistance.
- They are compatible with wide frequency band noise, from low to high frequency.
- W type products are the new standard type products that have both large current and low resistance.
- OL type products have a resistance up to 60% lower than W type products.

APPLICATION

Automotive equipment, smart phones, tablet terminals, note PCs, various modules such as camera modules, DSCs, video games, portable memory audio devices, navigation systems, PNDs, WLANs, SSDs

PART NUMBER CONSTRUCTION



■ OPERATING TEMPERATURE RANGE, PACKAGE QUANTITY, PRODUCT WEIGHT

	Temperat	ure range	Package quantity	Individual weight
Туре	Operating temperature*	Storage temperature**		
	(°C)	(°C)	(pieces/reel)	(mg)
MLZ1608	-55 to +125	-55 to +125	4000	4

^{*} Operating temperature range includes self-temperature rise.


^{**} The Storage temperature range is for after the circuit board is mounted.

RoHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html

O Halogen-free: Indicates that CI content is less than 900ppm, Br content is less than 900ppm, and that the total CI and Br content is less than 1500ppm.




■ RECOMMENDED REFLOW PROFILE



Preheating	g		Soldering		Peak	
Temp.		Time	Temp.	Time	Temp.	Time
T1	T2	t1	T3	t2	T4	t3
150°C	180°C	60 to 120s	230°C	30 to 60s	250 to 260°C	10s max.




SHAPE & DIMENSIONS





■ RECOMMENDED LAND PATTERN



Dimensions in mm



■ ELECTRICAL CHARACTERISTICS

□ CHARACTERISTICS SPECIFICATION TABLE

Туре	L		L measuring	conditions	DC resistance	Isat*1	Itemp*2	Part No.
			Frequency	Current				
	(µH)	Tolerance	(MHz)	(mA)	(Ω)±30%	(mA)	(mA)	
Liale	0.10	±20%	25	1.0	0.14	700	850	MLZ1608DR10DTD25
High	0.22	±20%	25	1.0	0.27	550	600	MLZ1608DR22DTD25
frequency	0.47	±20%	25	1.0	0.42	400	500	MLZ1608DR47DTD25
	1.00	±20%	10	1.0	0.15	190	600	MLZ1608A1R0WTD25
	2.20	±20%	10	1.0	0.25	130	500	MLZ1608A2R2WTD25
Large current	4.70	±20%	2	0.1	0.50	120	350	MLZ1608M4R7WTD25
Current	10.0	±20%	2	0.1	1.05	90	250	MLZ1608M100WTD25
	22.0	±20%	2	0.1	2.40	55	150	MLZ1608M220WTD25
Low resistance	1.00	±20%	2	0.1	0.11	140	700	MLZ1608N1R0LTD25
	2.20	±20%	2	0.1	0.18	110	500	MLZ1608N2R2LTD25
	4.70	±20%	2	0.1	0.32	80	400	MLZ1608N4R7LTD25
	10.0	±20%	2	0.1	0.60	60	300	MLZ1608N100LTD25

^{*1} Current assumed when inductance ratio has decreased by 50% max...

O Measurement equipment

Measurement item	Product No.	Manufacturer
L	4294A+16034G	Keysight Technologies
DC resistance	Type-7561	Yokogawa


^{*} Equivalent measurement equipment may be used.

^{*2} Current assumed when temperature has risen to 20°C max. (reference value). Operating temperature environment at this time: 105°C max.



■ ELECTRICAL CHARACTERISTICS

☐ L FREQUENCY CHARACTERISTICS GRAPH



 $\bigcirc \ \text{Measurement equipment}$


Product No.	Manufacturer
E4991A+16192A	Keysight Technologies

^{*} Equivalent measurement equipment may be used.



■ ELECTRICAL CHARACTERISTICS

☐ INDUCTANCE VS. DC BIAS CHARACTERISTICS GRAPH



 $\bigcirc \ {\bf Measurement\ equipment}$


Product No.	Manufacturer
4291B+16200A+16192A	Keysight Technologies

^{*} Equivalent measurement equipment may be used.



■ ELECTRICAL CHARACTERISTICS

☐ IMPEDANCE FREQUENCY CHARACTERISTICS GRAPH



O Measurement equipment


Product No.	Manufacturer
E4991A+16192A	Keysight Technologies

^{*} Equivalent measurement equipment may be used.




■PACKAGING STYLE


REEL DIMENSIONS



TAPE DIMENSIONS



Type	Α	В	K
MLZ1608	1.9±0.2	1.1±0.2	1.1 max.



Dimensions in mm