

### **Technical Data Sheet**

## **Chip LED with Right Angle Lens**

### 27-21/G6C-AN1P1/3C

#### **Features**

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb free
- The product itself will remain within RoHS compliant version

### **Descriptions**

- The 27-21 SMD LED is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

### **Applications**

- Backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

#### **Device Selection Guide**

David N.	Chip	E:44 - 1 C-1	Resin Color	
Part No.	Material	Emitted Color		
27-21/G6C-AN1P1/3C	AlGaInP	Brilliant Yellow Green	Water Clear	




Everlight Electronics Co., Ltd. Device No:DSE-0000xxxx

http://www.everlight.com Prepared date: 24-Feb.-2009 Rev 1 Page: 1 of 10




## 27-21/G6C-AN1P1/3C


### **Package Outline Dimensions**














**Note:** The tolerances unless mentioned is  $\pm 0.1$ mm, Unit = mm



## 27-21/G6C-AN1P1/3C

### **Absolute Maximum Ratings (Ta=25°C)**

Parameter	Symbol	Rating	Unit
Reverse Voltage	$V_R$	5	V
Forward Current	$I_{\mathrm{F}}$	25	mA
Peak Forward Current (Duty 1/10 @1KHz)	$I_{\mathrm{FP}}$	60	mA
Power Dissipation	$P_d$	60	mW
Electrostatic Discharge(HBM)	ESD	2000	V
Operating Temperature	Topr	-40 ~ +85	$^{\circ}\!\mathbb{C}$
Storage Temperature	Tstg	-40 ~ +90	$^{\circ}\!\mathbb{C}$
Soldering Temperature	Tsol	Reflow Soldering: 260 °C for 10 sec Hand Soldering: 350 °C for 3 sec.	

### **Electro-Optical Characteristics (Ta=25°C)**

D	C1- 1	M	T	N /	T.T., 14	Can divis
Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	$I_V$	28.5		57.0	mcd	
Viewing Angle	2 0 1/2		130		deg	
Peak Wavelength	λр		575		nm	
Dominant Wavelength	λd	569.5		577.5	nm	I <sub>F</sub> =20mA
Spectrum Radiation Bandwidth	Δλ		20		nm	
Forward Voltage	$V_{\mathrm{F}}$	1.70	2.00	2.40	V	
Reverse Current	$I_R$			10	$\mu$ A	V <sub>R</sub> =5V

#### **Notes:**

- 1. Tolerance of Luminous Intensity ±11%
- 2.Tolerance of Dominant Wavelength ±1nm

Everlight Electronics Co., Ltd. Device No:DSE-0000xxxx http://www.everlight.com Prepared date: 24-Feb.-2009

Prepared by: Cheng Dejiang

Page: 3 of 10

Rev 1



## 27-21/G6C-AN1P1/3C

### Bin Range Of Dom. Wavelength

		0			
Groups	Bin	Min	Max	Unit	Condition
	C16	569.5	571.5	1 20 4	
A	C17	571.5	573.5		I 20 A
	C18	573.5	575.5	nm	$I_F=20\text{mA}$
	C19	575.5	577.5		

### **Bin Range Of Luminous Intensity**

Bin	Min	Max	Unit	Condition
N1	28.5	36.0		
N2	36.0	45.0	mcd	$I_F=20mA$
P1	45.0	57.0		

#### **Notes:**


- 1.Tolerance of Luminous Intensity ±11%
- 2.Tolerance of Dominant Wavelength ±1nm


Everlight Electronics Co., Ltd. Device No:DSE-0000xxxx http://www.everlight.com Prepared date: 24-Feb.-2009 Rev 1 Page: 4 of 10




### 27-21/G6C-AN1P1/3C


### **Typical Electro-Optical Characteristics Curves**










Forward Current Denating Curve










# Radiation Diagram





### 27-21/G6C-AN1P1/3C

### Label explanation


**CAT: Luminous Intensity Rank** 

**HUE: Dom. Wavelength Rank** 

**REF: Forward Voltage Rank** 



#### **Reel Dimensions**




**Note:** The tolerances unless mentioned is  $\pm 0.1$ mm, Unit = mm




### 27-21/G6C-AN1P1/3C

### Carrier Tape Dimensions: Loaded quantity 3000 PCS per reel



**Note:** The tolerances unless mentioned is  $\pm 0.1$ mm, Unit = mm

### **Moisture Resistant Packaging**



Everlight Electronics Co., Ltd. Device No:DSE-0000xxxx http://www.everlight.com

Prepared date: 24-Feb.-2009

Rev 1

Page: 7 of 10



## 27-21/G6C-AN1P1/3C

### **Reliability Test Items And Conditions**

The reliability of products shall be satisfied with items listed below.

Confidence level: 90%

LTPD: 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp. : 260°C±5°C Min. 5sec.	6 Min.	22 PCS.	0/1
2	Temperature Cycle	$H: +100^{\circ}\mathbb{C}$ 15min $\int 5 \text{ min}$ $L: -40^{\circ}\mathbb{C}$ 15min	300 Cycles	22 PCS.	0/1
3	Thermal Shock	$H: +100^{\circ}\mathbb{C}$ 5min $\int 10 \sec$ $L: -10^{\circ}\mathbb{C}$ 5min	300 Cycles	22 PCS.	0/1
4	High Temperature Storage	Temp. : 100°C	1000 Hrs.	22 PCS.	0/1
5	Low Temperature Storage	Temp. : -40°€	1000 Hrs.	22 PCS.	0/1
6	DC Operating Life	$I_F = 20 \text{ mA}$	1000 Hrs.	22 PCS.	0/1
7	High Temperature / High Humidity	85°C / 85%RH	1000 Hrs.	22 PCS.	0/1

http://www.everlight.com

Prepared date: 24-Feb.-2009

Rev 1

Page: 8 of 10



### 27-21/G6C-AN1P1/3C

#### **Precautions For Use**


1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
  - 2.1 Do not open moisture proof bag before the products are ready to use.
  - 2.2 Before opening the package: The LEDs should be kept at  $30^{\circ}$ C or less and 90%RH or less.
  - 2.3 After opening the package: The LED's floor life is 1 year under 30°C or less and 60% RH or less. If unused LEDs remain, it should be stored in moisture proof packages.
  - 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

Baking treatment :  $60\pm5^{\circ}$ C for 24 hours.

- 3. Soldering Condition
- 3.1Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

Prepared date: 24-Feb.-2009




### 27-21/G6C-AN1P1/3C

#### 4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than  $350^{\circ}$ C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

#### 5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



EVERLIGHT ELECTRONICS CO., LTD.

Office: No 25, Lane 76, Sec 3, Chung Yang Rd, Tucheng, Taipei 236, Taiwan, R.O.C Tel: 886-2-2267-2000, 2267-9936

Fax: 886-2267-6244, 2267-6189, 2267-6306

http://www.everlight.com