

# 60V, $13m\Omega$ Synchronous Rectifier

Parameters Subject to Change Without Notice

### **DESCRIPTION**

 $JW^{\otimes}7707C$  is a synchronous rectifier for Flyback converters. It integrates a 60V power MOSFET that can replace Schottky diode for high efficiency. It turns on the internal MOSFET if the  $V_{SW}$ <-500mV and turns it off before the current from GND to SW is lower than zero.

Company's Logo is Protected, "JW" and "JOULWATT" are Registered Trademarks of JoulWatt technology Inc.


# **FEATURES**

- Supports DCM and Quasi-Resonant Flyback converter
- Integrated 13mΩ 60V Power MOSFET
- Supports High-side and Low-side Rectification
- No need external power supply

#### **APPLICATIONS**

- Flyback converters
- Adaptors

#### TYPICAL APPLICATION



Note 1:  $R_{VCC}$  is recommended in case IC is damaged in CCM.

Note 2:  $D_{VCC}$  is recommended if VCC voltage is too low in light load.

# **ORDER INFORMATION**

	LEAD FREE FINISH	TAPE AND REEL <sup>1)</sup>	BULK	TRAY	PACKAGE	TOP MARKING <sup>2)</sup>
	JW7707CESOP#PBF	JW7707CESOP#TRPBF	-	-	ESOP8	JW7707C
						XXXXXXX
	11477070C0DD#DDF	JW7707CSOPB#TRPBF	PBF - SOP	6000	JW7707C	
	JW7707CSOPB#PBF			-	SOP8	xxxxxxx
	1147707CT011/IDDE	JW7707CTOH#TRPBF	-	- TO251-3	T0254 2	JW7707C
	JW7707CTOH#PBF				xxxxxx	


#### Notes:



2) Line 1 of top marking means Part No., and the line 2 of top marking means Date Code.

# **PIN CONFIGURATION**

#### **TOP VIEW**



# ABSOLUTE MAXIMUM RATING1)

SW PIN	60V
VCC PIN	
Maximum Power Dissipation <sup>2)</sup>	2.5W
Junction Temperature <sup>3)</sup>	
Lead Temperature	260°C
Storage Temperature	

## RECOMMENDED OPERATING CONDITIONS

SW Pin	20V to 55V
VCC PIN	7V to 9V
Operation Junction Temp.	40°C to 125°C
THERMAL PERFORMANCE <sup>4)</sup>	$ heta_{JA} \qquad  heta_{Jc}$
ESOP8	5010°C/W
SOP8	
TO251-3	
Note	

#### Note:

- 1) Exceeding these ratings may damage the device.
- 2) TA=25 °C. The maximum allowable power dissipation is a function of the maximum junction temperature T<sub>J</sub>(MAX), the junction-to-ambient thermal resistance θ<sub>JA</sub>, and the ambient temperature T<sub>A</sub>. The maximum allowable continuous power dissipation at any ambient temperature is calculated by P<sub>D</sub>(MAX)=(T<sub>J</sub>(MAX)-T<sub>A</sub>)/ θ<sub>JA</sub>. Exceeding the maximum allowable power dissipation will cause excessive die temperature, and the regulator will go into thermal shutdown. Internal shutdown circuitry protects the device from permanent damage.
- 3) Measured on JESD51-7, 4-layer PCB.

# **ELECTRICAL CHARACTERISTICS**


TA = 25°C, unless otherwise stated.							
Item	Symbol	Condition	Min.	Тур.	Max.	Units	
VCC Section							
VCC Operation Voltage	V <sub>cc</sub>	SW=40V, VCC=0.1uF	7.4	7.75	8.1	V	
VCC Start up Voltage	V <sub>CC_STAR UP</sub>		3.6	3.8	4.0	V	
VCC UVLO	V <sub>CC_UVLO</sub>		3.5	3.65	3.8	<b>V</b>	
Quiescent Current	I <sub>Q</sub>	V <sub>CC</sub> =6.5V, C <sub>VCC</sub> =0.1uF	70	85	100	uA	
Internal MOS Section							
Internal MOS R <sub>dson</sub>	R <sub>dson</sub>	VCC=8.5V, Isw=8A		13	20	mΩ	
Maximum Peak Current	I <sub>peak</sub>	TJ=25℃	(	58		Α	
Drain Current-continuous	ID	TJ=25℃		20		Α	
Internal MOS turn on delay	T <sub>DON</sub>	(		24		nS	
Internal MOS turn off delay	$T_{DOFF}$	(4)		10		nS	
Internal MOS turn on minimum time	Ton_min			1		uS	
Internal MOS turn off minimum time	T <sub>OFF_MIN</sub>		2.5	3.5		uS	
SW Section							
Internal MOS turn on Threshold	V <sub>MOS_ON</sub>			-0.5		V	
SW to GND Breakdown Voltage	V <sub>(BR)DSS</sub>	VCC=9V, I <sub>SW</sub> =250uA	60			V	

JW7707C

# **PIN DESCRIPTION**

Pin No. ESOP8	Name	Description		
1、2、3	GND	Ground		
4	VCC	Power supply, Bypass a capacitor between VCC and GND.		
5、6、7	NC	Not Connected.	<b>A</b>	
8、9	SW	Internal Power MOSFET Drain.		

# **BLOCK DIAGRAM**



**JoulWatt** 

#### **FUNCTIONAL DESCRIPTION**

#### Operation

JW7707C is a synchronous rectifier, it can replace the Schottky to improve the efficiency in Flyback converters. It supports operation in DCM and Quasi-Resonant Flyback converters. It can power itself through the internal LDO during the turn-off period, a 0.1uF capacitor is needed between VCC and GND.

## **Turn-on Blanking Time**

The control circuitry contains a blanking function. When the internal MOSFET is turned on, it at least last for some time, the turn on blanking time is about 1uS. During the turn on blanking period, the turn off threshold is not totally blanked, but changes the threshold current. This assures that the internal MOSFET can always be turned off even during the blanking period.

#### **Under-Voltage Lockout (UVLO)**


When the VCC is below UVLO threshold, the internal MOSFET is turned off and never turned on before the VCC exceeds the startup voltage.

#### **Turn On Phase**

The switch current first flows through the body diode of integrate MOSFET, which generates a negative  $V_{SW}$ . When the  $V_{SW}$  is higher than 0.7V and then  $V_{SW}$  is lower than  $V_{MOS\_ON}$ , it turns on the integrate MOSFET after 24ns delay.

#### **Turn Off Phase**

The JW7707C senses the current of the internal MOSFET  $I_{SW}$ , before  $I_{SW}$  is lower than Internal MOS turn off threshold, the driver voltage of the switch is pulled down to zero after 10ns delay.




Turn on and turn off delay

## Startup

During the startup period, when the VCC is lower than startup voltage, the internal MOSFET is turned off. The current flows though body diode until the VCC exceeds the startup voltage.

#### **RC Snubber Circuit**


In some applications (output short circuit protection), the inductor current may go into slight CCM condition. To avoid the voltage spike across the synchronous rectifier, we suggest RC snubber should be placed between SW and GND, and a resistor should be paralleled with VCC capacitor.



**RC Snubber circuit** 

#### **PCB Layout Guidelines**

- The VCC pin must be locally bypassed with a capacitor.
- 2. The PAD must be connected to main power loop.
- NC pins can be connected to SW pins for ESOP package.
- The distance between GND and SW should be more than 1mm in case of too much coupled noise.
- 5. The EUT, a 5V/2A adaptor<sup>4)</sup>, can pass  $\pm$  25KV air discharging test by following with the recommended layout .



The recommended layout


#### Package and Bag Caution


- 1. JW7707C is Moisture-Sensitive Devices and its MSL<sup>5)</sup> (Moisture-Sensitive Level) is level-3.
- 2. Calculated shelf life in sealed bag is  $\underline{12}$  months at <40  $^{\circ}$ C and <90%RH(Relative Humidity).
- 3. Peak package body temperature<sup>5)</sup> is 260 °C.
- After bag is opened, devices that will be subjected to reflow solder or other high temperature process must
  - a) Mounted within <u>168 hours</u> of factory at the condition  $\leq 30^{\circ}\text{C}/60^{\circ}\text{RH}$ .
  - b) Stored at <10%RH.
- 5. Devices require bake before mounting if Humidity Indicator Car(HIC) is >10%RH when read at  $23\pm5^{\circ}$ C.
- 6. If baking is required, devices may be baked for 48 hours at  $125\pm5$  °C . If device containers cannot be subjected to high temperature for shorter bake times are desired, reference IPC/JEDEC J-STD-033 for bake procedure.

#### Note:


- 4) ESD pass criterion is  $\pm$  15KV air discharging can be met per IEC61000-4-2. And the test equipment is TESEQ NSG 438.
- 5) Level and body temperature defined by IPC/JEDEC J-STD-020.


# **PACKAGE OUTLINE**





TO251-3 UNIT: mm





Cumbal	Dimensions In Millimeters		Dimensions In Inches			
Symbol	Min.	Max.	Min.	Max.		
Α	2.200	2.400	0.087	0.094		
A1	1.050	1.350	0.042	0.054		
В	1.350	1.650	0.053	0.065		
b	0.500	0.700	0.020	0.028		
b1	0.700	0.900	0.028	0.035		
С	0.430	0.580	0.017	0.023		
c1	0.430	0.580	0.017	0.023		
D	6.350	6.650	0.250	0.262		
D1	5.200	5.400	0.205	0.213		
E	5.400	5.700	0.213	0.224		
е	2.300 TYP.		0.091 TYP.			
e1	4.500	4.700	0.177	0.185		
L	7.500	7.900	0.295	0.311		

# **IMPORTANT NOTICE**

 Joulwatt Technology Inc. reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein.

- Any unauthorized redistribution or copy of this document for any purpose is strictly forbidden.
- Joulwatt Technology Inc. does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Copyright © 2015 JW7707C Incorporated.

All rights are reserved by Joulwatt Technology Inc.