

Is Now Part of





ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor and is officers, employees, uniotificated use, even if such claim any manner.





Тор

FAIRCHILD

Power 33

D D

Bottom

MOSFET Maximum Ratings T_A = 25 °C unless otherwise noted.

Symbol	Parameter				Ratings	Units
V _{DS}	Drain to Source	/oltage			60	V
V _{GS}	Gate to Source V	/oltage			±20	V
	Drain Current	-Continuous	T _C = 25 °C	(Note 5)	84	
		-Continuous	T _C = 100 °C	(Note 5)	53	^
Ъ		-Continuous	T _A = 25 °C	(Note 1a)	18	Α
		-Pulsed		(Note 4)	416	
E _{AS}	Single Pulse Ava	lanche Energy		(Note 3)	253	mJ
P _D	Power Dissipatio	ower Dissipation $T_{\rm C} = 25 ^{\circ}{\rm C}$		54	W	
	Power Dissipatio	n	T _A = 25 °C	(Note 1a)	2.3	VV
T _J , T _{STG}	Operating and Storage Junction Temperature Range				-55 to +150	°C

Thermal Characteristics

$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	(Note 1)	2.3	°C/W
R_{\thetaJA}	Thermal Resistance, Junction-to-Ambient	(Note 1a)	53	C/ VV

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDMC86570L	FDMC86570L	Power33	13 "	12 mm	3000 units


1

March 2015

Symbol	Parameter	Test Con	ditions	Min.	Тур.	Max.	Units
Off Chara	acteristics						
BV _{DSS}	Drain to Source Breakdown Voltage	I _D = 250 μA, V _{GS} = 0 V		60			V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	$I_D = 250 \ \mu$ A, referenced to 25 °C			30		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 48 V, V _{GS} = 0 V				1	μA
I _{GSS}	Gate to Source Leakage Current	$V_{GS} = \pm 20 \text{ V}, V_{DS} = 0 \text{ V}$				±100	nA
On Chara	cteristics						
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 250 \ \mu A$		1.0	1.8	3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = 250 \ \mu$ A, referenced to 25 °C			-7		mV/°C
r _{DS(on)}		V _{GS} = 10 V, I _D = 18 A			3.1	4.3	mΩ
	Static Drain to Source On Resistance	V _{GS} = 4.5 V, I _D = 15 A			4.7	6.5	
		$V_{GS} = 10 \text{ V}, \ \text{I}_{\text{D}} = 18 \text{ A}, \ \text{T}_{\text{J}} = 125 \ ^{\circ}\text{C}$			5.0	6.9	
9 _{FS}	Forward Transconductance	$V_{DD} = 5 V, I_D = 18 J$	A		75		S
Dynamic	Characteristics						
C _{iss}	Input Capacitance	V _{DS} = 30 V, V _{GS} = 0 V, f = 1 MHz			4790	6705	pF
C _{oss}	Output Capacitance				821	1150	pF
C _{rss}	Reverse Transfer Capacitance				19	30	pF
R _g	Gate Resistance			0.1	0.9	2.7	Ω
Switching	g Characteristics						
t _{d(on)}	Turn-On Delay Time				19	34	ns
t _r	Rise Time	V_{DD} = 30 V, I _D = 18 A, V _{GS} = 10 V, R _{GEN} = 6 Ω			6.2	12	ns
t _{d(off)}	Turn-Off Delay Time				38	61	ns
t _f	Fall Time				3.9	10	ns
Q _{g(TOT)}	Total Gate Charge	$V_{GS} = 0 V$ to 10 V			63	88	nC
Q _{g(TOT)}	Total Gate Charge	$V_{GS} = 0 V \text{ to } 4.5 V$	V _{DD} = 30 V,		29	41	nC
Q _{gs}	Gate to Source Charge	I _D = 18 A			14		nC
Q _{gd}	Gate to Drain "Miller" Charge				6.3		nC
Drain-Sou	urce Diode Characteristics						
		V _{GS} = 0 V, I _S = 18 A	A (Note 2)		0.8	1.3	V
V _{SD}	Source to Drain Diode Forward Voltage	$V_{GS} = 0 \text{ V}, \text{ I}_{S} = 1.9$			0.7	1.2	V
t _{rr}	Reverse Recovery Time				43	69	ns
		I _F = 18 A, di/dt = 100 A/μs					


Q_{rr} Notes:

1. $R_{\theta,JA}$ is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. $R_{\theta CA}$ is determined by the user's board design.



Reverse Recovery Charge

a. 53 °C/W when mounted on a 1 in² pad of 2 oz copper



b. 125 °C/W when mounted on a minimum pad of 2 oz copper

26


42


nC

3. E_{AS} of 253 mJ is based on starting T_J = 25 °C, L = 3 mH, I_{AS} = 13 A, V_{DD} = 60 V, V_{GS} = 10 V. 100% test at L = 0.1 mH, I_{AS} = 43 A.

4. Pulsed Id please refer to Fig 11 SOA graph for more details.

5. Computed continuous current limited to Max Junction Temperature only, actual continuous current will be limited by thermal & electro-mechanical application board design.








1

60


150

















NOTES: UNLESS OTHERWISE SPECIFIED

- A) PACKAGE STANDARD REFERENCE: JEDEC MO-240, ISSUE A, VAR. BA, DATED OCTOBER 2002.
- B) ALL DIMENSIONS ARE IN MILLIMETERS.
- C) DIMENSIONS DO NOT INCLUDE BURRS OR MOLD FLASH. MOLD FLASH OR BURRS DOES NOT EXCEED 0.10MM.
- D) DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
- E) DRAWING FILE NAME: PQFN08HREV1

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC