

# 9mm Size Metal Shaft Multi-ganged Type RK097 Series

Single-shaft without switch type				
Part number		RK097111080J		
Number of resistor elements		Single-unit		
Mounting direction		Horizontal type		
Fixing method of bushing		Screw		
Shaft types		Flat		
Length of the shaft		15mm		
Center detent		Without		
Total resistance		10kΩ		
Resistance taper		15A		
Operating temperature range		-20℃ to +70℃		
Electrical Performance	Total resistance tolerance	±20%		
	Rated power	0.05W		
	Maximum operating voltage	50V AC, 10V DC		
	Residual resistance	20Ω max.		
	Insulation resistance	100MΩ min. 250V DC		
	Voltage proof	300V AC for 1 minute		
Mechanical Performance	Total rotational angle	300°±5°		
	Rotational torque	2 to 25mN·m		
	Stopper strength	0.5N·m		
	Push-pull strength	100N max.		


#### RK097 Series - Basic information

	Vibration	10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z and for 2 hours respectively
Durability	Operating life	15,000 cycles
Minimum order unit (pcs.)	Japan	1,200
	Export	2,400


#### Photo



#### Dimensions




### Mounting Hole Dimensions




Viewed from mounting side.


### **Dimensions of Terminal**



#### **Dimensions of Bushings**



### Attached Parts



These parts are attached to the following products.

### **Packing Specifications**

#### Tray

Number of packages (pcs.)	1 case / Japan	1,200
	1 case / export packing	2,400
Export package mea	surements (mm)	375×490×185

## Soldering Conditions

#### **Reference for Dip Soldering**

Preheating	Soldering surface temperature	100℃ max.
	Heating time	2 min. max.
Dip soldering	Soldering temperature	260±5℃ max.
	Soldering time	5±1s
No. of solders		2 time max.

#### **Reference for Hand Soldering**

Tip temperature	350℃ max.
Soldering time	3s max.
No. of solders	1 time

#### Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. For the switch attached, the single-shaft or inner shaft of the dual-shaft type can be chosen.
- 3. Please place purchase orders per minimum order unit (integer).
- 4. Products other than those listed in above products are also available. Please contact us for details.
- 5. This products can be used in vehicles.

Although these products are designed to perform over a wide operating temperature range, please ensure that you receive and read the formal delivery specifications before use.