Note: This datasheet may be out of date Please download the latest datasheet of LFL215G51TC1A149 from the official website of Murata Manufacturing Co., Ltd.

https://www.murata.com/en-global/products/productdetail?partno=LFL215G51TC1A149

LFL215G51TC1A149












Appearance & Shape





Terminal of *NC" should be fixed to no connected pattern.

* All the technical data and information contained herein are change without prior notice.

Packaging Information

| Packaging | Specifications | Minimum Order Quantity |
|-----------|---------------------|---------------------------|
| - | 180mm Embossed Tape | 4000 |



Features

Ultra-small, low-profiled, lightweight chip filters based on ceramic multilayer technology.

Offering stable high selectivity up to very high frequency.

- 1. Low loss
- 2. Ultra-small, low-profiled, lightweight low-pass filters.
- 3. Ideal for removing high-frequency harmonics at power amplifier and IF stage.
- 4. Available in tape and reel packings for automatic mounting.
- 5. Absolutely no adjustment required.
- 6. Reflow solderable.
- 7. Center frequencies and responses are ready for customization. Samples are available in a short lead time.

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/


Last updated : 2018/12/10

Note: This datasheet may be out of date

 $\underline{ Please \ download \ the \ latest \ data sheet \ of \ LFL 215G51TC1A149 \ from \ the \ official \ website \ of \ Murata \ Manufacturing} }$

 $\underline{\text{Co., Ltd.}} \\ \text{https://www.murata.com/en-global/products/productdetail?partno=LFL215G51TC1A149} \\$

LFL215G51TC1A149



| Applications | WLAN | |
|---------------------------------|------------------------------|--|
| Nominal Center Frequency(fo) | 5512.00MHz | |
| Bandwidth(BW) | fo±363.00MHz | |
| Insertion Loss in BW I) | 0.70dB max. (at 25°C) | |
| Insertion Loss in BW II) | 0.90dB max. (-40 to +85°C) | |
| Attenuation(Absolute Value) I) | 30.0dB min. at 2x(fo±363)MHz | |
| Attenuation(Absolute Value) II) | 20.0dB min. at 3x(fo±363)MHz | |
| VSWR(max.) | 1.9 | |
| Characteristic Impedance(Nom.) | 50Ω | |
| Power Capacity | 3W | |
| Operating Temperature Range | -40℃ to 85℃ | |
| L x W (size) | 2.00x1.25mm | |
| Thickness(max.) | 1.05mm | |

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated :2018/12/10


Note: This datasheet may be out of date


 $\underline{ Please \ download \ the \ latest \ data sheet \ of \ LFL 215G51TC1A149 \ from \ the \ official \ website \ of \ Murata \ Manufacturing} }$

 $\underline{\text{Co., Ltd.}} \\ \text{https://www.murata.com/en-global/products/productdetail?partno=LFL215G51TC1A149} \\$

LFL215G51TC1A149







Frequency Characteristics

Spurious Response

3 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering

