

MH188 Specifications Ultra High Sensitivity Hall Effect Latch

MH188 Hall-effect sensor is a temperature stable, stress-resistant sensor. Superior high-temperature performance is made possible through a dynamic offset cancellation that utilizes chopper-stabilization. This method reduces the offset voltage normally caused by device over molding, temperature dependencies, and thermal stress.

MH188 includes the following on a single silicon chip: voltage regulator, Hall voltage generator, small-signal amplifier, chopper stabilization, Schmitt trigger, Advanced DMOS wafer fabrication processing is used to take advantage of low-voltage requirements, component matching, very low input-offset errors, and small component geometries.

This device requires the presence of both south and north polarity magnetic fields for operation. In the presence of a south polarity field of sufficient strength, the device output sensor on, and only switches off when a north polarity field of sufficient strength is present.

MH188 is rated for operation between the ambient temperatures −40°C and 85°C for the E temperature range, and −40°C to 125°C for the K temperature range. The two package styles available provide magnetically optimized solutions for most applications. Package SO is an SOT-23, a miniature low-profile surface-mount package, while package UA is a three-lead ultra mini SIP for through-hole mounting.

Packages is Halogen Free standard and which have been verified by third party lab.

Features and Benefits

- DMOS Hall IC Technology.
- Reverse bias protection on power supply pin.
- Chopper stabilized amplifier stage.
- Optimized for BLDC motor applications.
- Reliable and low shifting on high Temp condition.
- Good ESD Protection.
- 100% tested at 125 °C for K.
- Custom sensitivity / Temperature selection are available.


Applications

- High temperature Fan motor
- 3 phase BLDC motor application
- Speed sensing
- Position sensing
- Current sensing
- Revolution counting
- Solid-State Switch
- Linear Position Detection
- Angular Position Detection
- Proximity Detection
- High ESD Capability



MH188 Specifications Ultra High Sensitivity Hall Effect Latch


Ordering Information



Part No.	Temperature Suffix	Package Type
MH188KUA	$K (-40^{\circ}C \text{ to} + 125^{\circ}C)$	UA (TO-92S)
MH188KSO	$K (-40^{\circ}C \text{ to} + 125^{\circ}C)$	SO (SOT-23)
MH188EUA	$E (-40^{\circ}C \text{ to} + 85^{\circ}C)$	UA (TO-92S)
MH188ESO	E $(-40^{\circ}\text{C to} + 85^{\circ}\text{C})$	SO (SOT-23)

KUA spec is using in industrial and automotive application. Special Hot Testing is utilized.

Functional Diagram





MH188 Specifications Ultra High Sensitivity Hall Effect Latch

Absolute Maximum Ratings At (Ta=25 °C)

Characteristics			Values	Unit
Supply voltage, (VDD)			28	V
Output Voltage,(Vout)			28	V
Reverse voltage, (VDD)			-28/-0.3	V
Output current, (Iout)			50	mA
O 1: T 1 P	(T-)	"E" version	-40 to +85	°C
Operating Temperature Range,	(1a)	"K" version	-40 to +125	°C
Storage temperature range, (<i>Ts</i>)			-65 to +150	\mathcal{C}
Maximum Junction Temp,(<i>Tj</i>)			150	\mathcal{C}
Thermal Resistance	$(heta_{ja})$	UA/SO	206 / 543	°C/W
	(θ_{jc}) UA / SO		148 / 410	°C/W
Package Power Dissipation, (P_D) UA / SO			606 / 230	mW


 $\textit{Note: Do not apply reverse voltage to V_{DD} and V_{OUT} Pin, It may be caused for Miss function or damaged device.}$

Electrical Specifications

DC Operating Parameters: $T_A=+25$ °C, $V_{DD}=12V$

Parameters	Test Conditions	Min	Тур	Max	Units
Supply Voltage, (V_{DD})	Operating	2.5		26.0	V
Supply Current,(<i>IDD</i>)	B <bop< td=""><td></td><td></td><td>5.0</td><td>mA</td></bop<>			5.0	mA
Output Saturation Voltage, (V_{sat})	Iout=20mA,B>BOP			400.0	mV
Output Leakage Current, (Ioff)	IOFF B <brp, vout="12V</td"><td></td><td></td><td>10.0</td><td>uA</td></brp,>			10.0	uA
Internal Oscillator Chopper Frequency, (fosc)			69		kHz
Output Rise Time, (T_R)	RL=1.1KΩ, CL =20pF		0.04	0.45	uS
Output Fall Time, (<i>T_F</i>)	RL=820Ω; CL =20pF		0.18	0.45	uS
Electro-Static Discharge	НВМ	4			KV
Operate Point,(BoP)	UA(SO)	5(-25)		25(-5)	Gauss
Release Point,(BRP)	UA(SO)	-25(5)		-5(25)	Gauss
Hysteresis,(BHYS)			30		Gauss

Typical application circuit






Specifications *MH188* Ultra High Sensitivity Hall Effect Latch


Sensor Location, Package Dimension and Marking

MH188 Package

UA Package



Hall Chip location



NOTES:


- 1).Controlling dimension: mm
- 2).Leads must be free of flash and plating voids
- 3).Do not bend leads within 1 mm of lead to package interface.
- 4).PINOUT:

Pin 1 V_{DD}


Pin 2 **GND**

Pin 3 Output


Output Pin Assignment (Top view)



SO Package (Top View)



Hall Plate Chip Location (Bottom view)



1. PINOUT (See Top View at left :)

Pin 1 V_{DD}

Pin 2 Output

Pin 3 **GND**

- 2. Controlling dimension: mm
- 3. Lead thickness after solder plating will be 0.254mm maximum