

Chip beads

For general signal line

MMZ series

MMZ0603 type

MMZ0603

0603[0201 inch]*

* Dimensions Code JIS[EIA]

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

<u> </u>
The storage period is less than 12 months. Be sure to follow the storage conditions (Temperature: 5 to 40°C, Humidity: 10 to 75% RF or less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
On not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C.
Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference.
Use a wrist band to discharge static electricity in your body through the grounding wire.
On not expose the products to magnets or magnetic fields.
On not use for a purpose outside of the contents regulated in the delivery specifications.
The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.
If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment

set forth in the each catalog, please contact us.

- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.



Chip beads

For general signal line

Product compatible with RoHS directive
Halogen-free
Compatible with lead-free solders

Overview of MMZ0603 type

FEATURES

- O Noise reduction solution for general signal line.
- Various frequency characteristics with 4 materials of different features for countermeasures against everything from general signals to high-speed signals.

APPLICATION

- O Noise removal for mobile devices such as smartphones and tablet terminals, and various modules.
- O Noise removal for PCs and recorders, household appliances such as STBs, smart grids, and industrial equipment.

PART NUMBER CONSTRUCTION

MMZ	0603	S	100		С		Т	00	00
Series name	L×W×T dimensions (mm)	Material name	Impedance (Ω) at 100M		acteristic type	Pac	kaging style	Interna	al code
	0603 0.6×0.3x0.3	D	100	10	С	Т	Taping	00	00
		F	121 12	20			_		
		S							
		Υ							

■ OPERATING TEMPERATURE RANGE, PACKAGE QUANTITY, PRODUCT WEIGHT

	Temperat	ure range	Package quantity	Individual weight
Type	Operating	Storage		
туре	temperature	temperature*		
	(°C)	(°C)	(pieces/reel)	(mg)
MMZ0603	-55 to +125	-55 to +125	15.000	0.3


^{*} The Storage temperature range is for after the circuit board is mounted.

RoHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html

O Halogen-free: Indicates that CI content is less than 900ppm, Br content is less than 900ppm, and that the total CI and Br content is less than 1500ppm.



■ RECOMMENDED REFLOW PROFILE



Preheating		Soldering	Soldering		Peak	
Temp.		Time	Temp.	Time	Temp.	Time
T1	T2	t1	Т3	t2	T4	t3
150°C	180°C	60 to 120s	230°C	30 to 60s	250 to 260°C	10s



■ MATERIAL CHARACTERISTICS

S material: Standard type that features impedance characteristics similar to those of a typical ferrite core. For signal line applications in which the blocking region is near 100MHz. Impedance values selected for effectiveness at 40 to 300MHz.

Y material: High frequency range type intended for the 100MHz region and above.


For signal line applications in which the signal frequency is far from the cutoff frequency. Impedance values selected for effectiveness at 80 to 400MHz.

D material: For applications calling for low insertion loss at low frequencies and sharply increasing impedance at high frequencies.

Designed for high impedance at high frequencies (300MHz to 1GHz) for signal line applications.


F material: This new product inherits the characteristic of our D-material, namely its sharp impedance rise time, and its impedance peak frequency has been shifted higher into range. The product offers excellent noise suppression from 600MHz to as high as in the GHz range.

TYPICAL MATERIAL IMPEDANCE CHARACTERISTICS






SHAPE & DIMENSIONS





Dimensions in mm

■ RECOMMENDED LAND PATTERN



Dimensions in mm



■ ELECTRICAL CHARACTERISTICS

□ CHARACTERISTICS SPECIFICATION TABLE

Impedance		DC resistance	Rated current	Part No.
[100MHz]				
(Ω)	Tolerance	(Ω)max.	(mA)max.	
10	$\pm 5\Omega$	0.05	1000	MMZ0603S100CT000
80	±25%	0.30	200	MMZ0603S800CT000
120	±25%	0.45	200	MMZ0603S121CT000
240	±25%	0.57	200	MMZ0603S241CT000
470	±25%	1.30	100	MMZ0603S471CT000
600	±25%	1.45	100	MMZ0603S601CT000
75	±25%	0.35	300	MMZ0603Y750CT000
120	±25%	0.39	200	MMZ0603Y121CT000
240	±25%	0.80	200	MMZ0603Y241CT000
470	±25%	1.40	200	MMZ0603Y471CT000
600	±25%	1.50	200	MMZ0603Y601CT000
33	±25%	0.70	200	MMZ0603D330CT000
47	±25%	0.70	200	MMZ0603D470CT000
56	±25%	0.95	100	MMZ0603D560CT000
80	±25%	1.25	100	MMZ0603D800CT000
120	±25%	1.40	100	MMZ0603D121CT000
10	±5Ω	0.50	200	MMZ0603F100CT000
22	±25%	1.00	200	MMZ0603F220CT000
33	±25%	1.30	150	MMZ0603F330CT000

O Measurement equipment

Measurement item	Product No.	Manufacturer
Impedance	E4991A+16197	Keysight Technologies
DC resistance	Type-7556	Yokogawa

^{*} Equivalent measurement equipment may be used.





■ ELECTRICAL CHARACTERISTICS

□ Z VS. FREQUENCY CHARACTERISTICS (BY SERIES)


MMZ0603S-C series 1000 900 MMZ0603S471C 800 700 mpedance (Ω) MMZ0603S121C 600 MMZ0603S800C 500 MMZ0603S100C 400 300 200 100 100 1000 10000 Frequency (MHz)

1000 MMZ0603Y601C 900 800 700 mpedance (Ω) 600 500 MMZ0603Y121C 400






MMZ0603F series





MMZ0603S100CT000


■ ELECTRICAL CHARACTERISTICS


Z, X, R VS. FREQUENCY CHARACTERISTICS







































Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.




ELECTRICAL CHARACTERISTICS

□Z, X, R VS. FREQUENCY CHARACTERISTICS


MMZ0603D121CT000




MMZ0603F100CT000



MMZ0603F220CT000




MMZ0603F330CT000




■PACKAGING STYLE

□REEL DIMENSIONS




Dimensions in mm

TAPE DIMENSIONS



Dimensions in mm

Type	Α	В	P1	K
MMZ0603	0.38±0.05	0.68±0.05	2.0±0.05	0.5max.



Dimensions in mm