Surface Mount Fuses EBF Fuse Fast-Acting > 446/447 Series

446/447 Series EBF Fuse Fast-Acting











Agency Approvals

AGENCY	AGENCY FILE NUMBER	AMPERE RANGE	
71	E71611	2A - 10A	
(29862	2A - 10A	

Electrical Characteristics for Series

% of Ampere Rating	Opening Time		
100%	4 hours, Minimum		
200%	0.15 sec. Min.; 5 sec. Max.		

Description

The 446/447 series are circuit-board mountable, flat profile, fast-acting fuses designed for protection of electronic ballasts and power inverter applications. The 446 series is designed with leads for surface mount applications, and the 447 series is designed with leads for through-hole applications.

This series of devices are 100% lead-free and meets the requirements of the RoHS directive.

Features

- RoHS compliant and 100% lead-free
- Ideal for use in electronic lighting ballast, power supply and power inverter applications.
- Rated for use in 125,
- 250, 277 and 350 VAC circuits.
- Based on the proven reliability of the automotive MINI® Fuse; available from 2 through 10 amperes.

Electrical Specifications by Item

Ampere	Amp Code	Max Voltage Rating (V)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Nominal Melting I ² t (A ² sec)	Agency Approvals	
Rating (A)						71	(
2.00	002.	350	100A @ 350VAC 50A @ 125VDC 450 @ 60VDC	0.0563	2.8	X	X
3.00	003.	350		0.0336	9.4	х	x
4.00	004.	350		0.0237	17	х	x
5.00	005.	350		0.0178	25	х	×
7.50	07.5	350		0.0110	68	×	×
10.0	010.	350		0.0073	93	х	×

Additional Information



Datasheet 446 Series



Datasheet 447 Series



Resources 446 Series



Resources 447 Series




Samples 446 Series



Samples 447 Series



Temperature Re-rating Curve



Note

 Re-rating depicted in this curve is in addition to the standard re-rating of 25% for continuous operation.

Soldering Parameters

446 Series:

Reflow Solder — 235°C, 5 seconds maximum. No-clean process recommended. Wave Solder — Not recommended. Non-plated terminal surfaces may not meet MIL-STD-202, Method 208.


447 Series:

Contact Littelfuse for soldering parameters.

Inside terminal face of each lead is non-plated zinc.


Non-plated zinc terminal faces may not meet MIL-STD-202, method 208. To ensure that the fuse is acceptable for the application, appropriate application testing should be performed.

Dimensions



For 447 dimensions, please contact Littelfuse for specifications.

Average Time Current Curves



Product Characteristics

Materials	Body: Plastic Body – Terminations: Tin plated Zinc, Ni barrier		
Cleaning	No-cleaning process recommended		
Operating Temperature	-40°C to 125°C		

Part Numbering System

Surface Mount Fuses:

0446 002. ZRP

Series — Amp Code —

Quantity Code ZRP = 800 Through Hole Fuses:

YXP = 4000

O447 O02. YXP
Series
Amp Code
Quantity Code

Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code
446 Series			
24mm Tape and Reel	EIA RS-481-1 (IEC 286, part 3)	800	ZRP
447 Series			
Bulk Pack	-	4000	YXP

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littlefuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littlefuse.com/disclaimer-electronics.