

# SURFACE MOUNT SCHOTTKY BARRIER RECTIFIERS




#### ROHS 🍗

## **FEATURES**

- For surface mounted applications
- Metal silicon junction, majority carrier conduction
- Low power loss, high efficiency
- Built-in strain relief, ideal for automated placement
- High forward surge current capability
- High temperature soldering guaranteed: 250°C/10 seconds at terminals
- The plastic material carries U/L recognition 94V-O

### **MECHANICAL DATA**

- Case: JEDEC DO -214AC. molded plastic
- Terminals: Axial leads. Solderable per MIL STD 750 Method 2026
- Polarity: Color band denotes cathode
- Weight: 0.003 ounce. 0.093 grams
- Mounting position: Any



## MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25  $^\circ\!\mathrm{C}$  ambient temperature unless otherwise specified.

Single phase. half wave. 60HZ. resistive or inductive load. For capacitive load. derate current by 20%

Characteristic	Symbol	SS22	SS23	SS24	SS25	SS26	SS28	SS29	SS210	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	Vrrm Vrwm Vr	20	30	40	50	60	80	90	100	V
RMS Reverse Voltage	VR(RMS)	14	21	28	35	42	56	64	71	V
Average Rectified Output Current $@T_L = 75^{\circ}C$	ю	2.0								А
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	Ігѕм	50							A	
Forward Voltage $@I_F = 1.0A$	Vfм	0.55 0.70 0.85							V	
Peak Reverse Current $@T_A = 25^{\circ}C$ At Rated DC Blocking Voltage $@T_A = 100^{\circ}C$	IRM	0.5 20								mA
Typical Thermal Resistance (Note 1)	R∂JL R∂JA	28 88								°C/W
Operating Temperature Range	Tj	-65 to +125								°C
Storage Temperature Range	Тѕтс	-65 to +150								°C


**NOTE:** 1. Measured at 1.0MHZ and applied reverse voltage of 4.0V DC

2. P.C.B.mounted with 0.2×0.2 (5.0×5.0mm)copper pad areas



# SURFACE MOUNT SCHOTTKY BARRIER RECTIFIERS

RO<u>HS 🛬</u>



www.born-tw.com