

Miniature PCB Relay OJ/OJE

- 1 pole, 1 Form A (NO) contact
- 3 to 10A rating
- Small size
- 4000V_{rms} coil to contact dielectric strength (OJ type)
- Sensitive coil optional



Typical applications Appliances, HVAC, industrial control.

Approvals

VDE 40007630, TUV R 50139166, UL E82292, CQC03001007764 Technical data of approved types on request.

Contact Data		
Contact arrangement	1 form A, 1 NO	
Rated voltage	30VDC, 250VAC	
Max. switching voltage	30VDC, 277VAC	
Rated current	3 to 10A	
Contact material	AgNi, AgSnO, AgCdO	
Min. recommended contact load	100mA, 5VDC	
Initial contact resistance	100mohms at 1A, 5VDC	
Frequency of operation	360 ops./h	
Operate time max.	OJ/OJE-L: 15ms	
	OJ/OJE-D/H: 10ms	
Release time max.	4ms	
Electrical endurance		
LM 3A, 250VAC, res., -30°C to	o +95°C 100x10 ³ (ops.
DM 5A, 250VAC, res, -30°C to	+85°C 60x10 ³ c	ops.
LMH(2) 8A, 250VAC, res., -30°C to	o +70°C 50x10 ³ c	pps.
LMH2 8A, 250VAC,res., -30°C to	+85°C 30x10 ³ c	ops.
HM 10A, 250VAC, res., -30°C	to +70°C 10x10 ³ c	ops.
HM2 10A, 250VAC, res., -30°C	to +85°C 10x10 ³ c	ops.
HM6 10A, 250VAC, res., -30°C	to +85°C 50x10 ³ c	pps.
Contact ratings		
LM	3A, 250VAC	
DM	5A 250VAC	
LMH(2)	8A 250VAC	
HM(2), HM6	10A 250VAC	
Mechanical endurance, DC coil	10x10 ⁶ operations	

Coil Data

Coil voltage range	3 to 48VDC
Operative range, IEC 61810	2
Coil insulation system according UL	Class E, F

Coil versions, DC coil, OJ/OJE-L sensitive type


	,	,			
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	Ω±10%	mW
003	3	2.25	0.15	45	200
005	5	3.75	0.25	125	200
006	6	4.5	0.3	180	200
009	9	6.75	0.45	405	200
012	12	9	0.6	720	200
024	24	18	1.2	2880	200
048	48	36	2.4	11520	200

All figures are given for coil without pre-energization, at ambient temperature +23°C.


Coil versions, DC coil, OJ/OJE-D and -H type

		,			
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	Ω±10%	mW
003	3	2.1	0.15	20	450
005	5	3.5	0.25	55.6	450
006	6	4.2	0.3	80	450
009	9	6.3	0.45	180	450
012	12	8.4	0.6	320	450
024	24	16.8	1.2	1280	450
048	48	33.6	2.4	5120	450

All figures are given for coil without pre-energization, at ambient temperature +23°C.



Coil temperature rise



3-2018, Rev. 0318 www.te.com © 2018 TE Connectivity Ltd. family of companies. All rights reserved. Catalog and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section. Catalog and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Catalog product data, 'Definitions' section, application notes and all specifications are subject to change. 1



Miniature PCB Relay OJ/OJE (Continued)


750V _{rms}
OJ: 4000V _{rms}
OJE: 3000V _{rms}
1000Mohms min
OJ: > 7.7mm / 9.4mm
OJE: > 3.2mm / 3.6mm
PTI 250

Other Data

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter


Ambient temperature	
DM:	-30°C to +85°C
HM:	-30°C to +70°C
HM2, HM6:	-30°C to +85°C
LM	-30°C to +90°C
LMH:	-30°C to +70°C
LMH2:	-30°C to +85°C
Category of environmental protection	on
IEC 61810	RTII - flux proof/dust protected
	RTIII - wash tight
Vibration resistance (functional)	10 to 55 hz., 1.5mm double amplitude
Vibration resistance (ddestructive)	10 to 55 hz., 1.5mm double amplitude
Shock resistance (functional)	10g
Shock resistance (destructive)	100g
Weight	9g
Resistance to soldering heat THT	
IEC 60068-2-20	RTII: 270°C/10s
	RTIII: 260°C/5s
Packaging unit	tray/100, carton box/1000

Terminal assignment Bottom view on solder pins



PCB layout Bottom view on solder pins 4 - .05 DIA (1.3) .067 (1.71) .300 ± .004 (7.6 ± .1) .500 ± .004 (2.54 ± .1)

Dimensions



Product	t cod	de structure	Турі	cal product code	OJ	-SH	-1	12	LMH	F	-WG	,000
Туре		Miniature PCB Relay OJ, 4kV dielectric betw		oil and contacts								
	JE	Miniature PCB Relay OJE, 3kV dielectric bet										
Category	/ of p	rotection										
SS	-	Flux proof										
SH	H	Wash tight										
Number of	of po	les										
1		1 pole										
Coil volta	age											
Co	oil co	de: please refer to coil versions table (e.g. 12	! = 12V	DC)								
Contact I	rating	g and coil power										
		450 mW coil power		200mW coil power								
DI			LM	3A type, coil power								
H				8A type, coil power								
			LMH2	8A type, coil power	200mW							
		10A type, coil power 450mW										
	-	tem designation										
		Insulation Class E (standard)	F	Insulation Class F								
Special ty												
	lank	Standard	WG	For domestic applia	inces (IEC	60335-1)					
Suffix												
,00	00	Standard										

2

Catalog and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section.

Catalog and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Catalog product data, 'Definitions' section, application notes and all specifications are subject to change.



Miniature PCB Relay OJ/OJE (Continued)

Product code	Rating	Cont. mat.	Coil	Coil power	Туре	Insulation	Enclosure	Part Number
OJ-SH-105LM,000	ЗA	AgNi	5VDC	200mW	Standard	Class E	Wash tight	1461404-1
OJE-SH-112LM,000			12VDC					1461401-5
OJE-SS-112LM,000							Flux proof	4-1419128-6
OJ-SH-112LM,000							Wash tight	1461404-6
OJ-SS-112LM,000							Flux proof	2-1419129-1
OJ-SS-124LM,000								3-1419129-1
OJ-SH-124LM,000			24VDC				Wash tight	1461404-4
OJE-SH-105DM,000	5A	1 1	5VDC	450mW				1461400-1
OJE-SS-105DM,000							Flux proof	2-1419128-8
OJE-SH-112DM,000			12VDC				Wash tight	1461400-4
OJE-SS-112DM,000							Flux proof	4-1419128-2
OJ-SH-112DM,000							Wash tight	1461406-4
OJ-SS-112DM,000							Flux proof	1-1419129-8
OJE-SH-124DM,000			24VDC				Wash tight	1461400-5
OJE-SS-124DM,000			24000				Flux proof	6-1419128-2
OJ-SS-124DM,000								2-1419129-9
OJE-SH-105LMH,000	8A	AgCdO	5VDC	200mW			Wash tight	1461403-3
OJE-SH-105LMH-WG	04	Agouo	5700	2001111	WG type		vvasir tigrit	1721875-2
OJE-SS-105LMH.000				-	Standard		Flux proof	1461034-2
OJ-SH-105LMH,000					Otaridard		Wash tight	8-1419128-1
OJ-SH-106LMH,000		-	6VDC				vvasii tigiit	1461247-1
OJE-SH-109LMH,000			9VDC					1461403-2
OJE-SS-109LMH,000			3000				Flux proof	5-1419144-3
OJ-SH-109LMH,000							Wash tight	1461247-2
OJ-SH-109LMH,000 OJ-SS-109LMH2-WG		AgSnO			WG type	-	Flux proof	1721874-4
OJ-SS-109LMHF,000		AgCdO			Standard	Class F		1721083-5
OJE-SH-112LMH.000		Agodo	12VDC	_	Stanuaru	Class F Class E	Wash tight	1461403-4
OJE-SH-112LMH-WG			12VDC		WG type		washtight	1721875-5
OJE-SI-112LMH,000					Standard	-	Flux proof	5-1419128-0
OJE-SS-112LMH2		AgSnO			Stanuaru			
OJ-SH-112LMH,000		AgCdO					Wash tight	1721261-5
OJ-SH-112LMH2		AgCuO					washtight	9-1419128-8 1-1721260-1
							Flux proof	
OJ-SS-112LMH,000		AgCdO					Flux proof	2-1419129-5
OJ-SS-112LMH2		AgSnO						1721260-5
OJ-SS-112LMHF,000		AgCdO	041/00			Class F		1721083-1
OJE-SH-124LMH,000			24VDC			Class E	Wash tight	1461403-5
OJE-SH-124LMH-WG					WG type	-		1721875-6
OJE-SS-124LMH,000					Standard		Flux proof	7-1419128-1
OJ-SH-124LMH,000							Wash tight	1461247-3
OJ-SS-124LMH,000		A = 0 = 0					Flux proof	4-1419144-4
OJ-SS-124LMH2		AgSnO				-		1721260-6
OJ-SS-124LMH2-WG		A 0.10			WG type		-	1721874-6
OJ-SS-124LMHF,000	101	AgCdO		450 \\	Standard	Class F		1461014-2
OJ-SH-105HM,000	10A	AgCdO	5VDC	450mW		Class E	Wash tight	1461405-3
OJE-SH-112HM,000			12VDC					1461402-6
OJE-SS-112HM,000							Flux proof	4-1419128-3
OJE-SS-112HM2,000		AgSnO						1721539-5
OJ-SH-112HM,000		AgCdO					Wash tight	1461405-5
OJ-SS-112HM,000							Flux proof	1419135-3
OJ-SS-112HMF,000						Class F		1461078-5
OJ-SS-112HM6-WG		AgSnO			WG type			2071398-1
OJE-SS-124HM,000		AgCdO	24VDC		Standard	Class E		6-1419128-4
OJ-SS-124HM,000								1440007-2
OJ-SS-124HM2,000		AgSnO						1721538-7

3



Miniature PCB Relay OJ/OJE (Continued)

te.com

TE Connectivity and TE connectivity (logo) are trademarks. Other products, logos and company namesmentioned herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

3-2018, Rev. 0318 www.te.com © 2018 TE Connectivity Ltd. family of companies. All rights reserved.

4

Catalog and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section.

Catalog and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Catalog product data, 'Definitions' section, application notes and all specifications are subject to change.