


## IRM-36xxM2F32series

#### **Features**

- · High protection ability against EMI
- · Circular lens for improved reception characteristics
- · Available for various carrier frequencies
- · Min burst length: 8 cycles
- · Min gap length: 12 cycles
- · Low operating voltage and low power consumption
- · High immunity against ambient light
- · High immunity against TFT and PDP backlight
- · Long reception range
- · High sensitivity
- · Pb free and RoHS compliant



### **Description**

The IRM-36xxM2F32devices are DIP type infrared receivers which have been developed and designed by using the latest IC technology.

The PIN diode and preamplifier are assembled onto a lead frame and molded into a black epoxy package which operates as an IR filter. The demodulated output signal can directly be decoded by a microprocessor.

#### Pin Configuration

- 1. OUT
- 2. GND
- 3. V<sub>CC</sub>


#### **Applications**

- AV equipment such as TV, VCR, DVD, CD, MD, etc.
- CATV set top boxes
- Multi-media Equipment
- · Other devices using IR remote control

## **Application Circuit**

## 

#### **Block Diagram**



The RC Filter must be connected as close as possible to Vcc and GND pins.




# IRM-36xxM2F32series

#### **Parts Table**

Model No.	Carrier Frequency
IRM-3636M2F32	36 kHz
IRM-3638M2F32	38 kHz
IRM-3640M2F32	40 kHz

## **Package Dimensions**

(Dimensions in mm)





# IRM-36xxM2F32series

## Absolute Maximum Ratings (T<sub>a</sub>=25 °C)

Parameter	Symbol	Rating	Unit
Supply Voltage	Vcc	6	V
Operating Temperature	Topr	-20 ~ +80	$^{\circ}$ C
Storage Temperature	Tstg	-40 ~ +85	$^{\circ}$ C
Soldering Temperature *1	Tsol	260	$^{\circ}$ C

 $<sup>^{\</sup>star 1}$  4mm from mold body for less than 10 seconds

# Electro-Optical Characteristics (Ta=25°C, Vcc=3V)

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Condition
Current consumption	Icc		0.4	0.6	mA	No input signal
Supply voltage	V <sub>CC</sub>	2.7	1	5.5	V	
Peak wavelength	$\lambda_{p}$		940		nm	
5	L <sub>0</sub>	14			m	
Reception range	L <sub>45</sub>	6			111	See chapter
Half angle(horizontal)	$\phi_{h}$		±35		deg	,Test method'
Half angle(vertical)	φν		±35		deg	
High level pulse width	T <sub>H</sub>	450		750	μs	Test signal according to
Low level pulse width	TL	450		750	μs	figure 1
High level output voltage	V <sub>OH</sub>	Vcc-0.4			V	
Low level output voltage	V <sub>OL</sub>		0.2	0.5	V	I <sub>SINK</sub> ≦2mA
Internal pull up resistor	R <sub>PU</sub>	34	40	46	kΩ	



## IRM-36xxM2F32series

#### **Test method**

The specified electro-optical characteristics are valid under the following conditions.

- 1. Measurement environment
  - A place without extreme light reflections.
- 2. External light

The environment contains an ordinary, white fluorescent lamp without high frequency modulation. The color temperature is 2856K and the illumination at the IR receiver is less than 10 Lux ( $Ev \le 10Lux$ ).

- 3. Standard transmitter
  - The test transmitter is calibrated by using the circuit shown in figure 2. The radiation intensity of the transmitter is adjusted until **Vo=400mVp-p.** Both, the test transmitter and the photo diode, have a peak wavelength of 940nm. The photo diode for calibration is PD438B (λp=940nm, Vr=5V).
- 4. The measurement system is shown in Fig.-3

Fig.-1 Transmitter Wave Form

D.U.T output Pulse




Fig.-2 standard transmitter calibration






Fig.-3 Measuring System





# IRM-36xxM2F32series

## **Typical Electro-Optical Characteristic Curves**



Ver.:1




# IRM-36xxM2F32series

#### **Code information**

Protocol	Suitable	Protocol	Suitable	
JVC	Yes	RCA	No	
Matsushita	Yes	Sharp	Yes	
Mitsubishi	No	Sony 12 Bit	Yes	
NEC	Yes	Sony 15 Bit	No	
RC5	Yes	Sony 20Bit	No	
RC6	Yes	Toshiba	Yes	
RCMM	No	Zenith	Yes	
RCS-80	No	Continuous Code	No	

## **Device Marking**



#### **Notes**

- 1 denotes Year code
- denotes Month code
- 3 denotes Device number
- denotes Carrier frequency

狀態:Approved(正式發行)



# IRM-36xxM2F32series

## **Packing Quantity**

1500 pcs / Box 10 Boxes / Carton

#### **DISCLAIMER**

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 3. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without the specific consent of EVERLIGHT.