



江苏华能电子有限公司

JIANGSU HUANENG ELECTRONICS CO., LTD.

CUSTOMER:

MODEL NO.: MLT-8540H

OUR PART NO ..:

CUSTOMER PART NO .:

CUSTOMER	APPROVED	CHECKED
	Zhangchanghua	Yangshuyin


Add: Chenbao Industrial Park, Chenbao Town, Xinghua, Taizhou City, Jiangsu China. 江苏省兴化市陈堡镇工业园区 Tel:+86-523-83710666 Fax:+86-523-83724866 Email: hn@huawha.com; http://www.huawha.com



Chenbao Industrial Park, Chenbao Town, Xinghua,Taizhou City,China. Jiangsu China. Tel:+86-523-83710666 Fax:+86-523-83724866 Email: hn@huawha.com: http://www.huawha.com

			Linaii. Iii@iuawiia.com, iiup.//www.iuawiia.com		
Specification for Electro-Magnetic Buzzer (SMD Type)				Page 2 of 5	
			Des.	Chk.	
Model No.:	Model No.: MLT-8540H	Part No.			
	Part No.		5/22/2017	5/22/2017	


1. Technical Parameter **Measuring condition** Part shall be measured under a condition (Temperature: $5 \sim 35^{\circ}$ C, Humidity: $45\% \sim 85\%$ R.H., Atmospheric pressure: 860 \sim 1060hPa) unless the standard condition (Temperature: 25±3°C, Humidity: $60\pm10\%$ R.H. Atmospheric pressure: $860 \sim 1060$ hPa) is regulated to measure. 1 Rated Voltage 3.6 Vo-p 2 **Operating Voltage** 2.5~4.5Vo-p 3 Rated Current Max.100mA 4 Min. 85dB Sound Output at 10cm $16\pm 3\Omega$ 5 Coil Resistance 6 2700Hz **Resonant Frequency** 7 **Operating Temperature** -20°C~+70°C 8 Store Temperature -30°C∼+85°C



2. Dimensions

HNDZ

Unit: mm



*Unit: mm; Tolerance: ± 0.3mm Except Specified *Housing Material: Black LCP *Terminal plate: 3 soldering pads, tin Plating Brass




Chenbao Industrial Park, Chenbao Town, Xinghua,Taizhou City,China. Jiangsu China. Tel:+86-523-83710666 Fax:+86-523-83724866 Email: hn@huawha.com; http://www.huawha.com

Specification for Electro-Magnetic Buzzer (SMD Type)		Des.	Page 3 of 5 Chk.		
Model No.:	MLT-8540H	Part No.		5/22/2017	5/22/2017


Recommended Setting

3. Electrical And Acoustical Measuring Condition


Recommended Driving Circuit



Resonant frequency, 1/2 duty cycle. Square wave. Signal amplitude should be large enough tosaturate the transistor.



4. Frequency Response





Chenbao Industrial Park, Chenbao Town, Xinghua, Taizhou City, China. Jiangsu China. Tel:+86-523-83710666 Fax:+86-523-83724866


Email: hn@huawha.com; http://www.huawha.com

Specification for Electro-Magnetic Buzzer (SMD Type)		Des.	Page 4 of 5 Chk.		
Model No.:	MLT-8540H	Part No.		5/22/2017	5/22/2017

5. Surface mounting condition

5.1 Reflow soldering

Recommendable reflow soldering condition is as follows.



Note: (1) In automated mounting of the SMD sound transducers on PCB, any bending, expanding and pulling forces or shocks against the SMD sound transducers shall be kept minimum to prevent them from electrical failures and mechanical damages of the devices. (2) In the reflow soldering, too high soldering temperatures and too large temperature Gradient such as rapid heating or cooling may cause electrical failures and mechanical damages of the devices.



江苏华能电子有限公司

JIANG SU HUANENG ELECTRONICS CO.,LTD

Specification for Electro-Magnetic Buzzer				Page 5 of 5
(SMD Type)			Des.	Chk.
Model No.:		Part No.		
Model No.: MLT-8540H	Part NO.	5/22/2017	5/22/2017	

6. Reliability Test

After any following tests the part shall meet specifications without any degradation in appearance and performance except SPL. SPL shall not deviate more than -10 dB from the initial value

6.1 Ordinary Temperature Life Test

The part shall be subjected to 96 hours at $25\pm10^{\circ}$ C. Input rated voltage Resonant frequency, 1/2 duty Square wave.

6.2 High Temperature Test

The part shall be capable of with standing a storage temperature of $+80^{\circ}$ C for 96 hours.

6.3 Low Temperature Test

The part shall be capable of with standing a storage temperature of -30 $^\circ\!\mathrm{C}$ for 96 hours.

6.4 Humidity Test

Temperature:+40 $^\circ\!C\pm3\,^\circ\!C$ Relative Humidity:90% \sim 95% Duration: 48 hours and expose to room temperature for 6 hours

6.5 Temperature Shock Test

Temperature:60 °C /1hour→ 25 °C/3hours→-20 °C/1hour→ 25 °C/3hours (1cycle) Total cycle: 10 cycles

6.6 Drop Test

Standard Packaging From 75cm(Drop on hard wood or board of 5cm thick, three sides, six plain.)

6.7 Vibration Test

Vibration:1000cycles /min. Amplitude:1.5mm, Duration: 1 hour in each 3 axes

6.8 Reflow Test

Use recommendable reflow soldering condition (as shown in 5.1)

(1) No abnormality should be found after reflow

(2) Good soldering to meet soldering requirements

Note:

As this product is not protected from foreign material entering, please make sure that any foreign materials (e.g. magnetic powder, washing solvent, flux, corrosive gas) do not enter this product in your production processes. The functional degradation (e.g. SPL down) may occur if foreign material enter it.