

Technical Data Sheet

0603 Package Chip LED(0.4mm Height)

19-217/Y5C-AM1N1VY/3T

Features

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb-free
- The product itself will remain with in RoHS compliant Version.

Descriptions

- The 19-217 SMD LED is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- Backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

Device Selection Guide


Part No.	Chip	Emitted Color	Resin Color	
Fart No.	Material	Emitted Color		
19-217/Y5C-AM1N1VY/3T	AlGaInP	Brilliant Yellow	Water Clear	






19-217/Y5C-AM1N1VY/3T

Package Outline Dimensions







<u>19-217/Y5C-AM1N1VY/3T</u>

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit
Reverse Voltage	V _R	5	V
Forward Current	$I_{\rm F}$	25	mA
Peak Forward Current (Duty 1/10 @1KHz)	$I_{\rm FP}$	60	mA
Power Dissipation	P _d	60	mW
Electrostatic Discharge(HBM)	ESD	2000	V
Operating Temperature	Topr	-40 ~ +85	°C
Storage Temperature	Tstg	-40 ~ +90	°C
Soldering Temperature	Tsol	Reflow Soldering : 260 $^{\circ}$ C for 10 sec. Hand Soldering : 350 $^{\circ}$ C for 3 sec.	

Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition	
Luminous Intensity	Iv	16.0		40	mcd		
Viewing Angle	2 heta 1/2		120		deg		
Peak Wavelength	λp		591		nm	I _F =5mA	
Dominant Wavelength	λd	585.0		595.0	nm		
Spectrum Radiation Bandwidth	$\bigtriangleup \lambda$		15		nm		
Forward Voltage	V_{F}	1.65		2.25	V		
Reverse Current	I _R			10	μA	V _R =5V	



<u>19-217/Y5C-AM1N1VY/3T</u>

Bin Range Of Dom. Wavelength

Group	Bin	Min	Max	Unit	Condition	
	D3	585.0	589.0			
Α	D4	588.0	592.0	nm	I _F =5mA	
	D5	591.0	595.0			

Bin Range Of Luminous Intensity

Bin	Min	Max	Unit	Condition
M1	16.0	25.0		
M2	20.0	32.0	mcd	I _F =5mA
N1	25.0	40.0		


Bin Range Of Forward Voltage

Group	Bin	Min	Max	Unit	Condition
	19	1.65	1.85		
	20	1.75	1.95		
v	21	1.85	2.05	V	$I_F = 5mA$
	22	1.95	2.15		
	23	2.05	2.25		



19-217/Y5C-AM1N1VY/3T

Typical Electro-Optical Characteristics Curves




Everlight Electronics Co., Ltd. Device No: DSE-0001534 http://www.everlight.com Prepared date:18-May-2009 Rev 1 Page: 5 of 10 Prepared by:Xie Haitao




<u>19-217/Y5C-AM1N1VY/3T</u>

Label explanation

- **CAT: Luminous Intensity Rank**
- HUE: Dom. Wavelength Rank
- **REF: Forward Voltage Rank**



Reel Dimensions




Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

http://www.everlight.com Prepared date:18-May-2009




<u>19-217/Y5C-AM1N1VY/3T</u>

Carrier Tape Dimensions: Loaded quantity 3000 PCS per reel



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Moisture Resistant Packaging





<u>19-217/Y5C-AM1N1VY/3T</u>

Reliability Test Items And Conditions

The reliability of products shall be satisfied with items listed below.

Confidence level : 90%

LTPD: 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp. : 260°C±5°C Min. 5sec.	6 Min.	22 PCS.	0/1
2	Temperature Cycle	H : +100°C 15min ∫ 5 min L : -40°C 15min	300 Cycles	22 PCS.	0/1
3	Thermal Shock	H: +100°C 5min $\int 10 \sec$ L: -10°C 5min	300 Cycles	22 PCS.	0/1
4	High Temperature Storage	Temp. : 100°C	1000 Hrs.	22 PCS.	0/1
5	Low Temperature Storage	Temp. : -40°C	1000 Hrs.	22 PCS.	0/1
6	DC Operating Life	$I_F = 20 \text{ mA}$	1000 Hrs.	22 PCS.	0/1
7	High Temperature / High Humidity	85°C/85% RH	1000 Hrs.	22 PCS.	0/1




<u>19-217/Y5C-AM1N1VY/3T</u>

Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package: The LEDs should be kept at 30° C or less and 90% RH or less.
- 2.3 After opening the package: The LED's floor life is 1 year under 30℃ or less and 60% RH or less. If unused LEDs remain, it should be stored in moisture proof packages.
- 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.
 Baking treatment : 60±5°C for 24 hours.
- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.




<u>19-217/Y5C-AM1N1VY/3T</u>

4.Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350° C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



EVERLIGHT ELECTRONICS CO., LTD.	Tel: 886-2-2267-2000, 2267-9936
Office: No 25, Lane 76, Sec 3, Chung Yang Rd,	Fax: 886-2267-6244, 2267-6189, 2267-6306
Tucheng, Taipei 236, Taiwan, R.O.C	http://www.everlight.com