Linear Single Cell Li-Ion Battery Charger IC


General Description

The RT9513 is a fully integrated low cost single-cell Lilon battery charger IC ideal for portable applications. The RT9513 is capable of being powered up from AC adapter. The RT9513 enters sleep mode when AC adapter is removed.

The RT9513 optimizes the charging task by using a control algorithm including preconditioning mode, fast charge mode and constant voltage mode. The charging task is terminated as the charge current drops below the preset threshold. The AC adapter charge current can be programmed up to 1A with an external resister. The internal thermal feedback circuitry regulates the die temperature to optimize the charge rate for all ambient temperatures.

The RT9513 features 18V maximum rating voltages for AC adapter. The other features are under voltage protection, over voltage protection for AC adapter supply.

Ordering Information



Note:

Richtek products are:

- ▶ RoHS compliant and compatible with the current requirements of IPC/JEDEC J-STD-020.
- ▶ Suitable for use in SnPb or Pb-free soldering processes.


Features

- 18V Maximum Rating for AC Adapter
- Internal Integrate P-MOSFETs
- AC Adapter Power Good Status Indicator
- Charge Status Indicator
- Under Voltage Protection
- Over Voltage Protection
- Automatic Recharge Feature
- Small 10-Lead WDFN Package
- Thermal Feedback Optimizing Charge Rate
- RoHS Compliant and Halogen Free

Applications

- Digital Cameras
- Cellular Phones
- Personal Data Assistants (PDAs)
- MP3 Players
- Hand Held PCs

Pin Configurations




WDFN-10L 3x3

Marking Information

For marking information, contact our sales representative directly or through a Richtek distributor located in your area.

Typical Application Circuit






Functional Pin Description


Pin No.	Pin Name	Pin Function		
1	ACIN	Wall Adaptor Charge Input Supply.		
2, 7, 9	NC	No Internal Connection.		
3	CHG_S	Charge Status Indicator Output (open drain).		
4	PGOOD	Power Good Indicator Output (open drain).		
5	GND	Ground.		
6	ISETA	Wall Adaptor Supply Charge Current Set Point.		
8	EN	Charge Enable Input (active low).		
10	BATT	Battery Charge Current Output.		
I Exposed Pad (11) IGND		Ground. The exposed pad must be soldered to a large PCB and connected to GND for maximum power dissipation.		

Function Block Diagram





Table





Absolute Maximum Ratings (Note 1)

• AC Input Voltage	0.3V to 18V
• EN Input Voltage	0.3V to 6V
• Output Current	- 1.2A
 Power Dissipation, P_D @ T_A = 25°C 	
WDFN-10L 3x3	- 0.926W
Package Thermal Resistance (Note 2)	
WDFN-10L 3x3, θ_{JA}	- 108°C/W
WDFN-10L 3x3, θ_{JC}	- 8.2°C/W
• Lead Temperature (Soldering, 10 sec.)	
• Junction Temperature	- 150°C
Storage Temperature Range	- −65°C to 150°C
• ESD Susceptibility (Note 3)	
HBM (Human Body Mode)	- 2kV
MM (Machine Mode)	- 200V
Recommended Operating Conditions (Note 4)	
Junction Temperature Range	40°C to 125°C
Ambient Temperature Range	40°C to 85°C

Electrical Characteristics

(ACIN = 5V, $T_A = 27$ °C, Unless Otherwise specification)

Parameter	Symbol	Test Conditions	Min	Тур	Мах	Units	
Supply Input							
ACIN Input Voltage Range	VACIN		4.5		6	V	
ACIN UVP Rising Threshold Voltage	V _{UV_HIGH}			4.4	4.5	V	
ACIN UVP Hysteresis	Vuv_Low		50	80	120	mV	
ACIN Standby Current	I _{STBY}	$V_{BATT} = 4.5V$	-	300	500	μА	
ACIN Shutdown Current	ISHDN	V _{EN} = HIGH		50	100	μА	
ACIN UVP Current	I _{UVP}	V _{ACIN} = 4V, V _{BATT} = 3V		150	250	μΑ	
BATT Sleep Leakage Current	ISLEEP	V _{ACIN} = 4V, V _{BATT} = 4.5V			10	μА	
Voltage Regulation							
BATT Regulation Voltage	V_{REG}	$I_{BATT} = 60 \text{mA}$	4.158	4.2	4.242	V	
Regulation Voltage Accuracy			-1		+1	%	
ACIN MOSFET	R _{DS(ON)_ACIN}	$I_{BATT} = 500 \text{mA}$		600		mΩ	
Current Regulation							
ISETA Set Voltage (Fast Charge Phase)	VISETA	V _{BATT} = 3.5 V	2.45	2.5	2.55	V	
Full Charge Setting Range	I _{CHG_AC}		100		1200	mA	
AC Charge Current accuracy	I _{CHG_AC}	$V_{BATT} = 3.8 \text{ V}, R_{ISET} = 1.5 \text{ k}\Omega$		500		mA	

To be continued





Pa	rameter	Symbol	Test Conditions	Min	Тур	Max	Units
Precharge	Precharge						
BATT Pre-Char	rge Rising Threshold	VPRECH		2.6	2.8	3	V
BATT Pre-Charge Threshold Hysteresis		ΔV _{PRECH}		50	100	200	mV
Pre-Charge Cu	irrent	I _{PCHG}	V _{BATT} = 2V	8	10	12	%
Recharge Thre	eshold						
BATT Re-Charge Falling Threshold Hysteresis		∆V _{RECH_L}	V _{REG} – V _{BATT}	60	100	150	mV
Charge Termi	nation Detection						
Termination Current Ratio (default)		I _{TERM}	V _{BATT} = 4.2V		10		%
Logic Input/O	utput			·			
CHG_S Pull Down Voltage		V CHG_S	TBD, ICHG_S = 5mA		65		mV
PGOOD Pull Down Voltage		V _{PGOOD}	TBD, $I_{\overline{PGOOD}} = 5mA$		220		m۷
EN Threshold	Logic-High Voltage	V _{IH}		1.5			V
	Logic-Low Voltage	VIL				0.4	V
EN Pin Input Current		t _{EN}	√ <u>EN</u> = 2 V			2	μА
Protection			•	•			-
Thermal Regulation					125		°C
OVP SET			Internal Default		6.5		V


- **Note 1.** Stresses listed as the above "Absolute Maximum Ratings" may cause permanent damage to the device. These are for stress ratings. Functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may remain possibility to affect device reliability.
- Note 2. θ_{JA} is measured in the natural convection at $T_A = 25$ °C on a high effective thermal conductivity test board (4 layers, 1S) of JEDEC 51-7 thermal measurement standard. The case point of θ_{JC} is on the expose pad for the package.
- Note 3. Devices are ESD sensitive. Handling precaution is recommended.
- Note 4. The device is not guaranteed to function outside its operating conditions.





Typical Operating Characteristics
















Application Information

Automatically Power Source Selection

The RT9513 is a battery charger IC which is designed for Li-ion Battery with 4.2V rated voltage.

AC Mode: When the AC input voltage (ACIN) is higher than the UVP voltage level (4.4V), the RT9513 will enter AC Mode. In the AC Mode, ACIN P-MOSFET is turned on and USB P-MOSFET is turned off.

Sleep Mode: The RT9513 will enter Sleep Mode when AC input voltage are removed. This feature provides low leakage current from the battery during the absence of input supply.

ACIN Over Voltage Protection

The AC input voltage is monitored by an internal OVP comparator. The comparator has an accurate reference of 2.5V from the band-gap reference. The OVP threshold is set by the internal resistive. The protection threshold is set to 6.5V. When the input voltage exceeds the threshold, the comparator outputs a logic signal to turn off the power P-MOSFET to prevent the high input voltage from damaging the electronics in the handheld system. When the input over oltage condition is removed (ACIN < 6V), the comparator re-enables the output by running through the soft-start.




Figure 1. AC Mode Charge Current Setting

Fast-Charge Current Setting

The RT9513 offers ISETA pin to determine the AC charge rate from 100mA to 1.2A. The charge current can be calculated as following equation.

$$I_{charge_ac} = K_{SET} \frac{V_{SET}}{R_{SETA}}$$

The parameter K_{SET} = 300 ; V_{SET} = 2.5V. R_{SETA} is the resistor connected between the ISETA and GND.

Pre- Charge Current Setting

During a charge cycle if the battery voltage is below the VPRECH threshold, the RT9513 applies a pre-charge mode to the battery. This feature revives deeply discharged cells and protects battery life. The RT9513 internal determines the pre-charge rate as 10% of the fast-charge current.

Battery Voltage Regulation

The RT9513 monitors the battery voltage through the BATT pin. Once the battery voltage level closes to the VREG threshold, the RT9513 voltage enters constant phase and the charging current begins to taper down. When battery voltage is over the VREG threshold, the RT9513 will stop charge and keep to monitor the battery voltage. However, when the battery voltage decreases 100mV below the V_{REG} , it will be recharged to keep the battery voltage.

Charge Status Outputs

The open-drain CHG_S and PGOOD outputs indicate various charger operations as shown in the following table.

These status pins can be used to drive LEDs or communicate to the host processor. Note that ON indicates the open-drain transistor is turned on and LED is bright.

Charge State		CHG_S	PGOOD	
ACIN	Charge	ON	ON	
	Charge done	OFF	ON	



Temperature Regulation and Thermal Protection

In order to maximize the charge rate, the RT9513 features a junction temperature regulation loop. If the power dissipation of the IC results in a junction temperature greater than the thermal regulation threshold (125°C), the RT9513 throttles back on the charge current in order to maintain a junction temperature around the thermal regulation threshold (125°C). The RT9513 monitors the junction temperature, T_J, of the die and disconnects the battery from the input if T_J exceeds 125°C. This operation continues until junction temperature falls below thermal regulation threshold (125°C) by the hysteresis level. This feature prevents the chip from damage.

Selecting the Input and Output Capacitors

In most applications, the most important is the high-frequency decoupling capacitor on the input of the RT9513. A 1uF ceramic capacitor, placed in close proximity to input pin and GND pin is recommended. In some applications depending on the power supply characteristics and cable length, it may be necessary to add an additional 10uF ceramic capacitor to the input. The RT9513 requires a small output capacitor for loop stability. A 1uF ceramic capacitor placed between the BATT pin and GND is typically sufficient.

Layout Consideration

The RT9513 is a fully integrated low cost single-cell Li- Ion battery charger ideal for portable applications. Careful PCB layout is necessary. For best performance, place all peripheral components as close to the IC as possible. A short connection is highly recommended. The following guidelines should be strictly followed when designing a PCB layout for the RT9513.

- ▶ Input capacitor should be placed close to IC and connected to ground plane. The trace of input in the PCB should be placed far away the sensitive devices or shielded by the ground.
- ▶ The GND should be connected to a strong ground plane for heat sinking and noise protection.
- ▶ The connection of R_{SETA} should be isolated from other noisy traces. The short wire is recommended to prevent EMI and noise coupling.
- ▶ Output capacitor should be placed close to IC and connected to ground plane to reduce noise coupling.






Figure 2



Outline Dimension





DETAIL APin #1 ID and Tie Bar Mark Options

:: The configuration of the Pin #1 identifier is optional, but must be located within the zone indicated.

Symbol	Dimensions I	In Millimeters	Dimensions In Inches		
	Min	Max	Min	Max	
А	0.700	0.800	0.028	0.031	
A1	0.000	0.050	0.000	0.002	
А3	0.175	0.250	0.007	0.010	
b	0.180	0.300	0.007	0.012	
D	2.950	3.050	0.116	0.120	
D2	2.300	2.650	0.091	0.104	
Е	2.950	3.050	0.116	0.120	
E2	1.500	1.750	0.059	0.069	
е	0.5	500	0.0)20	
L	0.350	0.450	0.014	0.018	

W-Type 10L DFN 3x3 Package

Richtek Technology Corporation

Headquarter

5F, No. 20, Taiyuen Street, Chupei City

Hsinchu, Taiwan, R.O.C.

Tel: (8863)5526789 Fax: (8863)5526611

Richtek Technology Corporation

Taipei Office (Marketing)

5F, No. 95, Minchiuan Road, Hsintien City

Taipei County, Taiwan, R.O.C.

Tel: (8862)86672399 Fax: (8862)86672377

Email: marketing@richtek.com

Information that is provided by Richtek Technology Corporation is believed to be accurate and reliable. Richtek reserves the right to make any change in circuit design, specification or other related things if necessary without notice at any time. No third party intellectual property infringement of the applications should be guaranteed by users when integrating Richtek products into any application. No legal responsibility for any said applications is assumed by Richtek.