
APPROVAL SHEET

Customer Name	:		
Customer P/N	:		
Frequency	:	26.000000	MHz
Aker Approved P/	N:	CXA-026000-3FCF2	20
Aker MPN	:	CXA-026000-3FCF	20
Rev.	:	1	
ISSUE DATE	:	Nov.26.2019	



AKER TECHNOLOGY CO., LTD.

ADDRESS : NO 11-3, Jianguo Rd., T.E.P.Z , Tanzi Dist., Taichung City 427, Taiwan.

TEL: 886-4-25335978 FAX: 886-4-25336011

Web: www.aker.com.tw

RoHS compliant

	CUST. P/N	:		
	Aker Approved P/N	:	CXA-02600	0-3FCF20
Accurate Kinetic Energy	APPROVED	:	Xtal	SHEET : 1 of 9
	PREPARED	:	Sandy	REV. : 1

Rev.	Date	Reviser	Revise contents
1	2019/11/26	Sandy	Initial Released



CUST. P/N	:		
Aker Approved P/N	:	CXA-02600	0-3FCF20
APPROVED	:	Xtal	SHEET : 2 of 9
PREPARED	:	Sandy	REV. : 1

SMD CRYSTAL SPECIFICATION

1. ELECTRICAL CHARACTERISTICS

■ Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions for making measurement and tests are as follow :

Ambient temperature : 25 ± 5 °C

Relative humidity : 40%~70%

If there is any doubt about the results, measurement shall be made within the following limits:

Ambient temperature : 25 ± 3 °C

Relative humidity : 40%~70%


- AKER Model : CXA-321
- Oscillation Model : Fundamental
- Cutting Model : AT CUT
- Measurement Equipment : 350A(Measured FL)
- Insulation Resistance : More than 500M ohms at DC 100V

		Electrical Spec				
Parameters	Symbol	Min.	Тур.	Max.	Units.	Notes
Nominal Frequency	FL	2	6.00000	0	MHz	
Frequency Tolerance			±10		ppm	at 25°C \pm 3°C
Frequency Stability			±10		ppm	Operating Temp (Refer 25°C)
Load Capacitance	CL		8		pF	
Aging			±3		ppm	First Year
Operating Temperature		-20	\sim	70	°C	
Storage Temperature Range		-55	\sim	125	°C	
Drive Level	DL			100	uW	
Effective Resistance Rr	Rr			60	Ω	
Shunt Capacitance	C0			5	pF	
Please kindly be noted that AK	ER DO NOT	guarante	ee parts q	uality wh	ich involv	ves human security application.



CUST. P/N :		
Aker Approved P/N :	CXA-02600	0-3FCF20
APPROVED :	Xtal	SHEET : 3 of 9
PREPARED :	Sandy	REV. : 1

2. MARKING :



Year/Month Code : Please make refer to following tables.


AKER LOGO. → Production line code

NOTE 1 :


CODE	CL	CODE	CL	CODE	CL	CODE	CL
0	0pF	9	14pF	K	9.5pF	U	8.5pF
1	16pF	A	32 pF	L	19.5pF	V	24pF
2	22pF	В	27pF	М	21.5pF	W	4pF
3	15pF	C	8pF	N	33pF	X	39pF
4	20 pF	D	37pF	P	7pF	Y	26pF
5	30pF	E	25 pF	Q	15.5pF	Ζ	7.2pF
6	18pF	F	35pF	R	12.5pF	а	17pF
7	12pF	G	13pF	5	11pF	b	9.85pF
8	10 pF	H	9pF	Т	брF	đ	ĴрF

Year	2019	2020	2021	2022
rear	2023	2024	2025	2026
	2027	2028	2029	2030
Month	2031	2032	2033	2034
Wohn	2035	2036	2037	2038
JAN	Α	Ν	а	n
FEB	В	Р	b	р
MAR	С	Q	с	q
APR	D	R	d	r
MAY	E	s	е	S
JUN	F	Т	f	t
JUL	G	U	g	u
AUG	Н	V	h	v
SEP	J	W	j	w
OCT	K	Х	k	х
NOV	L	Y	1	у
DEC	М	Z	m	z

3. DIMENSION :









<SIDE>

(Unit:mm)




<SUGGESTED LAYOUT>





CUST. P/N	:		
Aker Approved P/N	:	CXA-02600	0-3FCF20
APPROVED	:	Xtal	SHEET: 4 of 9
PREPARED	:	Sandy	REV. : 1


4. STRUCTURE ILLUSTRATION




	COMPONENTS	MATERIALS		MPONENTS	MATERIALS
А	Base (Package)	Ceramic(Al2O3)+Kovar(Fe/Co/Ni)	D	Electrode	Cr / Ag
В	Conductive adhesive	Ag / Silicon resin	E	Lid	Fe/Co/Ni
С	Crystal blank	SiO2			

	CUST. P/N	:		
	Aker Approved P/N	:	CXA-02600	0-3FCF20
	APPROVED	:	Xtal	SHEET : 5 of 9
Accurate Kinetic Energy	PREPARED	:	Sandy	REV . : 1


5. PACKING : TAPE SPECIFICATION







OUTLINE DIMENSION

(Unit:mm)









CUST. P/N	:		
Aker Approved P/N	:	CXA-02600	0-3FCF20
APPROVED	:	Xtal	SHEET : 8 of 9
PREPARED	:	Sandy	REV. : 1

0 MECHANICAL PERFORMANCE

9. MECHANICAL PERFORMANCE					
TEST ITEMS	TEST METHODS AND TEST CONDITION	PERFORMANCE			
9.1 Drop Test	The specimen is measured for its frequency and resistance before the test. It is then dropped from a hight of 100 cm or more as a free fall object onto a hard wooden plate of 30mm or more in thickness. (in accordance with JIS-C0044)				
9.2 Vibration Test	The specimen is measured for its frequency and resistance before the test. Most them into X,Y and Z axes, respectively, for the vibration test. Vibration condition: Frequency range ; $20 \ 2000$ HZ Peak to peak amplitude : 1.52 mm Peak acceleration : $20G$ Sweep time : 20 minute / axis Pendicular total test time : 4 hours (in accordance with MIL STD 882E : 2007.3)	To satisfy the electrical performance .			
9.3 Resistance to Soldering Test	(in accordance with MIL-STD-883F : 2007.3) The specimen is measured for its frequency and resistance before the test. Place the specimen on the belt of the converynace and let it pass through the reflow with the presetted temperature condition. After passing twice the reflow place, the specimen under the referee condition for -~2 hours and then measure its electrical performance. Temperature Condition of IR Simulation: The temperature range of the preheated section is setted at 150 $^{\sim}$ 180°C for 60~120 sec. For the next section the temperature range is setted at 217~260°C for 45~90 sec. and within this time range the specimen should be able to sustain at the peak temperature, 260+/-3°C , for 10 sec long. (in accordance with JESD22-B106-B)				
9.4 Fine Leak Test	Place the specimen in a pressurized container and pressurize it with the detection gas (mixed gas consisting of 95% or more helium) for at least 2 hours. Complete the measurement of the concentration of helium within 30 min after taking it out from the pressurized container. (in accordance with MIL-STD-883F: 1014.11) The referee condition.	Less than 1.0 * 10 ⁻⁸ atm .c.c. / sec, Helium			
	Temperature $25 \pm 2 \degree$ Humidity $44 \degree 55 \%$ Pressure $86 \degree 106 \text{ kPa}$ (in accordance with MIL-STD-883E : 1014. 9)				



CUST. P/N	:		
Aker Approved P/N	:	CXA-02600	0-3FCF20
APPROVED	:	Xtal	SHEET : 9 of 9
PREPARED	:	Sandy	REV. : 1

10. CLIMATIC RESISTANCE

IU. CLIVIATIC RESISTANCE					
TEST ITEMS	TEST METHODS AND TEST CONDITION	PERFORMANCE			
10.1 Low Temp Exposure Test	The specimen is measured for its frequency and resistance before the test . Place the specimen in the chamber and kept it at the temperature of $-40 \pm 3^{\circ}$ C for 168 ± 6 hours . Take the specimen out of the chamber and measure itselectrical performance after leaving 1 ~ 2 hours under the referee condition. (in accordance with JIS-C0020)				
10.2 Aging Test	The specimen is measured for its frequency and resistance before the test . Place the specimen in the testing chamber and keep it at the temperature of $+ 125 \pm 3^{\circ}$ C for 720 ± 48 hours. And then take the specimen out of the chamber and measure its electrical performance after leaving for $1 \ 2$ hours under the referee condition . (in accordance with JIS-C0021)	To satisfy the electrical performance .			
10.3 High Temperature & High Humidty	The specimen is measured for its frequency and resistance before the test . Place the specimen in the testing chamber and kept it at the temperature of $+ 85 \pm 5$ °C and humidity of 85 ± 5 % for 168 ± 6 hours.and then take the specimen out and measure its electrical performance after leaving for 1 ~ 2 hours under the referee condition. (in accordance with MIL-STD-883F : 1004.7)				
10.4 Temperature Cycle Test	The specimen is measured for its frequency and resistance before the test . Subject the specimen to the 100 cycles of temperature ranges stated below . High temp . + 125 ± 3 °C (15± 3 min). $2\sim3 \text{ min.}$ $2\sim3 \text{ min.}$ Low temp55 ± 3 °C (15± 3 min). Measure its electrical performance after leaving it for 1 ~ 2 hours under the referee condition . (in accordance with MIL-STD-883F : 1010.8)				