
APPROVAL SHEET

Customer Name	•				
Customer P/N	•				
Frequency	: 4.000000	MHz			
Aker Approved P/N	: SMA-004000-5BL4T2				
Aker MPN	: SMA-004000-5BL4T2				
Rev.	:1				
ISSUE DATE	: Jan.25.2019				



AKER TECHNOLOGY CO., LTD.

ADDRESS : NO 11-3, Jianguo Rd., T.E.P.Z , Tanzi Dist., Taichung City 427, Taiwan.

TEL: 886-4-25335978 FAX: 886-4-25336011

Web: www.aker.com.tw

RoHS compliant



CUST. P/N	:		
Aker Approved P/N	:	SMA-0040	00-5BL4T2
APPROVED	:	Tin	SHEET : 1 of 10
PREPARED	:	Kiku	REV. : 1

Initial Released
1
_



CUST. P/N	:		
Aker Approved P/N :		SMA-004000-5BL4T2	
APPROVED	:	Tin	SHEET : 2 of 10
PREPARED	•	Kiku	REV. : 1
	Aker Approved P/N APPROVED	Aker Approved P/N :APPROVED :	Aker Approved P/N :SMA-0040APPROVED :Tin

SMD CRYSTAL OSCILLATOR

1. ELECTRICAL CHARACTERISTICS

Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions for making measurement and tests are as follow :

Ambient temperature : 25 ± 5 °C

Relative humidity : 40%~70%

If there is any doubt about the results, measurement shall be made within the following limits:

Ambient temperature : 25±3 °C

Relative humidity : 40%~70%

AKER Model : SMA-531

• Cutting Model : AT CUT


]	Electrical Spec			
Parameters	Symbol	Min.	Тур.	Max.	Units.	Notes
Nominal Frequency		4	.000000)	MHz	
Frequency Stability			± 50		ppm	
Supply Voltage	Vdd	3	$.3 \pm 109$	%	V	
Output Load CMOS	CL		15		pF	
Aging			±3		ppm	First Year
Enable Control			Yes			Pad 1
Operating Temperature		-40	25	85	°C	
Storage Temperature Range		-55	~	125	°C	
Output Voltage High	VoH	2.97			V	
Output Voltage Low	VoL			0.33	V	
Input Current	Icc			7	mA	
Standby Current	Ist			10	μA	
Rise Time	Tr			10	ns	10%~90%VDD Level
Fall Time	Tf			10	ns	10%~90%VDD Level
Symmetry (Duty ratio)	TH/T	40	~	60	%	
Start-up Time	Tosc			10	ms	
Enable Voltage High	Vhi	70%Vdd			V	
Disable Voltage Low	Vlo			30%Vdd	V	
Output Enable Delay Time	T on			10	ms	
Output Disable Delay Time	T off			200	ns	

Please kindly be noted that AKER DO NOT guarantee parts quality which involves human security application.



	CLICE DAI					
	CUST. P/N	•				
	Aker Approved P/N	: SMA-004	-004000-5BL4T2			
	APPROVED	: Tin	SHEET : 3 of 10			
Accurate Kinetic Energy	PREPARED	PREPARED : Kiku				
2.C-MOS LOAD OUTH		Tr				
			VDD			
"1"Level			- 90% VDD			
			-			
			50% VDD			
"0"Level		/	=10% VDD			
			- GND			
TW	r					
	Т					
	I					

3.C-MOS LOAD TEST CIRCUIT




***Because SMA series has no by pass capacitor. So, we recommend our customer to use capacitor 0.01 μF in join Vcc and GND.



CUST. P/N	•		
Aker Approved I	P/N :	SMA-0	04000-5BL4T2
APPROVED	:	Tin	SHEET : 4 of 10
PREPARED	:	Kiku	REV. : 1

4. MARKING :



SEP

OCT

NOV

DEC

J

Κ

L

Μ

0.8~1.4V CMOS W Voltage Range CMOS

(UNIT:mm)

w

х

У

Z


5. DIMENSION :

Ζ

Enable / Disable Function

E/D(#1)	OUTPUT(#3)
HIGH (Open)	Operating
LOW	High impedance

PIN FUNCTION					
#1:Enable / Disable Control					
#2 : GND					
#3:OUTPUT					
#4:VDD					



W

Х

Y

Ζ

j

k

l


m

Bottom



	CUST. P/N	:		
	Aker Approved P/N	:	SMA-0040)00-5BL4T2
	APPROVED	:	Tin	SHEET : 5 of 10
	PREPARED	:	Kiku	REV. : 1
-				

6 . STRUCTURE ILLUSTRATION




	COMPONENTS	MATERIALS		MPONENTS	MATERIALS
A	Base (Package)	Ceramic (Al2O3)+Kovar (Fe/Co/Ni)	D	Crystal blank	SiO2
В	IC chip		E	Electrode	Cr / Ag
С	Conductive adhesive	Ag / Silicon resin	F	Lid	Fe/Co/Ni





CUST. P/N	:		
Aker Approved P/N	:	SMA-0040	000-5BL4T2
APPROVED	:	Tin	SHEET : 6 of 10
PREPARED	:	Kiku	REV. : 1

7. PACKING :

TAPE SPECIFICATION











OUTLINE DIMENSION

(Unit:mm)











CUST. P/N	:		
Aker Approved P/	N :	SMA-004	4000-5BL4T2
APPROVED	:	Tin	SHEET : 9 of 10
PREPARED	•	Kiku	REV. : 1

11 . MECHA	NICAL PERFORMANCE	
TEST ITEMS	TEST METHODS AND TEST CONDITION	PERFORMANCE
11.1 Drop Test	The specimen is measured for its frequency before the test. It is then dropped from a hight of 100 cm or more as a free fall object onto a hard wooden plate of 30mm or more in thickness. (in accordance with JIS-C0044)	
11.2 Vibration Test	 before the test. Most them into X,Y and Z axes, respectively, for the vibration test. Vibration condition: Frequency range ; 20 ~ 2000HZ Peak to peak amplitude : 1.52 mm Peak acceleration : 20G Sweep time : 20 minute / axis Pendicular total test time : 4 hours 	
11.3 Resistance to Soldering Test	 (in accordance with MIL-STD-883F : 2007.3) The specimen is measured for its frequency before the test. Place the specimen on the belt of the converynace and let it pass through the reflow with the presetted temperature condition. After passing twice the reflow place, the specimen under the referee condition for -~2 hours and then measure its electrical performance. Temperature Condition of IR Simulation: The temperature range of the preheated section is setted at 150 ~ 180°C for 60~120 sec. For the next section the temperature range is setted at 217~260°C for 45~90 sec. and within this time range the specimen should be able to sustain at the peak temperature, 260+/-3°C , for 10 sec long. (in accordance with JESD22-B106-B) 	
11.4 Fine Leak Test	Place the specimen in a pressurized container and pressurize it with the detection gas (mixed gas consisting of 95% or more helium) for at least 2 hours. Complete the measurement of the concentration of helium within 30 min after taking it out from the pressurized container. (in accordance with MIL-STD-883F : 1014.11) The referee condition . Temperature 25 ± 2 °C Humidity $44 \approx 55$ % Pressure $86 \approx 106$ kPa	Less than 1.0 * 10 ⁻⁸ atm .c.c. / sec, Helium
	(in accordance with MIL-STD-883E : 1014. 9)	



CUST. P/N	:		
Aker Approved P/N	:	SMA-0040)00-5BL4T2
APPROVED	:	Tin	SHEET : 10 of 10
PREPARED	:	Kiku	REV. : 1

12. CLIMATIC RESISTANCE

	TC REDISTANCE	
TEST ITEMS	TEST METHODS AND TEST CONDITION	PERFORMANCE
12.1 Low Temp Exposure Test	The specimen is measured for its frequency before the test . Place the specimen in the chamber and kept it at the temperature of $-40 \pm 3^{\circ}$ C for 168 ± 6 hours . Take the specimen out of the chamber and measure itselectrical performance after leaving 1 ~ 2 hours under the referee condition. (in accordance with JIS-C0020)	
12.2 Aging Test	The specimen is measured for its frequency before the test . Place the specimen in the testing chamber and keep it at the temperature of $+ 125 \pm 3^{\circ}$ C for 720 ± 48 hours. And then take the specimen out of the chamber and measure its electrical performance after leaving for 1 ~ 2 hours under the referee condition . (in accordance with JIS-C0021)	To satisfy the electrical performance .
12.3 High Temperature & High Humidty	The specimen is measured for its frequency before the test . Place the specimen in the testing chamber and kept it at the temperature of $+85 \pm 5$ °C and humidity of 85 ± 5 % for 168 ± 6 hours.and then take the specimen out and measure its electrical performance after leaving for 1 ~ 2 hours under the referee condition. (in accordance with MIL-STD-883F : 1004.7)	
12.4 Temperature Cycle Test	The specimen is measured for its frequency before the test . Subject the specimen to the 100 cycles of temperature ranges stated below . High temp $. + 125 \pm 3 \degree C$ (15 $\pm 3 \min$). $2 \sim 3 \min$. Low temp $55 \pm 3 \degree C$ (15 $\pm 3 \min$). Measure its electrical performance after leaving it for 1 ~ 2 hours under the referee condition . (in accordance with MIL-STD-883F : 1010.8)	