APPROVAL SHEET

 Customer
 Name
 :

 Customer
 P/N
 :

 Frequency
 : 40.000000
 MHz

 Aker Approved P/N
 : SMA-040000-5CL4T5

 Aker MPN
 : SMA-040000-5CL4T5

 Rev.
 : 1

 ISSUE DATE
 : Nov.15.2019

APPROVED	CHECKED	PREPARED
(in		Sandy
APPROVED BY CUS	TOMER	

AKER TECHNOLOGY CO., LTD.

ADDRESS: NO 11-3, Jianguo Rd., T.E.P.Z, Tanzi Dist., Taichung City 427, Taiwan.

TEL: 886-4-25335978 FAX: 886-4-25336011

Web: www.aker.com.tw

RoHS compliant



CUST. P/N	:		
Aker Approved P/N	:	SMA-040000-5CL	4T5
APPROVED	:	Tin SHEET	: 1 of 10

	-					
PREPARED	:	Sandy	REV.	:	1	

Rev.	Date	Reviser	Revise contents
1	2019/11/15	Sandy	Initial Released



CUST. P/N	•		
Aker Approved P/	N :	SMA-04	0000-5CL4T5
APPROVED	:	Tin	SHEET: 2 of 10
PREPARED	:	Sandy	REV . : 1

SMD CRYSTAL OSCILLATOR

1. ELECTRICAL CHARACTERISTICS

■ Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions for making measurement and tests are as follow:

Ambient temperature : 25±5 ℃

Relative humidity : 40%~70%

If there is any doubt about the results, measurement shall be made within the following limits:

Ambient temperature: 25±3°C

Relative humidity : 40%~70%

AKER Model: SMA-531Cutting Model: AT CUT


		Electrical Spec				
Parameters	Symbol	Min.	Typ.	Max.	Units.	Notes
Nominal Frequency		40	0.00000	0	MHz	
Frequency Stability			±25		ppm	
Supply Voltage	Vcc	3	3.3±10%	6	V	
Output Load CMOS	CL		15		pF	
Aging			±3		ppm	First Year
Enable Control			Yes			Pad 1
Operating Temperature		-40	25	85	$^{\circ}\!\mathbb{C}$	
Storage Temperature Range		-55	?	125	$^{\circ}$ C	
Output Voltage High	VoH	90%V _{DD}			V	
Output Voltage Low	VoL			10%Vdd	V	
Input Current	Icc			20	mA	
Standby Current	Ist			10	μA	
Rise Time	Tr			10	ns	10%~90%V _{DD} Level
Fall Time	Tf			10	ns	10%~90%V _{DD} Level
Symmetry (Duty ratio)	TH/T	45	~	55	%	
Start-up Time	Tosc			10	ms	
Enable Voltage High	Vhi	70%V _{DD}			V	
Disable Voltage Low	Vlo		_	30%VDD	V	
Output Enable Delay Time	T on			10	ms	
Output Disable Delay Time	T off			200	ns	
Phase Jitter RMS				1	ps	12KHz~20MHz

^{*}Please kindly be noted that AKER DO NOT guarantee parts quality which involves human security application.*




CUST. P/N	:		
Aker Approved P/N	V :	SMA-040	0000-5CL4T5
APPROVED	:	Tin	SHEET: 3 of 10
PREPARED	:	Sandy	REV . : 1

2. C-MOS LOAD OUTPUT WAVEFORM



3. C-MOS LOAD TEST CIRCUIT




***Because SMA series has no by pass capacitor. So,we recommend our customer to use capacitor 0.01 μF in join Vcc and GND.



CUST. P/N	•		
Aker Approved P	P/N :	SMA-04	10000-5CL4T5
APPROVED	:	Tin	SHEET: 4 of 10
PREPARED	:	Sandy	REV . : 1

4. MARKING:



NOTE1:

Pin1

NOIDI.	
T	5.0V TTL
С	4.5~5.0V CMOS
L	2.97~3.63V TTL&CMOS
R	2.8~3.0V CMOS
S	2.25~2.75V CMOS
Y	1.5~2.0V CMOS
Z	0.8~1.4V CMOS
W	Voltage Range CMOS

AKER LOGO.


	2019	2020	2021	2022
Year	2023	2024	2025	2026
	2027	2028	2029	2030
Month	2031	2032	2033	2034
	2035	2036	2037	2038
JAN	A	N	a	n
FEB	В	P	ъ	p
MAR	C	Q	С	q
APR	D	R	d	r
MAY	E	S	e	S
JUN	F	T	f	t
JUL	G	U	g	u
AUG	H	V	h	v
SEP	J	W	j	w
OCT	K	X	k	X
NOV	L	Y	1	у
DEC	M	Z	m	Z

5. DIMENSION:

Enable / Disable Function

E/D (#1)	OUTPUT (#3)
HIGH (Open)	Operating
LOW	High impedance


ΡI	IN FUNCTION
#1	: Enable / Disable Control
#2	: GND
#3	: OUTPUT
#4	: VDD





CUST. P/N	:		
Aker Approved P/N	:	SMA-0400	000-5CL4T5
APPROVED	:	Tin	SHEET: 5 of 10
PREPARED	:	Sandy	REV . : 1

6. STRUCTURE ILLUSTRATION



COMPONENTS		MATERIALS	COMPONENTS		MATERIALS
A	Base (Package)	Ceramic (Al2O3)+Kovar (Fe/Co/Ni)	D	Crystal blank	SiO ₂
В	IC chip		Е	Electrode	Cr / Ag
С	Conductive adhesive	Ag / Silicon resin	F	Lid	Fe/Co/Ni





CUST. P/N	:		
Aker Approved P/	V :	SMA-040	000-5CL4T5
APPROVED	:	Tin	SHEET: 6 of 10
PREPARED	:	Sandy	REV . : 1

7. PACKING:

TAPE SPECIFICATION


(Unit:mm)





OUTLINE DIMENSION


(Unit:mm)






CUST. P/N	:		
Aker Approved P/	N :	SMA-040	0000-5CL4T5
APPROVED	:	Tin	SHEET: 7 of 10
PREPARED	:	Sandy	REV . : 1

8. COVER TAPE ADHESION STRENGTH:




9. SOLDERING REFLOW PROFILE






CUST. P/N	:		
Aker Approved P/N	:	SMA-0400	000-5CL4T5
APPROVED	:	Tin	SHEET: 8 of 10
PREPARED	:	Sandy	REV . : 1

10. PACKING:



BOX = 1000 PCS / REEL





SMD product packs 32 BOX = The outside box packs (1000 PCS * 32 BOX = 32000 PCS)(MAX)



CUST. P/N	:		
Aker Approved P	/N :	SMA-04	.0000-5CL4T5
APPROVED	:	Tin	SHEET: 9 of 10
PREPARED	:	Sandy	REV . : 1

11. MECHANICAL PERFORMANCE

TEST ITEMS	TEST METHODS AND TEST CONDITION	PERFORMANCE
11.1 Drop Test	The specimen is measured for its frequency before the test. It is then dropped from a hight of 100 cm or more as a free fall object onto a hard wooden plate of 30mm or more in thickness. (in accordance with JIS-C0044)	
11.2 Vibration Test	The specimen is measured for its frequency before the test. Most them into X,Y and Z axes, respectively, for the vibration test. Vibration condition: Frequency range; 20~2000HZ Peak to peak amplitude: 1.52 mm Peak acceleration: 20G Sweep time: 20 minute / axis Pendicular total test time: 4 hours	To satisfy the electrical performance.
11.3 Resistance to Soldering Test	(in accordance with MIL-STD-883F: 2007.3) The specimen is measured for its frequency before the test. Place the specimen on the belt of the converynace and let it pass through the reflow with the presetted temperature condition. After passing twice the reflow place, the specimen under the referee condition for -~2 hours and then measure its electrical performance. Temperature Condition of IR Simulation: The temperature range of the preheated section is setted at 150 ~ 180°C for 60~120 sec. For the next section the temperature range is setted at 217~260°C for 45~90 sec. and within this time range the specimen should be able to sustain at the peak temperature, 260+/-3°C , for 10 sec long. (in accordance with JESD22-B106-B)	
11.4 Fine Leak Test	Place the specimen in a pressurized container and pressurize it with the detection gas (mixed gas consisting of 95% or more helium) for at least 2 hours. Complete the measurement of the concentration of helium within 30 min after taking it out from the pressurized container. (in accordance with MIL-STD-883F: 1014.11) The referee condition. Temperature 25 ± 2 °C Humidity 44 ~ 55 % Pressure 86 ~ 106 kPa	Less than $1.0*10^{-8} \text{ atm .c.c. / sec,}$ Helium



CUST. P/N	:		
Aker Approved P/N:		SMA-040000-5CL4T5	
APPROVED	:	Tin	SHEET: 10 of 10
PREPARED	:	Sandy	REV . : 1

12. CLIMATIC RESISTANCE

; 3							
TEST ITEMS	TEST METHODS AND TEST CONDITION	PERFORMANCE					
12.1 Low Temp Exposure Test	The specimen is measured for its frequency before the test . Place the specimen in the chamber and kept it at the temperature of - $40 \pm 3^{\circ}$ C for 168 ± 6 hours . Take the specimen out of the chamber and measure itselectrical performance after leaving 1 $^{\circ}$ 2 hours under the referee condition. (in accordance with JIS-C0020)						
12.2 Aging Test	The specimen is measured for its frequency before the test. Place the specimen in the testing chamber and keep it at the temperature of $+125 \pm 3^{\circ}$ C for 720 ± 48 hours. And then take the specimen out of the chamber and measure its electrical performance after leaving for 1° 2 hours under the referee condition. (in accordance with JIS-C0021)	To satisfy the electrical performance .					
12.3 High Temperature & High Humidty	The specimen is measured for its frequency before the test . Place the specimen in the testing chamber and kept it at the temperature of $+85 \pm 5$ °C and humidity of 85 ± 5 % for 168 ± 6 hours.and then take the specimen out and measure its electrical performance after leaving for 1^{\sim} 2 hours under the referee condition. (in accordance with MIL-STD-883F: 1004.7)						
12.4 Temperature Cycle Test	The specimen is measured for its frequency before the test . Subject the specimen to the 100 cycles of temperature ranges stated below . High temp . + 125 \pm 3 °C (15 \pm 3 min). Low temp55 \pm 3 °C (15 \pm 3 min). Measure its electrical performance after leaving it for 1 ~ 2 hours under the referee condition . (in accordance with MIL-STD-883F : 1010.8)						