




DIMENSIONS




TERMINATION



ORDERING INFORMATION

SERIES	8609	3	96	7	8	14	7	4	5	ELF
ROWS FITTED WITH CONTACTS										
ROW a b c		3	96							
ROW a - c		4	64							
ROW a b -		2	64							
NO. OF CONTACTS										
TYPE OF INSULATOR										
3 ROW MALE INSULATOR						7				
METHOD OF MOUNTING										
REVERSE MOUNTING - STYLE R								8		
TERMINATION										
STRAIGHT SPILL									14	
OPTIONS										
NO OPTION										7
WITH HARPOONS										H
PERFORMANCE CLASS										
DIN 41612 CLASS 3										4
DIN 41612 CLASS 2										5
DIN 41612 CLASS 1										6
AS PER MIL C 55302 / JSS 50808										8
PITCH PER ROW										
2.54 mm										5
LEAD FREE VERSION										ELF

PCB LAYOUT



GENERAL CHARACTERISTICS & RoHS INFO

REFER DRAWING C-8609-0000A

mat'l. code		surface		tolerance		projection		product family	
SEE DWG C-8609-0000A		ISO 1302 ✓		ISO 406 ISO 1101		mm		8609	
ltr		ecn no		dr		date		title	
A		104-0063		MINI		2004-09-17		DIN REVERSE HEADER	
B		105-0089		MINI		2005-05-19		DIN 41612 STYLE R	
C		105-0174		MINI		2005-09-27		scale 3:2	
D		106-0061		MINI		2006-05-31		dwg no	
E		108-0142		KR		2008-10-17		sheet 1 of 1	
F		108-0146		KR		2008-10-21		size	
G		ELX-I-31454		MJA		2018-10-06		A3	
sheet index		revision		G				type Product Customer Drawing	
1		sheet		1					