

November 2017

# Inductors for power circuits

Wound metal

**SPM** series

# SPM10040 type

SPM10040

(2/9)

### **REMINDERS FOR USING THESE PRODUCTS**

Before using these products, be sure to request the delivery specifications.

### SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

A REMI	NDERS
<ul> <li>The storage period is less than 12 months. Be sure to follow the stor less).</li> <li>If the storage period elapses, the soldering of the terminal electrode</li> </ul>	
O Do not use or store in locations where there are conditions such as	
<ul> <li>Before soldering, be sure to preheat components.</li> <li>The preheating temperature should be set so that the temperature does not exceed 150°C.</li> </ul>	
<ul> <li>Soldering corrections after mounting should be within the range of t If overheated, a short circuit, performance deterioration, or lifespan</li> </ul>	
O When embedding a printed circuit board where a chip is mounted t the overall distortion of the printed circuit board and partial distortion	
<ul> <li>Self heating (temperature increase) occurs when the power is tur design.</li> </ul>	ned ON, so the tolerance should be sufficient for the set thermal
<ul> <li>Carefully lay out the coil for the circuit board design of the non-maging A malfunction may occur due to magnetic interference.</li> </ul>	netic shield type.
$\bigcirc$ Use a wrist band to discharge static electricity in your body through	the grounding wire.
$\bigcirc$ Do not expose the products to magnets or magnetic fields.	
$\bigcirc$ Do not use for a purpose outside of the contents regulated in the de	livery specifications.
<ul> <li>The products listed on this catalog are intended for use in general ment, home appliances, amusement equipment, computer equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirement ity require a more stringent level of safety or reliability, or whose fail person or property.</li> <li>If you intend to use the products in the applications listed below or interval and the person or property.</li> </ul>	nent, personal equipment, office equipment, measurement equip- t. Its of the applications listed below, whose performance and/or qual- ure, malfunction or trouble could cause serious damage to society,
set forth in the each catalog, please contact us.	,
<ol> <li>(1) Aerospace/aviation equipment</li> <li>(2) Transportation equipment (cars, electric trains, ships, etc.)</li> <li>(3) Medical equipment</li> <li>(4) Power-generation control equipment</li> <li>(5) Atomic energy-related equipment</li> <li>(6) Seabed equipment</li> <li>(7) Transportation control equipment</li> </ol>	<ul> <li>(8) Public information-processing equipment</li> <li>(9) Military equipment</li> <li>(10) Electric heating apparatus, burning equipment</li> <li>(11) Disaster prevention/crime prevention equipment</li> <li>(12) Safety equipment</li> <li>(13) Other applications that are not considered general-purpose applications</li> </ul>
When designing your equipment even for general-purpose applications tection circuit/device or providing backup circuits in your equipment.	s, you are kindly requested to take into consideration securing pro-

#### INDUCTORS

### Inductors for power circuits Wound metal

⊗TDK

Product compatible with RoHS directive Halogen-free Compatible with lead-free solders

# **Overview of SPM10040 series**

#### FEATURES

O Magnetic shield type wound inductor for power circuits using a metallic magnetic material.

- O Compared to ferrite wound type inductors, it is possible to achieve large current, low Rdc, and compactness.
- O Low inductance variance in high-temperature environments with good DC superimposition characteristics.
- O Metallic magnetic material is used, and the structure has an integrated molded coil, so hum noise is lower than with core adhesive coils.

#### APPLICATION

Note PCs, HDDs, servers, VRMs, compact power supply modules, other

#### PART NUMBER CONSTRUCTION

SPM	10040	T -	- 1R0	M
Series name	L×W×H dimensions (mm max.)	Packaging style	Inductance (µH)	Inductance tolerance
	10040 10.7×10.0×4.0	T Taping	1R01.010010	M ±20%

#### OPERATING TEMPERATURE RANGE, PACKAGE QUANTITY, PRODUCT WEIGHT

	Temperat	ure range	Package quantity	Individual weight	
Туре	Operating temperature* (°C)	Storage temperature** (°C)	(pieces/reel)		
	( •)	(•)	(piccosiicoi)	(g)	
SPM10040	-40 to +125	-40 to +125	500	1.96	
* • • •			•		

\* Operating temperature range includes self-temperature rise.

\*\* The storage temperature range is for after the assembly.


O RoHS Directive Compliant Product: See the following for more details. https://product.tdk.com/info/en/environment/rohs/index.html

O Halogen-free: indicates that CI content is less than 900ppm, Br content is less than 900ppm, and that the total CI and Br content is less than 1500ppm.

(4/9)

# SPM10040 type

#### RECOMMENDED REFLOW PROFILE




Preheati	ng		Soldering	3	Peak		
Temp.		Time	Temp.	Time	Temp.	Time	
T1	T2	t1	Т3	t2	Τ4	t3	
150°C	180°C	120s	230°C	30s	260°C	10s max.	

**⊗TDK** 

INDUCTORS

## SPM10040 type


#### SHAPE & DIMENSIONS





Dimensions in mm

#### RECOMMENDED LAND PATTERN



Dimensions in mm

# SPM10040 type

#### ELECTRICAL CHARACTERISTICS

#### CHARACTERISTICS SPECIFICATION TABLE

L		Measuring frequency	DC resistant	DC resistance Rated current*		Part No.	
					Isat	Itemp	
(µH)	Tolerance	(kHz)	(m $\Omega$ )max.	(m $\Omega$ )typ.	(A)typ.	(A)typ.	
1.0	±20%	100	4.2	3.9	18.0	15.0	SPM10040T-1R0M
2.2	±20%	100	7.5	6.8	12.2	12.0	SPM10040T-2R2M
3.3	±20%	100	11.0	10.0	11.0	9.8	SPM10040T-3R3M
4.7	±20%	100	15.6	14.1	8.0	7.9	SPM10040T-4R7M
6.8	±20%	100	23.3	21.1	7.1	6.9	SPM10040T-6R8M
10.0	±20%	100	29.4	26.7	6.0	5.8	SPM10040T-100M
22.0	±20%	100	79.0	71.8	4.6	3.6	SPM10040T-220M

\* Rated current: smaller value of either lsat or Itemp.

Isat: When based on the inductance change rate (20% below the initial value)

Itemp: When based on the temperature increase (temperature increase of 40°C by self heating)

 $\cdot$  The cleaning agent can not be used for these products.

#### O Measurement equipment

Measurement item	Product No.	Manufacturer
L	4284A	Keysight Technologies
DC resistance	AX-111A	ADEX
Rated current Isat	4284A+42841A+42842C	Keysight Technologies

\* Equivalent measurement equipment may be used.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.


**⊗TDK** 

(7/9)

# SPM10040 type

#### ELECTRICAL CHARACTERISTICS

#### L FREQUENCY CHARACTERISTICS GRAPH



O Measurement equipment

Product No.	Manufacturer
4294A	Keysight Technologies
* Equivalent measur	ement equinment may be used


\* Equivalent measurement equipment may be used.

(8/9)

# SPM10040 type

#### ELECTRICAL CHARACTERISTICS

#### **INDUCTANCE VS. DC BIAS CHARACTERISTICS GRAPH**



O Measurement equipment

Product No.


Manufacturer 4284A+42841A+42842C **Keysight Technologies** 

\* Equivalent measurement equipment may be used.

# SPM10040 type

#### PACKAGING STYLE


**REEL DIMENSIONS** 



Туре	Α	W1	W2	Ν	Е
SPM10040	ø330	24.5	29.1	ø100	2.3

\* These values are typical values.

TAPE DIMENSIONS



Туре	A	В	ØD0	E	F	P0	P1	P2	W	K	t
SPM10040	10.5±0.1	11.6±0.1	1.5+0.1/-0	1.75±0.1	11.5±0.1	4.0±0.1	16.0±0.1	2.0±0.1	24.0±0.3	4.2±0.1	0.40±0.05