# **ALUMINUM ELECTROLYTIC CAPACITORS**



Chip Type, High Voltage. High Reliability.



- Chip type, High voltage and High Reliability.
- Load life of 4000 hours at +125°C.
- Applicable to automatic mounting machine using carrier tape.
- Compliant to the RoHS directive (2011/65/EU).
- AEC-Q200 compliant. Please contact us for details.






#### Specifications

Item	Performance Characteristics										
Category Temperature Range	-40 to +125°C										
Rated Voltage Range	160 to 450V										
Rated Capacitance Range	2.2 to 27μF										
Capacitance Tolerance	±20% at 120Hz, 20°C										
Leakage Current	After 1 minute's application of rated voltage at 20°C, leakage current is not more than 0.04CV+100 (μA).										
	Measurement frequency : 120Hz at 20°C										
Tangent of loss angle (tan δ)	Rated voltage (V) 160 20	00	250	400	450						
	tan δ (MAX.) 0.20 0.5	20	0.25	0.25	0.30						
			Meas	surement	frequenc	y : 120Hz					
	Rated voltage (V)	160	200	250	400	450					
Stability at Low Temperature	Impedance ratio ZT / Z20 (MAX.)	6	6	10	10	15					
Endurance	The specifications listed at right sha capacitors are restored to 20°C after applied for 4000 hours at 125°C.			tan δ	itance cha ge current	Ŭ	Within ±30% of the initial capacitance value 300% or less than the initial specified value Less than or equal to the initial specified value				
Shelf Life	After storing the capacitors under no load at 125°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.										
Resistance to soldering heat	The capacitors are kept on a hot pla which is maintained at 250°C and the treatment based on JISC 5101-4 c shall meet the characteristic require when they are removed from the plants.	C and then performing voltage 101-4 clause 4.1 at 20°C, they requirements listed at right		Capacitance change tan δ Leakage current		Ŭ	Within ±10% of the initial capacitance value Less than or equal to the initial specified value Less than or equal to the initial specified value				
Marking	Black print on the case top.										


### ■Chip Type



			(mm)
øD×L	8×10	10 × 10	10 × 13.5
Α	2.9	3.2	3.2
В	8.3	10.3	10.3
С	8.3	10.3	10.3
Е	3.1	4.5	4.5
L	10	10	13.5
Н	0.8 to 1.1	0.8 to 1.1	0.8 to 1.1

Voltage					
V	160	200	250	400	450
Code	2C	2D	2E	2G	2W

# Type numbering system (Example : 400V 5.6µF)



### ■ Dimensions

	V	16	60	20	00	2	50	40	00	450	0
Cap.(µF)	Code	2	С	2	D	2	E	20	G	2V	/
2.2	2R2				l I		I I			8×10	20
3.3	3R3						ļ	8×10	30		
3.9	3R9						i			10 × 10	35
5.6	5R6						l I	10 × 10	45	10 × 13.5	40
7.5	7R5					8×10	¦ 30	10 × 13.5	50		
10	100			8×10	45						
12	120	8×10	45			10 × 10	45				
15	150			10×10	60	10 × 13.5	¦ 50				
18	180	10 × 10	60				İ				
22	220			10 × 13.5	65		i			Case size	Rated
27	270	10 × 13.5	65							$\phi D \times L (mm)$	Rated ripple

Rated ripple current (mArms) at 125°C 120Hz

## • Frequency coefficient of rated ripple current

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
Coefficient	0.70	1.00	1.17	1.36	1.50

- Taping specifications are given in page 23.
- Recommended land size, soldering by reflow are given in page 18, 19.
- Please refer to page 3 for the minimum order quantity.