

**N- AND P-Channel Enhancement Mode MOSFET**

# MTC3586BDFA6

	N-CH	P-CH
$BV_{DSS}$	20V	-20V
$I_D$	5A( $V_{GS}=4.5V$ )	-3.3A( $V_{GS}=-4.5V$ )
$R_{DS(on)(TYP.)}$	27m $\Omega$ ( $V_{GS}=4.5V$ )	78m $\Omega$ ( $V_{GS}=-4.5V$ )
	37m $\Omega$ ( $V_{GS}=2.5V$ )	115m $\Omega$ ( $V_{GS}=-2.5V$ )
	82m $\Omega$ ( $V_{GS}=1.5V$ )	280m $\Omega$ ( $V_{GS}=-1.5V$ )

**Description**


The MTC3586BDFA6 consists of a N-channel and a P-channel enhancement-mode MOSFET in a single DFN2\*2-6L package, providing the designer with the best combination of fast switching, ruggedized device design, low on-resistance and cost-effectiveness.

The DFN2\*2-6L package is universally preferred for all commercial-industrial surface mount applications.


**Features**

- Simple drive requirement
- Low gate charge
- Low on-resistance
- Fast switching speed
- Pb-free lead plating and halogen-free package

**Equivalent Circuit**




**Outline**



**Ordering Information**

Device	Package	Shipping
MTC3586BDFA6-0-T1-G	DFN2x2-6L (Pb-free lead plating and halogen-free package)	3000 pcs / Tape & Reel





**Absolute Maximum Ratings** (Ta=25°C)

Parameter	Symbol	Limits		Unit
		N-channel	P-channel	
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	20	-20	V
Gate-Source Voltage	V <sub>GS</sub>	±12	±12	
Continuous Drain Current @T <sub>A</sub> =25 °C (Note 1)	I <sub>D</sub>	5	-3.3	A
Continuous Drain Current @T <sub>A</sub> =70 °C (Note 1)	I <sub>D</sub>	4	-2.6	
Pulsed Drain Current (Note 2)	I <sub>DM</sub>	20	-20	
Total Power Dissipation (Note 1)	Pd	1.38		W
Linear Derating Factor		0.01		W / °C
Operating Junction and Storage Temperature	T <sub>j</sub> , T <sub>stg</sub>	-55~+150		°C

Note : 1.Surface mounted on 1 in<sup>2</sup> copper pad of FR-4 board, t≤5 sec  
 2.Pulse width limited by maximum junction temperature

**N-Channel Electrical Characteristics** (Tj=25°C, unless otherwise specified)

Symbol	Min.	Typ.	Max.	Unit	Test Conditions
<b>Static</b>					
BV <sub>DSS</sub>	20	-	-	V	V <sub>GS</sub> =0, I <sub>D</sub> =250μA
ΔBV <sub>DSS</sub> /ΔT <sub>j</sub>	-	0.02	-	V/°C	Reference to 25°C, I <sub>D</sub> =1mA
V <sub>GS(th)</sub>	0.5	0.7	1.2	V	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA
I <sub>GSS</sub>	-	-	±100	nA	V <sub>GS</sub> =±12V, V <sub>DS</sub> =0
I <sub>DSS</sub>	-	-	1	μA	V <sub>DS</sub> =20V, V <sub>GS</sub> =0
	-	-	10		V <sub>DS</sub> =16V, V <sub>GS</sub> =0, T <sub>j</sub> =70°C
*R <sub>DS(ON)</sub>	-	27	40	mΩ	I <sub>D</sub> =3.5A, V <sub>GS</sub> =4.5V
	-	37	50		I <sub>D</sub> =1.2A, V <sub>GS</sub> =2.5V
	-	82	105		I <sub>D</sub> =0.5A, V <sub>GS</sub> =1.5V
*G <sub>FS</sub>	-	7	-	S	V <sub>DS</sub> =5V, I <sub>D</sub> =3A
<b>Dynamic</b>					
C <sub>iss</sub>	-	423	-	pF	V <sub>DS</sub> =20V, V <sub>GS</sub> =0, f=1MHz
C <sub>oss</sub>	-	50	-		
C <sub>rss</sub>	-	48	-		
*t <sub>d(ON)</sub>	-	6	-	ns	V <sub>DS</sub> =15V, I <sub>D</sub> =1A, V <sub>GS</sub> =5V, R <sub>G</sub> =3.3Ω, R <sub>D</sub> =15Ω
*t <sub>r</sub>	-	8	-		
*t <sub>d(OFF)</sub>	-	11	-		
*t <sub>f</sub>	-	10	-		
*Q <sub>g</sub>	-	6	-	nC	V <sub>DS</sub> =16V, I <sub>D</sub> =3A, V <sub>GS</sub> =4.5V
*Q <sub>gs</sub>	-	0.8	-		
*Q <sub>gd</sub>	-	2.5	-		
<b>Source-Drain Diode</b>					
*V <sub>SD</sub>	-	0.77	1.2	V	V <sub>GS</sub> =0V, I <sub>S</sub> =1.2A
*t <sub>rr</sub>	-	16	-	ns	I <sub>S</sub> =3A, V <sub>GS</sub> =0V, dI/dt=100A/μs
*Q <sub>rr</sub>	-	8	-	nC	

\*Pulse Test : Pulse Width ≤300μs, Duty Cycle ≤2%



**P-Channel Electrical Characteristics** (Tj=25°C, unless otherwise specified)

Symbol	Min.	Typ.	Max.	Unit	Test Conditions
<b>Static</b>					
BV <sub>DSS</sub>	-20	-	-	V	V <sub>GS</sub> =0, I <sub>D</sub> =-250μA
ΔBV <sub>DSS</sub> /ΔT <sub>j</sub>	-	-0.01	-	V/°C	Reference to 25°C, I <sub>D</sub> =-1mA
V <sub>GS(th)</sub>	-	-0.8	-1.2	V	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =-250μA
I <sub>GSS</sub>	-	-	±100	nA	V <sub>GS</sub> =±12V, V <sub>DS</sub> =0
I <sub>DSS</sub>	-	-	-1	μA	V <sub>DS</sub> =-20V, V <sub>GS</sub> =0
	-	-	-25		V <sub>DS</sub> =-16V, V <sub>GS</sub> =0, T <sub>j</sub> =70°C
*R <sub>DS(ON)</sub>	-	78	105	mΩ	I <sub>D</sub> =-2.5A, V <sub>GS</sub> =-4.5V
	-	115	150		I <sub>D</sub> =-2A, V <sub>GS</sub> =-2.5V
	-	280	350		I <sub>D</sub> =-0.5A, V <sub>GS</sub> =-1.5V
*G <sub>FS</sub>	-	5	-	S	V <sub>DS</sub> =-5V, I <sub>D</sub> =-2A
<b>Dynamic</b>					
C <sub>iSS</sub>	-	429	-	pF	V <sub>DS</sub> =-20V, V <sub>GS</sub> =0, f=1MHz
C <sub>oSS</sub>	-	45	-		
C <sub>rSS</sub>	-	41	-		
*t <sub>d(ON)</sub>	-	6	-	ns	V <sub>DS</sub> =-10V, I <sub>D</sub> =-1A, V <sub>GS</sub> =-10V, R <sub>G</sub> =3.3Ω, R <sub>D</sub> =10Ω
*t <sub>r</sub>	-	17	-		
*t <sub>d(OFF)</sub>	-	16	-		
*t <sub>f</sub>	-	5	-		
*Q <sub>g</sub>	-	6	-	nC	V <sub>DS</sub> =-16V, I <sub>D</sub> =-2A, V <sub>GS</sub> =-4.5V
*Q <sub>gs</sub>	-	0.8	-		
*Q <sub>gd</sub>	-	2.4	-		
<b>Source-Drain Diode</b>					
*V <sub>SD</sub>	-	-0.82	-1.2	V	V <sub>GS</sub> =0V, I <sub>S</sub> =-1.2A
*t <sub>rr</sub>	-	20	-	ns	I <sub>S</sub> =-2A, V <sub>GS</sub> =0V, dI/dt=100A/μs
*Q <sub>rr</sub>	-	15	-	nC	

\*Pulse Test : Pulse Width ≤300μs, Duty Cycle ≤2%

**Thermal Data**


Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-case, max	R <sub>θJC</sub>	80	°C/W
Thermal Resistance, Junction-to-ambient, max	R <sub>θJA</sub>	90 (Note)	

Note : Surface mounted on 1 in<sup>2</sup> copper pad of FR-4 board, t ≤5 sec; 195°C/W when mounted on minimum copper pad




## N-channel Typical Characteristics


Typical Output Characteristics




Brekdown Voltage vs Ambient Temperature




Static Drain-Source On-State resistance vs Drain Current




Reverse Drain Current vs Source-Drain Voltage



Static Drain-Source On-State Resistance vs Gate-Source Voltage




Drain-Source On-State Resistance vs Junction Temperature






**N-channel Typical Characteristics(Cont.)**


Capacitance vs Drain-to-Source Voltage




Threshold Voltage vs Junction Temperature




Single Pulse Power Rating, Junction to Ambient




Gate Charge Characteristics



Maximum Safe Operating Area




Maximum Drain Current vs Junction Temperature




**N-channel Typical Characteristics(Cont.)**

Transient Thermal Response Curves




## P-channel Typical Characteristics


Typical Output Characteristics




Brekdown Voltage vs Ambient Temperature




Static Drain-Source On-State resistance vs Drain Current




Reverse Drain Current vs Source-Drain Voltage



Static Drain-Source On-State Resistance vs Gate-Source Voltage




Drain-Source On-State Resistance vs Junction Temperature




**P-channel Typical Characteristics(Cont.)**


Capacitance vs Drain-to-Source Voltage




Threshold Voltage vs Junction Temperature




Single Pulse Power Rating, Junction to Ambient




Gate Charge Characteristics



Maximum Safe Operating Area




Maximum Drain Current vs Junction Temperature






**P-channel Typical Characteristics(Cont.)**

Transient Thermal Response Curves




**Recommended Soldering Footprint**




Unit : mm

**Reel Dimension**




**Carrier Tape Dimension**



**Recommended wave soldering condition**

Product	Peak Temperature	Soldering Time
Pb-free devices	260 +0/-5 °C	5 +1/-1 seconds


**Recommended temperature profile for IR reflow**



Profile feature	Sn-Pb eutectic Assembly	Pb-free Assembly
Average ramp-up rate ( $T_{s\max}$ to $T_p$ )	3°C/second max.	3°C/second max.
Preheat		
-Temperature Min( $T_{s\min}$ )	100°C	150°C
-Temperature Max( $T_{s\max}$ )	150°C	200°C
-Time( $t_{s\min}$ to $t_{s\max}$ )	60-120 seconds	60-180 seconds
Time maintained above:		
-Temperature ( $T_L$ )	183°C	217°C
- Time ( $t_L$ )	60-150 seconds	60-150 seconds
Peak Temperature( $T_p$ )	240 +0/-5 °C	260 +0/-5 °C
Time within 5°C of actual peak temperature( $t_p$ )	10-30 seconds	20-40 seconds
Ramp down rate	6°C/second max.	6°C/second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

Note : All temperatures refer to topside of the package, measured on the package body surface.

**DFN2x2-6L Dimension**



DIM	Millimeters		Inches		DIM	Millimeters		Inches	
	Min.	Max.	Min.	Max.		Min.	Max.	Min.	Max.
A	0.700	0.800	0.028	0.031	E1	0.520	0.720	0.020	0.028
A1	0.000	0.050	0.000	0.002	k	0.200	-	0.008	-
A3	0.203	REF	0.008	REF	b	0.250	0.350	0.010	0.014
D	1.900	2.100	0.075	0.083	e	0.650	TYP	0.026	TYP
E	1.900	2.100	0.075	0.083	L	0.200	0.300	0.008	0.012
D1	0.900	1.100	0.035	0.043					

**Notes :** 1.Controlling dimension : millimeters.  
 2.Maximum lead thickness includes lead finish thickness, and minimum lead thickness is the minimum thickness of base material.  
 3.If there is any question with packing specification or packing method, please contact your local CYStek sales office.

**Material :**

- Lead :Pure tin plated.
- Mold Compound : Epoxy resin family, flammability solid burning class:UL94V-0.

**Important Notice:**

- All rights are reserved. Reproduction in whole or in part is prohibited without the prior written approval of CYStek.
- CYStek reserves the right to make changes to its products without notice.
- CYStek **semiconductor products are not warranted to be suitable for use in Life-Support Applications, or systems.**
- CYStek assumes no liability for any consequence of customer product design, infringement of patents, or application assistance.