

Form No.: QF-1274

Edition: 2

#### ISO9001 ISO14001 IATF16949 CHILISIN ELECTRONICS CORP.

## RoHS & Halogen Free & REACH Compliance.


## SPECIFICATION FOR APPROVAL

Customer :	超利維				
Customer P/N:					
Drawing No:	IE1-950243				
Quantity:	X Pcs. Date:	2019/5/15			
Chilisin P/N:	LD0805-4R7K-N				
	SPECIFICATION				
	ACCEPTED BY:				
COMPONENT					
ENGINEER					
ELECTRICAL					
ENGINEER					
MECHANICAL					
ENGINEER					
APPROVED					
REJECTED					
奇力新電子股份有限公司	東莞奇力新電子	(東莞廠)有限公司			
Chilisin Electronics Corp	Chilisin Electronics	(Dongguan) Co., Ltd.			
No. 29, Alley 301, Tehhsin Rd., Hukou, Hsinchu 303, Taiwan	No. 78, Puxing Rd., Area, Qingxi Town,	Yuliangwei Administration Dongguan City,			
TEL: +886-3-599-2646	Guangdong,China				
FAX: +886-3- 599-9176 E-mail: sales@chilisin.com	TEL: +86-769-8773 FAX: +86-769-877				
http://www.chilisin.com	E-mail : cect@chilis				
奇力新電子(越南廠)有限		海蘇)有限公司			
Chilisin Electronics (Vietnam) Li No 143 - 145, Road No 10, VSIF	HuNan Chilisin Elec	tronics Technology Co., Ltd			
Phong, Lap Le Commune, Thuy	, <sub>Nguven</sub> No. 8, Shaziao Lian	gshuijing Town, Yuanling ty, Hunan Province 419601,			
Dist, Haiphong City, Vietnam Tel: 84-316 255 688 Fax: 84-	316 255 China				
689	Tel: 86-745-867-58 E-mail: cect@chilis				
E-mail: sales@chilisin.com	L-mail · cect@chills				
Drawn by	Checked by	Approved by			
徐鈺雯 yumi.hsu	吳振賢 ian.wu	陳瑞揚 ryan.che			



## **LD0805 Series Specification**

- 1 Scope: This specification applies to Wire Wound Ferrite Chip Inductors
- 2 Part Numbering:



## 3 Rating:


Operating Temperature:  $-25\% \sim 105\%$  (Including self - temperature rise)

Storage Temperature:  $20^{\circ}$ C ~  $25^{\circ}$ C R.H.  $65^{\circ}$ %(In Tape & Reel Condition)

50 to 80 %RH

## 4 Marking:

Humidity



Ex Marking:1st→Red

5 Standard Testing Condition


# Unless otherwise specified In case of doubt Temperature Ordinary Temperature(15 to 35℃) 20 to 30℃

Ordinary Humidity(25 to 85% RH)



# **LD0805 Series Specification**

## 6 Configuration and Dimensions:



#### 7 Electrical Characteristics:

		L/Q Test							
Part No.	Inductance	Freq.	Q	SRF	RDC	IDC	Tolerance	Color Code	
	(uH)	(MHz)	Тур.	(MHz)Min.	(Ω)±30%	(mA)Typ.	(±%)	1st	
LD0805-4R7□-N	4.7	7.96	18	50	0.43	520	10	YEL	

#### NOTE: ☐-tolerance K=±10%

1.Operating temperature range  $-~2~5\,^\circ\!\!\!\!\mathrm{C}~\sim~1~0~5\,^\circ\!\!\!\!\mathrm{C}$  (Including self - temperature rise)

2.L/Q Test OSC @200mV.

 $3.\mbox{IDC}$  for Inductance drop 10% from its value without current.


"-N" FOR COMPLETELY LEAD FREE TYPE(INCLUDING FERRITE BODY & SOLDER)



# **LD0805 Series Specification**

## 8 LD0805 Series

## 8.1 Construction:



### 8.2 Material List:

No	Part	Material		
1	WIRE	Grade 180		
2	EPOXY	UV GLUE		
3	CORE	FERRITE		
4	TERMINAL	Ag/Cu/Ni/Sn		



## **LD0805 Series Specification**

## 9 Packaging:

## 9.1 Packaging -Cover Tape


The force for tearing off cover tape is 10 to 100 grams in the arrow direction.



### 9.2 Packaging Quantity

TYPE	PCS/REEL
LD0805	2000

#### 9.3 Reel Dimensions



Reel Dimensions: m/m


TYPE	A	В	U	D
LD0805	178	60	12	1.5




## **LD0805 Series Specification**

# 9 Packaging:

#### 9.4 Tape Dimensions in mm



## 10 Recommended Land Pattern:



## 11 Note:

- 1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
- 2. Do not knock nor drop.
- 3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose,under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
- 4. Please keep the distance between transformer/coil and other components (refer to the standard IEC 950)
- 5. The moisture sensitivity level (MSL) of products is classified as level 1.



# **LD0805 Series Specification**

12 Graph: LD0805-4R7K-N

