

## RoHS & Halogen Free & REACH Compliance.


## SPECIFICATION FOR APPROVAL

Customer:		超利維	<b>E</b>			
Customer P/N:						
Drawing No:		IE1-8B0	365			
Quantity:	X F	Pcs. Date:	2018/11/23			
Chilisin P/N:		MHCB06012-	100M-C1			
		IFICATION EPTED BY:				
COMPONENT						
ENGINEER						
ELECTRICAL						
ENGINEER						
MECHANICAL						
ENGINEER						
APPROVED						
REJECTED						
奇力新電子股份有限公司 Chilisin Electronics Corp No. 29, Alley 301, Tehhsin Rd. Hukou,Hsinchu 303, Taiwan TEL: +886-3-599-2646 FAX: +886-3-599-9176 E-mail: sales@chilisin.com http://www.chilisin.com			ongguan) Co., Ltd. uliangwei Administration Area, an City, Guangdong,China 251~3 0232			
奇力新電子(越南廠)有限 Chilisin Electronics (Vietnam) L No 143 - 145, Road No 10, VS Lap Le Commune, Thuy Nguye Haiphong City, Vietnam Tel: 84-316 255 688 Fax: 84 E-mail: sales@chilisin.com	.imited IP Hai Phong, en Dist,	No. 8, Shaziao Liangs	nics Technology Co., Ltd huijing Town, Yuanling Hunan Province 419601,			
Drawn by	C	necked by	Approved by			



# **MHCB06012 Series Specification**

- 1 Scope: This specification applies to Large current and Low Loss SMD Power INDUCTOR
- 2 Part Numbering:




### 3 Rating:

Operating Temperature: - 55°C ~ 125°C

Storage Temperature: (on tape & reel): -20 °C to +40 °C; 75% RH max.

### 4 Marking:



Ex: MHCB06012-100M-C1

Marking: 100

Marking color : Black


### 5 Standard Testing Condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°ℂ)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH



# **MHCB06012 Series Specification**

### 6 Configuration and Dimensions:



TYPE	MHCB06012
Α	6.6 ± 0.2
В	6.95 ± 0.35
C	1.0 ± 0.2
D	$3.0 \pm 0.3$
F	1.6 ± 0.5

### 7 Electrical Characteristics:

Part No.	Inductance (uH)	Tolerance (±%)	Test Freq.	Irms(A) Typ	Isat(A) Typ	RDC(mΩ) Max(Typ)	Marking
MHCB06012-100M-C1	10	20	100kHz,0.5V	2.0	2.4	272.7(267.3)	100

#### Note:


- 1. Operating temperature range -55° C ~125° C
- 2.Isat for Inductance drop 30% from its value without current.
- 4.The part temperature (ambient + temp rise) should not exceed 125°C under worst case operating conditions. Circuit design 125°C under worst case operating conditions. Component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.
- 5. Absolute maximum voltage 30VDC



# **MHCB06012 Series Specification**

### 8 MHCB06012 Series

#### 8.1 Construction:



#### 8.2 Material List:

No	Part	Material
1	COATING+ CORE	CARBONYL IRON POWDERS
2	WRE	COPPER WIRE
3	TERMINAL	TERMINAL COPPER




# **MHCB06012 Series Specification**

## 9 PACKAGING

### 9.1 Packaging -Cover tape


The force for tearing off cover tape is 10 to 130 grams in the arrow direction.



#### 9.2 Packaging Quantity

TYPE	PCS/REEL
MHCB06012	1000

#### 9.3 Reel Dimensions



#### Dimensions in mm


TYPE	Α	В	С	D
MHCB06012	330	100	13	16



# **MHCB06012 Series Specification**


## 9 PACKAGING

#### 9.4 Tape Dimensions in mm



TYPE	A0	B0	K0	D	Е	W	Р	P0	P2
MHCB06012	6.9	7.6	1.5	1.55	1.75	16	12	4	2

### 10 Recommended Pattern



#### Dimensions in mm

TYPE	A(mm)	B(mm)	C(mm)
MHCB06012	3.5	6.05	2.35

### 11 Note:

- 1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
- 2. Do not knock nor drop.
- 3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose,under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
- 4. Please keep the distance between transformer/coil and other components (refer to the standard IEC 950)
- 5. The moisture sensitivity level (MSL) of products is classified as level 1.



# **MHCB06012 Series Specification**



