



MATERIAL

Insulator : NY66+30% Glass fiber
 Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP
 Insulation Resistance : 5000MΩMin. at DC 500V
 Contact Resistance : 20mΩMax. at DC 100mA
 Dielectric Voltage : AC 500V for one minute
 Operation Temperature : -40°C to + 105°C

210-8 $\frac{2}{1}$ - $\frac{05}{2}$ G $\frac{B}{3}$ $\frac{B}{4}$ $\frac{06}{5}$

1. 1: Single row
2: Dual rows
2. No. of contacts per row
3. G: Gold flash
S: Selective
T: Tin plated
4. B: Black Insulator
W: White Insulator
5. Pinrex internal code.

| | | | | | | | | | | |
|------|-------------|------------|--|--|------|--------------------------------|------|--|---------------|---------------------------------------|
| | | | | TOLERANCE | | OLD PART NO. | | TITLE | | 頻銳科技股份有限公司 PINREX TECHNOLOGY CORP. |
| | | | | .0 =±.30 .00 =±.20 .000 =±.XXX .0000=±. ANG.=±3' | | UNITS : mm DRAWER 廖小芳 CHECK | | PIN HEADER 2.54*2.54mm STRAIGHT TYPE, DUAL ROWS | | |
| B | 修改總裝尺寸 | 2017/03/22 | | SCALE | SIZE | SHEET | REV. | APP'D | NEW PART NO. | DRAW NO. |
| A | RELEASE | 2005/09/15 | | NONE | A4 | 1 OF 1 | B | | 210-82-05GB06 | 210-82-05GB06(B版) |
| REV. | DESCRIPTION | DATE | | | | | | | | |