TFBS4650



Vishay Semiconductors

Infrared Transceiver, 9.6 kbit/s to 115.2 kbit/s (SIR)



DESIGN SUPPORT TOOLS AVAILABLE



DESCRIPTION

The TFBS4650 is one of the smallest IrDA[®] compliant transceivers available. It supports data rates up to 115 kbit/s. The transceiver consists of a PIN photodiode, infrared emitter, and control IC in a single package.

FEATURES

 Compliant with the IrDA physical layer IrPHY 1.4 (low power specification, 9.6 kbit/s to 115.2 kbit/s)



- Link distance: 30 cm/20 cm full 15° cone with standard or low power IrDA, respectively. Emission intensity can be set by an external resistor to increase the range for extended low power spec to > 50 cm
- Typical transmission distance to standard device: 50 cm
- Small package (L x W x H in mm): 6.8 x 2.8 x 1.6
- Low current consumption 75 μA idle at 3.6 V
- Shutdown current 10 nA typical at 25 °C
- Operates from 2.4 V to 5.5 V within specification over full temperature range from -30 °C to +85 °C
- Split power supply, emitter can be driven by a separate power supply not loading the regulated. U.S. pat. no. 6,157,476
- Qualified for lead (Pb)-free and Sn/Pb processing (MSL4)
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- Mobile phone
- PDAs


PRODUCT SUMMARY									
PART NUMBER	DATA RATE (kbit/s)	DIMENSIONS H x L x W (mm x mm x mm)	LINK DISTANCE (m)	OPERATING VOLTAGE (V)	IDLE SUPPLY CURRENT (mA)				
TFBS4650	115.2	1.6 x 6.8 x 2.8	0 to ≥ 0.3	2.4 to 5.5	0.075				

PARTS TABLE						
PART	DESCRIPTION	QTY/REEL				
TFBS4650-TR1	Oriented in carrier tape for side view surface mounting	1000 pcs				
TFBS4650-TR3	Oriented in carrier tape for side view surface mounting	2500 pcs				
TFBS4650-TR4	Oriented in carrier tape for side view surface mounting	6000 pcs				
TFBS4650-TT3	Oriented in carrier tape for top view surface mounting	2500 pcs				

1




FUNCTIONAL BLOCK DIAGRAM



PIN DESCR	PIN DESCRIPTION						
PIN NUMBER	SYMBOL	DESCRIPTION	I/O	ACTIVE			
1	IREDA	IRED anode, connected via a current limiting resistor to V _{CC2} . A separate unregulated power supply can be used.					
2	IREDC	IRED cathode, do not connect for standard operation.					
3	TXD	Transmitter data input. Setting this input above the threshold turns on the transmitter. This input switches the IRED with the maximum transmit pulse width of about 100 µs.	I	High			
4	RXD	Receiver output. Normally high, goes low for a defined pulse duration with the rising edge of the optical input signal. Output is a CMOS tri-state driver, which swings between ground and V_{CC} . Receiver echoes transmitter output.	0	Low			
5	SD	Shutdown. Logic low at this input enables the receiver, enables the transmitter, and un-tri-states the receiver output. It must be driven high for shutting down the transceiver.	I	High			
6	V_{CC}	Power supply, 2.4 V to 3.6 V. This pin provides power for the receiver and transmitter drive section. Connect V_{CC1} via an optional filter.					
7	GND	Ground					

PINOUT

TFBS4650, bottom view weight 0.05 g



Definitions:

In the Vishay transceiver datasheets the following nomenclature is used for defining the IrDA operating modes:

- SIR: 2.4 kbit/s to 115.2 kbit/s, equivalent to the basic serial infrared standard with the physical layer version IrPhy 1.0
- MIR: 576 kbit/s to 1152 kbit/s
- FIR: 4 Mbit/s
- VFIR: 16 Mbit/s

MIR and FIR were implemented with IrPhy 1.1, followed by IrPhy 1.2, adding the SIR low power standard. IrPhy 1.3 extended the low power option to MIR and FIR and VFIR was added with IrPhy 1.4. A new version of the standard in any case obsoletes the former version.

Rev. 1.9, 29-Apr-2019



ABSOLUTE MAXIMUM RATINGS							
PARAMETER	TEST CONDITIONS	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Supply voltage range, transceiver	0 V < V _{CC2} < 6 V	V _{CC1}	-0.5	-	6	V	
Supply voltage range, transmitter	0 V < V _{CC1} < 6 V	V _{CC2}	-0.5	-	6	V	
Voltage at RXD	All states	V _{IN}	-0.5	-	V _{CC} + 0.5	V	
Input voltage range, transmitter TXD	Independent of V_{CC1} or V_{CC2}	V _{IN}	-0.5	-	6	V	
Input currents	For all pins, except IRED anode pin		-40	-	40	mA	
Output sinking current			-	-	20	mA	
Power dissipation		PD	-	-	250	mW	
Junction temperature		TJ	-	-	125	°C	
Ambient temperature range (operating)		T _{amb}	-30	-	+85	°C	
Storage temperature range		T _{stg}	-40	-	+100	°C	
Soldering temperature ⁽¹⁾	See section "Recommended Solder Profile"		-	-	-	°C	
Repetitive pulse output current	< 90 µs, t _{on} < 20 %	I _{IRED} (RP)	-	-	500	mA	
Average output current (transmitter)		I _{IRED} (DC)	-	-	100	mA	
Thermal resistance junction-to-ambient	JESD51	R _{thJA}	-	300	-	K/W	

Notes

· Reference point pin, ground unless otherwise noted

Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing

⁽¹⁾ Sn/lead (Pb)-free soldering. The product passed Vishay's standard convection reflow profile soldering test

EYE SAFETY INFORMATION						
STANDARD	CLASSIFICATION					
IEC/EN 60825-1 (2007-03), DIN EN 60825-1 (2008-05) "SAFETY OF LASER PRODUCTS - Part 1: equipment classification and requirements", simplified method	Class 1					
IEC 62471 (2006), CIE S009 (2002) "Photobiological Safety of Lamps and Lamp Systems"	Exempt					
DIRECTIVE 2006/25/EC OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 5 th April 2006 on the minimum health and safety requirements regarding the exposure of workers to risks arising from physical agents (artificial optical radiation) (19 th individual directive within the meaning of article 16(1) of directive 89/391/EEC)	Exempt					

Note

· Vishay transceivers operating inside the absolute maximum ratings are classified as eye safe according the above table

 Rev. 1.9, 29-Apr-2019
 3
 Document Number: 84672

 For technical questions within your region: irdasupportAM@vishay.com, irdasupportAP@vishay.com, irdasupportEU@vishay.com
 THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



www.vishay.com

Vishay Semiconductors

PARAMETER	TEST CONDITIONS	SYMBOL	MIN.	TYP.	MAX.	UNIT
TRANSCEIVER		•				
Supply voltage range		V _{CC}	2.4	-	5.5	V
Dynamic supply current						
Idle, dark ambient	$\begin{array}{l} \text{SD} = \text{low} \ (< 0.8 \ \text{V}), \\ \text{E}_{\text{eamb}} = 0 \ \text{klx}, \\ \text{E}_{\text{e}} < 4 \ \text{mW/m}^2 \\ \text{-25 \ }^\circ\text{C} \leq \text{T} \leq +85 \ ^\circ\text{C} \end{array}$	Icc	-	90	130	μA
Idle, dark ambient	SD = low (< 0.8 V), E _{eamb} = 0 klx, E _e < 4 mW/m ² T = +25 °C	I _{CC}	-	75	-	μA
Peak supply current during transmission	SD = low, TXD = high	I _{ccpk}	-	2	3	mA
Shutdown supply current dark ambient	SD = high (> V _{CC} - 0.5 V), T = 25 °C, E _e = 0 klx	I _{SD}	-	-	0.1	μA
Shutdown supply current, dark ambient	SD = high (> V _{CC} - 0.5 V), -25 °C ≤ T ≤ +85 °C	I _{SD}	-	-	1	μA
Operating temperature range		T _A	-30	-	+85	°C
Input voltage low (TXD, SD)		VIL	-0.5	-	0.5	V
Input voltage high	$V_{CC} = 2.4 \text{ V} \text{ to } 3.6 \text{ V}$	V _{IH}	V _{CC} - 0.5	-	6	V
Input voltage threshold SD	$V_{CC} = 2.4 \text{ V to } 3.6 \text{ V}$		0.9	1.35	1.8	V
Output voltage low	$V_{CC} = 2.4 \text{ V to } 3.6 \text{ V}$ $C_{LOAD} = 15 \text{ pF}$	V _{OL}	-0.5	-	V _{CC} x 0.15	V
Output voltage high	V_{CC} = 2.4 V to 3.6 V C_{LOAD} = 15 pF	V _{OH}	V _{CC} x 0.8	-	V _{CC} + 0.5	V
RXD to V_{CC} pull-up impedance	$\begin{array}{c} \text{SD} = \text{V}_{\text{CC}} \\ \text{V}_{\text{CC}} = 2.4 \text{ V to 5 V} \end{array}$	R _{RXD}	-	500	-	kΩ
Input capacitance (TXD, SD)		Cı	-	-	6	pF

Note

• Typical values are for design aid only, not guaranteed nor subject to production testing



PARAMETER	TEST CONDITIONS	SYMBOL	MIN.	TYP.	MAX.	UNIT
RECEIVER						1
Sensitivity: minimum irradiance E_e in angular range $^{(1)(2)}$	9.6 kbit/s to 115.2 kbit/s $\lambda = 850$ nm to 900 nm	E _e	-	40 (4)	81 (8.1)	mW/m² (μW/cm²)
Maximum irradiance E _e in angular range	λ = 850 nm to 900 nm	E _e	5 (500)	-	-	kW/m ² (mW/cm ²)
No receiver output input irradiance ⁽³⁾	According to IrDA IrPHY 1.4, appendix A1, fluorescent light specification	E _e	4 (0.4)	-	-	mW/m² (µW/cm²)
Rise time of output signal	10 % to 90 %, C _L = 15 pF	t _{r (RXD)}	20	-	100	ns
Fall time of output signal	90 % to 10 %, C _L = 15 pF	t _{f (RXD)}	20	-	100	ns
RXD pulse width of outputInput pulse widthsignal, 50 % (4)1.63 μs		t _{PW}	1.7	2	2.9	μs
Receiver start up time	Power on delay		-	100	150	μs
Latency		tL	-	50	200	μs
TRANSMITTER						
IRED operating current, current controlled	The IRED current is internally controlled but also can be reduced by an external resistor R1	ID	200	300	400	mA
Forward voltage of built-in IRED	I _F = 300 mA	V _F	1.4	1.8	1.9	V
Output leakage IRED current	T _{amb} = 85 °C	I _{IRED}	-	-	1	μA
Output radiant intensity ⁽⁵⁾	$\begin{array}{l} a=0^\circ, 15^\circ, TXD=high, SD=low,\\ V_{CC1}=3 \; V, V_{CC2}=3 \; V, R1=30 \; \Omega\\ (resulting in about 50 \; mA \; drive\\ \; current) \end{array}$	l _e	5	10	25	mW/sr
Output radiant intensity ⁽⁵⁾	$ \begin{array}{l} a = 0^{\circ}, 15^{\circ}, TXD = high, SD = low, \\ V_{CC1} = 3 V, V_{CC2} = 3 V, R1 = 0 \Omega, \\ I_F = 300 mA \end{array} $	l _e	30	65	150	mW/sr
Output radiant intensity ⁽⁵⁾	$V_{CC1} = 5 V$, $a = 0^{\circ}$, 15° TXD = low or SD = high (receiver is inactive as long as SD = high)	l _e	-	-	0.04	mW/sr
Saturation voltage of IRED driver	$V_{CC} = 3 \text{ V}, \text{ I}_{F} = 50 \text{ mA}$	V _{CEsat}	-	0.4	-	V
Peak - emission wavelength		λ _p	880	886	900	nm
Spectral bandwidth		Δλ	-	45	-	nm
Optical rise time, optical fall time		t _{ropt} , t _{fopt}	20	-	100	ns
Optical output pulse duration	Input pulse width t < 30 μs Input pulse width t ³ 30 μs	t _{opt} t _{opt}	30	t 50	300	μs μs
Optical output pulse duration	Input pulse width t = 1.63 µs	t _{opt}	1.45	1.61	2.2	μs
Optical overshoot			-	-	20	%

Notes

• Typical values are for design aid only, not guaranteed nor subject to production testing

(2) This parameter reflects the backlight test of the IrDA physical layer specification to guarantee immunity against light from fluorescent lamps.
 (3) IrDA sensitivity definition: minimum irradiance E_e in angular range, power per unit area. The receiver must meet the BER specification while the source is operating at the minimum intensity in angular range into the minimum half-angular range at the maximum link length

(4) Maximum irradiance E_e in angular range, power per unit area. The optical delivered to the detector by a source operating at the maximum intensity in angular range at minimum link length must not cause receiver overdrive distortion and possible related link errors. If placed at the active output interface reference plane of the transmitter, the receiver must meet its bit error ratio (BER) specification. For more definitions see the document "Symbols and Terminology" on the Vishay website

⁽⁵⁾ RXD output is edge triggered by the rising edge of the optical input signal. The output pulse duration is independent of the input pulse duration

(6) The radiant intensity can be adjusted by the external current limiting resistor to adapt the intensity to the desired value. The given value is for minimum current consumption. This transceiver can be adapted to > 50 cm operation by increasing the current to > 200 mA, e.g. operating the transceiver without current control resistor (i.e. $R1 = 0 \Omega$) and using the internal current control

Rev. 1.9, 29-Apr-2019

5

TFBS4650



Vishay Semiconductors

TRUTH TABLE

	INPUTS						
SD	SD TXD OPTICAL INPUT IRRADIANCE mW/m ²			TRANSMITTER			
High	x	x	Tri-state floating with a weak pull-up to the supply voltage	0			
Low	High	x	Low (echo on)	l _e			
Low	High > 50 µs	x	High	0			
Low	Low	< 4	High	0			
Low	Low	> min. irradiance E _e < max. irradiance E _e	Low (active)	0			
Low	Low	> max. irradiance E _e	x	0			

RECOMMENDED CIRCUIT DIAGRAM

Operated at a clean low impedance power supply the TFBS4650 needs only one additional external component when the IRED drive current should be minimized for minimum current consumption according the low power IrDA standard. When combined operation in IrDA and remote control is intended no current limiting resistor is recommended.

However, depending on the entire system design and board layout, additional components may be required (see Fig. 1). When long wires are used for bench tests, the capacitors are mandatory for testing rise / fall time correctly.




Fig. 1 - Recommended Application Circuit

The capacitor C1 is buffering the supply voltage V_{CC2} and eliminates the inductance of the power supply line. This one should be a small ceramic version or other fast capacitor to guarantee the fast rise time of the IRED current. The resistor R1 is necessary for controlling the IRED drive current when the internally controlled current is too high for the application.

Vishay transceivers integrate a sensitive receiver and a built-in power driver. The combination of both needs a careful circuit board layout. The use of thin, long, resistive and inductive wiring should be avoided. The inputs (TXD, SD) and the output RXD should be directly (DC) coupled to the I/O circuit.

The capacitor C2 combined with the resistor R2 is the low pass filter for smoothing the supply voltage.

As already stated above R2, C1 and C2 are optional and depend on the quality of the supply voltages V_{CCx} and injected noise. An unstable power supply with dropping

voltage during transmission may reduce the sensitivity (and transmission range) of the transceiver.

The placement of these parts is critical. It is strongly recommended to position C2 as close as possible to the transceiver power supply pins.

When connecting the described circuit to the power supply, low impedance wiring should be used.

In case of extended wiring the inductance of the power supply can cause dynamically a voltage drop at V_{CC2}. Often some power supplies are not able to follow the fast current is rise time. In that case another 10 μF cap at V_{CC2} will be helpful.

Keep in mind that basic RF-design rules for circuit design should be taken into account. Especially longer signal lines should not be used without termination. See e.g. "The Art of Electronics" Paul Horowitz, Wienfield Hill, 1989, Cambridge University Press, ISBN: 0521370957.

RECOMMENDED APPLICATION CIRCUIT COMPONENTS						
COMPONENT RECOMMENDED VALUE						
C1, C2	0.1 μF, Ceramic Vishay part# VJ 1206 Y 104 J XXMT					
R1	See table below					
R2	47 Ω , 0.125 W (V _{CC1} = 3 V)					

RECOMMENDED RESISTOR R1 (Ω)					
V _{CC2} MINIMIZED CURRENT CONSUMPTION (V) IrDA LOW POWER COMPLIANT					
2.7	24				
3	30				
3.3	36				

Document Number: 84672

For technical questions within your region: irdasupportAM@vishay.com, irdasupportAP@vishay.com, irdasupportEU@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Rev. 1.9, 29-Apr-2019





RECOMMENDED SOLDER PROFILES

Solder Profile for Sn/Pb Soldering




Fig. 2 - Recommended Solder Profile for Sn/Pb Soldering

Lead (Pb)-free, Recommended Solder Profile

The TFBS4650 is a lead (Pb)-free transceiver and qualified for lead (Pb)-free processing. For lead (Pb)-free solder paste like $Sn_{(3.0-4.0)}Ag_{(0.5-0.9)}Cu$, there are two standard reflow profiles: Ramp-Soak-Spike (RSS) and Ramp-To-Spike (RTS). The Ramp-Soak-Spike profile was developed primarily for reflow ovens heated by infrared radiation. With widespread use of forced convection reflow ovens the Ramp-To-Spike profile is used increasingly. Shown in Fig. 3 is Vishay's recommended profiles for use with the TFBS4650 transceivers. For more details please refer to the application note "SMD Assembly Instructions".

Wave Soldering

For TFDUxxxx and TFBSxxxx transceiver devices wave soldering is not recommended.

Manual Soldering

Manual soldering is the standard method for lab use. However, for a production process it cannot be recommended because the risk of damage is highly dependent on the experience of the operator. Nevertheless, we added a chapter to the above mentioned application note, describing manual soldering and desoldering.

Storage

The storage and drying processes for all Vishay transceivers (TFDUxxxx and TFBSxxx) are equivalent to MSL4.

The data for the drying procedure is given on labels on the packing and also in the application note "Taping, Labeling, Storage and Packing".





Fig. 3 - Solder Profile, RSS Recommendation



PACKAGE DIMENSIONS in millimeters








Fig. 5 - TFBS4650 Soldering Footprint, Tolerance \pm 0.2 mm, if not otherwise mentioned


 Rev. 1.9, 29-Apr-2019
 8
 Document Number: 84672

 For technical questions within your region: irdasupportAM@vishay.com, irdasupportAP@vishay.com, irdasupportEU@vishay.com
 THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000






REEL DIMENSIONS in millimeters



TAPE WIDTH	A MAX.	N	W ₁ MIN.	W ₂ MAX.	W ₃ MIN.	W ₃ MAX.
(mm)	(mm)	(mm)	(mm)	(mm)	(mm)	(mm)
16	330	50	16.4	22.4	15.9	19.4




TAPE DIMENSIONS FOR TR1 AND TR3 in millimeters





TAPE DIMENSIONS FOR TR4 in millimeters





Drawing-No.: 9.700-5331.01-4 Issue: 2; 27.05.08 20872



technical drawings according to DIN specifications

TAPE DIMENSIONS FOR TT3 in millimeters





Drawing-No.: 9.700-5340.01-4 Issue: 1; 15.01.09 21663



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.