


#### ISO9001 & ISO14001 & TS16949 CHILISIN ELECTRONICS CORP.

## RoHS & Halogen Free & REACH Compliance.

## SPECIFICATION FOR APPROVAL

Customer :			國益興業	<b>4</b>
Customer P/N:				
Drawing No:				
Quantity:	Х	Pcs.	Date :	2016/12/22
Chilisin P/N:		MHCH	 IL201610A-2	2R2M-Q8A
	SP	ECIFIC	ATION	
	A(	CCEPTE	D BY:	
COMPONENT ENGINEER				
ELECTRICAL ENGINEER				
MECHANICAL ENGINEER				
APPROVED				
REJECTED				
奇力新電子股份有限公司 Chilisin Electronics Corp No. 29, Alley 301, Tehhsin Rd., Hukou,Hsinchu 303, Taiwan TEL: +886-3-599-2646 FAX: +886-3-599-9176 E-mail: sales@chilisin.com.tw http://www.chilisin.com.tw		Chili No. Qing TEL FAX	78, Puxing Rd., Yu	ongguan) Co., Ltd. uliangwei Administration Area, an City, Guangdong,China )251~3 0232
奇力新電子(河南)有限公司 Chilisin Electronics (Henan) Co. XiuWu Xian, industry gathering a JiaoZuo, Henan China Postal Code:454350 TEL:+86-391-717-0666	., Ltd.	SUZ No.1 Suzh Post TEL: FAX	N奇益新電子有 ZHOU QI YIXIN Ele 143,Song Shan Rd hou,China tal Code:215129 ::+86-512-6841-23 (:+86-512-6841-23 ail:suzhou@chili	ectronics Co., Ltd. d., Suzhou New District, s50 856
Drawn by 脹 <b>鈺雯 chang.yuwen</b>		Checked 还 <b>雯 chang</b>	-	Approved by 鍾瑞民 <b>jacky.chung</b>

- 1 Scope: This specification applies to Molding power inductors
- 2 Part Numbering:



3 Rating:

Operating Temperature:  $-4.0 \,^{\circ}\text{C} \sim 1.2.5 \,^{\circ}\text{C}$  (Including self - temperature rise)

Storage Temperature:  $-4.0 \,^{\circ}\text{C} \sim 1.2.5 \,^{\circ}\text{C}$  (after PCB)

 $-5\,^{\circ}\mathrm{C} \sim 3\,\,5\,^{\circ}\mathrm{C}$ , Humidity  $4\,\,5\,\% \sim 8\,\,5\,\%$  (before PCB)

4 Marking:

No Marking

## 5 Standard Testing Condition


Unless otherwise specified		In case of doubt
Temperature	Ordinary Temperature(15 to 35°ℂ)	20 to 30℃
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH



#### ISO9001 & ISO14001 & TS16949 CHILISIN ELECTRONICS CORP.

## **MHCHL201610A Series Specification**

## 6 Configuration and Dimensions:



Dimensions in mm		
TYPE	MHCHL201610A	
A	2.0±0.2	
В	1.6±0.2	
С	1.0 Max.	
D	0.5±0.3	

## 7 Electrical Characteristics:

Part No.	Inductance (uH)	Tolerance (±%)	Test Freq.	Irms(A) Max.(Typ)	Isat(A) Max.(Typ)	RDC(mΩ) Max.(Typ)	
MHCHL201610A-2R2M-Q8A	2.2	20	2MHz.0.2V	2.0(2.2)	2.4(2.7)	120(112)	


#### NOTE:

- 1.Operating temperature range  $-~4~0~^{\circ}\text{C} \sim 1~2~5~^{\circ}\text{C}$  (Including self temperature rise)
- 2.Isat for Inductance drop 30% from its value without current.
- 4.All test data is referenced to 25°C ambient
- 5. Absolute maximum voltage 25VDC



## 8 MHCHL201610A Series

### 8.1 Construction:



#### 8.2 Material List:

No	Part	Material
1	Core	Metal Powder
2	Wire	Copper wire
3	Sputter/Plating	Cu
4	Silver Electrode	Ag
S	Plating	Ni
6	Plating	Sn



#### ISO9001 & ISO14001 & TS16949 CHILISIN ELECTRONICS CORP.

# MHCHL201610A Series Specification 9 Reliability Of Molding power inductors


#### 1-1.Mechanical Performance

No	Item	Specification	Test Method
1-1-1	Flexure Strength	The forces applied on the right conditions must not damage the terminal electrode and the metal body	Test device shall be soldered on the substrate Substrate Dimension: 100x40x1.6mm Deflection: 2.0mm Keeping Time: 30sec
1-1-2	Vibration	Appearance:No damage (for microscope of CASTOR MZ-45 20X) Inductance change shall be within ±20%	Test device shall be soldered on the substrate Oscillation Frequency: 10 to 55 to 10Hz for 1min Amplitude: 1.5mm Time: 2hrs for each axis (X, Y & Z), total 6hrs
1-1-3	Resistance to Soldering Heat	l · ·	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5(Pb-Free) Solder Temperature: 260±5°C Immersion Time: 10±1sec
1-1-4	Solder ability	The electrodes shall be at least 95% covered with new solder coating	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5(Pb-Free) Solder Temperature: 245±5°C Immersion Time: 4±1sec
1-1-5	Terminal Strength Test	No split termination Chip F Mounting Pad	Test device shall be soldered on the substrate, then apply a force in the direction of the arrow. Force: 5N Keeping Time: 10±1sec

#### 1-2 Environmental Performance

No	Item	Specification		Test Method	
	Temperature Cycle	Appearance: No damage	One cycle:		
		Inductance:within±20% of	Step	Temperature (°ℂ)	Time (min)
		initial value	1	-40±3	30
			2	25±2	3
			3	125±3	30
			4	25±2	3
			Total: 100d	cycles	
			Measured	after exposure in the room co	ondition for 24hrs
1-2-2	Humidity Resistance	Temperature: 60±2℃			
			Relative H	umidity: 90 ~ 95% / Time: 500	Ohrs
			Measured	after exposure in the room co	ondition for 24hrs
1-2-3	High	Temperature: 85±3°ℂ			
	Temperature Resistance		Relative H	umidity: 0% / Time: 500hrs	
			Measured	after exposure in the room co	ondition for 24hrs
1-2-4	Low		Temperatu	ıre: -40±3°ℂ	
	Temperature Resistance		Relative Humidity: 0% / Time: 500hrs		
			Measured	after exposure in the room co	ondition for 24hrs





## Lead-Free(LF) 標準溫度分析範圍

Refer to J-STD-020C

管制項目 Item.	升溫區 Ramp-up	預熱區 Pre-heatimg	迴焊區 Reflow	Peak Temp	冷卻區 Cooling
温度範圍 Temp.scope	R.T. ~150°℃	150°C ~ 200°C	217℃	260±5°ℂ	Peak Temp. ~ 150°C
標準時間 Time spec.	-	60 ~ 180 sec	60 ~ 150 sec	20 ~ 40 sec	3 <del></del> 3
實際時間 Time result		75 ~ 100 sec	90 ~ 120 sec	20 ~ 35 sec	8-3

#### NOTE:

- 1. Re-flow possible times: within 2 times
- 2. Nitrogen adopted is recommended while in re-flow



## 10 Packaging:

### 10.1 Packaging -Cover Tape


The force for tearing off cover tape is 10 to 100 grams in the arrow direction.



### 10.2 Packaging Quantity

TYPE	PCS/REEL
MHCHL201610A	3000


#### 10.3 Reel Dimensions






## 10 Packaging:

#### 10.4 Tape Dimensions in mm



## 11 Recommended Land Pattern:



## 12 Note:

- 1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
- 2. Do not knock nor drop.
- 3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose,under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
- 4. Please keep the distance between transformer/coil and other components (refer to the standard IEC 950)
- 5. After manufacturing process, there might be slight irregular shape on the edge of the products, and it's a normal phenomenon that can be neglected
- 6. The moisture sensitivity level (MSL) of products is classified as level 1.





