Effective June 2017 Supersedes June 2011

FP1109 High frequency, high current power inductors



Product features

- 11.2 x 11.2 x 9.0mm maximum surface mount package
- Ferrite core material
- High current carrying capacity, low core losses
- Controlled DCR tolerance for sensing circuits
- Inductance range from 205nH to 950nH
- Current range from 11.5 to 69 amps
- Frequency range up to 2MHz

Applications

- Multi-phase regulators
- Voltage Regulator Module (VRM)
- Desktop and server VRMs and EVRDs
- Data networking and storage systems
- · Graphics cards and battery power systems
- Point-of-load modules
- DCR sensing

Environmental data

- Storage temperature range (component): -40 °C to +125 °C
- Operating temperature range: -40 °C to +125 °C (ambient plus self-temperature rise)
- Solder reflow temperature: J-STD-020 (latest revision) compliant





			Product	Specifications			
Part Number ⁷	$0CL^{1} \pm 20\%$ (nH)	FLL ² Min. (nH)	I _{rms} ³ (Amps)	I _{sat} 1⁴ @ 25°C (Amps)	I _{sat} 2 ⁵ @ 125°C (Amps)	DCR (mΩ) @ 20°C	K-factor ⁶
FP1109-R20-R	205	122		69	52		233
FP1109-R23-R	247	147		55	41		233
FP1109-R27-R	270	160	1	51	38		233
FP1109-R33-R	311	185	35	44	33	0.42 ±10%	233
FP1109-R47-R	463	275	1	27	20		233
FP1109-R58-R	548	325]	22.5	17		233
FP1109-1R0-R	950	565		11.5	8.5		233

1 Open Circuit Inductance (OCL) Test Parameters: 100kHz, 0.10V $_{\rm rms}$, 0.0Adc

2 Full Load Inductance (FLL) Test Parameters: 100kHz, 0.1V_{rms}, I_{sat}1

3 I_{rms}: DC current for an approximate temperature rise of 40°C without core loss. Derating is necessary for AC currents. PCB pad layout, trace thickness and width, air-flow and proximity of other heat generating components will affect the temperature rise. It is recommended the part temperature not exceed 125°C under worst case operating conditions verified in the end application. 4 I_{sat} 1: Peak current for approximately 30% rolloff at +25°C.

5 $~\mbox{I}_{sat}2$: Peak current for approximately 30% rolloff at +125°C.

6 K-factor: Used to determine B_{p-p} for core loss (see graph). $B_{p-p} = K * L * \Delta I * 10^{-3}$, B_{p-p} : (Gauss),

K: (K-factor from table), L: (inductance in nH), △I (peak-to-peak ripple current in amps).

7 Part Number Definition: FP1109-xxx-R


• FP1109 = Product code and size

• xxx= Inductance value in μ H, R = decimal point. If no "R" is present, then

third character = # of zeros

• "-R" suffix = RoHS compliant


Dimensions- mm



Part Marking: FP1109

xxx = Inductance value in μ H. (R = Decimal point). If no "R" is present, then last character is # of zeros wwllyy = Date code R = Revision level


Packaging information - mm




Supplied in tape-and-reel packaging, 350 parts per reel, 13" diameter reel.

FP1109 High frequency, high current power inductor

Temperature rise vs total loss



Core loss vs Bp-p








Table 1 Ctandard CpDb Calder (T.)

Solder Reflow Profile




Table 1 - Star	le 1 - Standard SnPb Solder (I _C)		
	Volume	Volume	
Package	mm ³	mm ³	
Thickness	<350	≥350	
<2.5mm	235°C	220°C	
≥2.5mm	220°C	220°C	
Table 2 - Lea	d (Pb) Fre	e Solder (T _C)	
Table 2 - Lea	d (Pb) Fre Volume	e Solder (T _C) Volume	Volume
Table 2 - Lea Package		• •	Volume mm ³
	Volume	Volume	
Package	Volume mm ³	Volume mm ³	mm ³
Package Thickness	Volume mm ³ <350 260°C	Volume mm ³ 350 - 2000	mm ³ >2000

Reference JDEC J-STD-020

Profile Feature		Standard SnPb Solder	Lead (Pb) Free Solder	
Preheat and Soak	 Temperature min. (T_{smin}) 	100°C	150°C	
	 Temperature max. (T_{smax}) 	150°C	200°C	
	 Time (T_{smin} to T_{smax}) (t_s) 	60-120 Seconds	60-120 Seconds	
Average ramp up rate T _{smax} to T _p		3°C/ Second Max.	3°C/ Second Max.	
Liquidous temperature (TL)		183°C	217°C	
Time at liquidous (tL)		60-150 Seconds	60-150 Seconds	
Peak package body temperature (Tp)*		Table 1	Table 2	
Time $(t_p)^{**}$ within 5 °C of the specified classification temperature (T_c)		20 Seconds**	30 Seconds**	
Average ramp-down rate (Tp to Tsmax)		6°C/ Second Max.	6°C/ Second Max.	
Time 25°C to Peak Temperature		6 Minutes Max.	8 Minutes Max.	

 * Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

** Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton Electronics Division 1000 Eaton Boulevard Cleveland, OH 44122 United States www.eaton.com/electronics

© 2017 Eaton All Rights Reserved Printed in USA Publication No. 4350 BU-SB11642 June 2017

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

