

GS2MA

2AMPS. GLASS PASSIVATED SURFACE MOUNT RECTIFIERS


FEATURE

- . High current capability
- . Low forward voltage drop
- . Low power loss, high efficiency
- . High surge capability
- . High temperature soldering guaranteed:
- 260°C/10 seconds at terminals.
- . For surface mounted application.
- . Easy pick and place.

MECHANICAL DATA

. Case: Molded plastic

- . Epoxy: UL94V-0 rate flame retardant
- . Lead: MIL-STD- 202E, Method 208 guaranteed
- . Polarity: Color band denotes cathode end
- . Packaging:12mm tape per EIA STD RS-481
- . Mounting position: Any



NO	Measurement
A	1.98~2.3
В	1.35~1.6
С	0.2MAX
D	2.4~2.9
Е	3.8~4.6
F	0.8~1.8
G	4.8~5.80

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

(single-phase, half-wave, 60HZ, resistive or inductive load rating at 25°C, unless otherwise stated)

Type Number	SYM BOL	GS2MA	units
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	1000	V
Maximum RMS Voltage	V_{RMS}	700	V
Maximum DC blocking Voltage	V _{DC}	1000	V
Maximum Average Forward Rectified Current at T _A =55°C	$I_{F(AV)}$	2.0	A
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load (JEDEC method)	I _{FSM}	50.0	A
Maximum Forward Voltage at 2.0A DC	V_F	1.1	V
Maximum DC Reverse Current Ta = 25°C at rated DC blocking voltage Ta = 125°C	I_R	5.0 125.0	μА
Typical Junction Capacitance (Note1)	Cj	30	pF
Typical Thermal Resistance (Note 2)	$R_{(JA)}$	50	°C/W
Storage Temperature	T _{STG}	-55 to +150	°C
Operation Junction Temperature	T_J	-55 to +150	°C

Note

- 1. Measured at 1.0 MHz and applied reverse voltage of 4.0Vdc
- 2. Measured on P.C.Board with 0.2×0.2"(5.0×5.0mm)Copper Pad Areas.

RATING AND CHARACTERISTIC CURVES (GS2MA)




FIG.2-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG.3-MAXIMUN NON-REPETITIVE FORWARD SURGE CURRENT




FIG4-TYPICAL REVERSE CHARACTERISTICS

