
APPROVAL SHEET

Customer Name :	
Customer P/N :	
Frequency :	16.000000 MHz
Aker Approved P/N:	CXA-016000-2D7D40
Aker MPN :	CXA-016000-2D7D40
Rev. :	1
ISSUE DATE :	Mar.1.2018



AKER TECHNOLOGY CO., LTD.

ADDRESS : NO 11-3, Jianguo Rd., T.E.P.Z , Tanzi Dist., Taichung City 427, Taiwan.

TEL: 886-4-25335978 FAX: 886-4-25336011

Web: www.aker.com.tw

RoHS compliant



CUST. P/N :		
Aker Approved P/N :	 CXA-016000)-2D7D40
APPROVED :	Xtal	SHEET : 1 of 9
PREPARED :	 Kiku	REV. : 1

Dov	Data	Dovisor	Poviso contents
Rev.	Date	Reviser	Revise contents
1	2018/3/1	Kiku	Initial Released
L	1	<u> </u>	



CUST. P/N	:		
Aker Approved P/N	•	CXA-016000)-2D7D40
APPROVED	•	Xtal	SHEET : 2 of 9
PREPARED	:	Kiku	REV. : 1

SMD CRYSTAL SPECIFICATION

1. ELECTRICAL CHARACTERISTICS

■ Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions for making measurement and tests are as follow:

Ambient temperature : 25 ± 5 °CRelative humidity: $40\%\sim70\%$

If there is any doubt about the results, measurement shall be made within the following limits:

Ambient temperature : 25±3 ℃


Relative humidity : 40%~70%

- AKER Model : CXA-221
- Oscillation Model : Fundamental
- Cutting Model : AT CUT
- Measurement Equipment : 350A(Measured FL)
- Insulation Resistance : More than 500M ohms at DC 100V

		Electrical Spec			-		
Parameters	Symbol	Min.	Тур.	Max.	Units.	Notes	
Nominal Frequency	FL	1	6.00000	0	MHz		
Frequency Tolerance			±20		ppm	at $25^{\circ}C \pm 3^{\circ}C$	
Frequency Stability			±20		ppm	Operating Temp (Refer 25°C)	
Load Capacitance	CL		12		pF		
Aging			± 3		ppm	Year	
Operating Temperature		-40	\sim	85	°C		
Storage Temperature Range		-55	\sim	125	°C		
Drive Level	DL			100	uW		
Effective Resistance Rr	Rr			100	Ω		
Shunt Capacitance	C0	3		pF			
Please kindly be noted that A	KER DO NO	T guarant	ee parts o	quality wi	nich invol	ves human security application.	

	CUST. P/N			
	Aker Approved P	/N :	CXA-01600	0-2D7D40
	APPROVED	:	Xtal	SHEET : 3 of 9
Accurate Kinetic Energy	PREPARED	:	Kiku	REV. : 1

2. MARKING :




Year/Month Code : Please make refer to following tables.


NOTI	E1:						
CODE	CL	CODE	CL	CODE	CL	CODE	CL
0	0pF	9	14pF	K	9.5pF	U	8.5pF
1	16pF	A	32 pF	L	19.5pF	V	24pF
2	22pF	В	27pF	М	21.5pF	W	4pF
3	15pF	C	8pF	N	33pF	X	39pF
4	20 pF	D	37pF	P	7pF	Y	26pF
5	30pF	E	25 pF	Q	15.5pF	Ζ	7.2pF
6	18pF	F	35pF	R	12.5pF	a	17pF
7	12pF	G	13pF	S	11pF	b	9.85pF
8	10pF	H	9pF	Т	6pF	đ	ĴрF


	2007	2008	2009	2010
Year	2011	2012	2013	2014
	2015	2016	2017	2018
Month	2019	2020	2021	2022
	2023	2024	2025	2026
JAN	А	N	а	n
FEB	В	Р	b	p
MAR	С	Q	с	q
APR	D	R	d	r
MAY	E	S	е	S
JUN	F	Т	f	t
JUL	G	U	g	u
AUG	Н	v	h	ν
SEP	J	W	j	w
OCT	K	Х	k	x
NOV	L	Y	1	у
DEC	М	Z	m	Z

(Unit:mm)


3. DIMENSION :








< SUGGESTED LAYOUT>





CUST. P/N :		
Aker Approved P/N :	CXA-01600	0-2D7D40
APPROVED :	Xtal	SHEET: 4 of 9
PREPARED :	Kiku	REV. : 1

4. STRUCTURE ILLUSTRATION



	COMPONENTS	MATERIALS		MPONENTS	MATERIALS
А	Base (Package)	Ceramic(Al2O3)+Kovar(Fe/Co/Ni)	D	Electrode	Cr / Ag
В	Conductive adhesive	Ag / Silicon resin	Е	Lid	Fe/Co/Ni
С	Crystal blank	SiO2			




D40
ET : 5 of 9
. : 1

5. PACKING :


TAPE SPECIFICATION


(Unit:mm)




OUTLINE DIMENSION

(Unit:mm)









CUST. P/N :			
Aker Approved P/N	:	CXA-016000	0-2D7D40
APPROVED	:	Xtal	SHEET : 8 of 9
PREPARED	:	Kiku	REV. : 1

9. MECHANICAL PERFORMANCE

TEST ITEMS	TEST METHODS AND TEST CONDITION	PERFORMANCE		
9.1 Drop Test	The specimen is measured for its frequency and resistance before the test. It is then dropped from a hight of 100 cm or more as a free fall object onto a hard wooden plate of 30mm or more in thickness. (in accordance with JIS-C0044)			
9.2 Vibration Test	The specimen is measured for its frequency and resistance before the test. Most them into X,Y and Z axes, respectively, for the vibration test. Vibration condition: Frequency range ; $20 \sim 2000$ HZ Peak to peak amplitude : 1.52 mm Peak acceleration : $20G$ Sweep time : 20 minute / axis Pendicular total test time : 4 hours	To satisfy the electrical performance .		
9.3 Resistance to Soldering Test	(in accordance with MIL-STD-883F : 2007.3) The specimen is measured for its frequency and resistance before the test. Place the specimen on the belt of the converynace and let it pass through the reflow with the presetted temperature condition. After passing twice the reflow place, the specimen under the referee condition for -~2 hours and then measure its electrical performance. Temperature Condition of IR Simulation: The temperature range of the preheated section is setted at $150 \sim 180^{\circ}$ C for $60 \sim 120$ sec. For the next section the temperature range is setted at $217 \sim 260^{\circ}$ C for $45 \sim 90$ sec. and within this time range the specimen should be able to sustain at the peak temperature, $260+/-3^{\circ}$ C , for 10 sec long. (in accordance with JESD22-B106-B)			
9.4 Fine Leak Test	 Place the specimen in a pressurized container and pressurize it with the detection gas (mixed gas consisting of 95% or more helium) for at least 2 hours. Complete the measurement of the concentration of helium within 30 min after taking it out from the pressurized container. (in accordance with MIL-STD-883F : 1014.11) 	Less than 1.0 * 10 ⁻⁸ atm .c.c. / sec, Helium		
	The referee condition . Temperature 25 ± 2 °C Humidity $44 \sim 55$ % Pressure $86 \sim 106$ kPa (in accordance with MIL-STD-883E : 1014. 9)			



CUST. P/N	•		
Aker Approved P/N :		CXA-016000-2D7D40	
APPROVED	:	Xtal	SHEET : 9 of 9
PREPARED	:	Kiku	REV. : 1

10. CLIMATIC RESISTANCE

TEST ITEMS	TEST METHODS AND TEST CONDITION	PERFORMANCE					
10.1 Low Temp Exposure Test	The specimen is measured for its frequency and resistance before the test . Place the specimen in the chamber and kept it at the temperature of $-40 \pm 3^{\circ}$ C for 168 ± 6 hours . Take the specimen out of the chamber and measure itselectrical performance after leaving $1 \sim 2$ hours under the referee condition. (in accordance with JIS-C0020)						
10.2 Aging Test	The specimen is measured for its frequency and resistance before the test . Place the specimen in the testing chamber and keep it at the temperature of $+125 \pm 3$ °C for 720 ± 48 hours. And then take the specimen out of the chamber and measure its electrical performance after leaving for $1 \sim 2$ hours under the referee condition . (in accordance with JIS-C0021)	To satisfy the electrical performance .					
10.3 High Temperature & High Humidty	The specimen is measured for its frequency and resistance before the test . Place the specimen in the testing chamber and kept it at the temperature of $+85 \pm 5$ °C and humidity of 85 ± 5 % for 168 ± 6 hours.and then take the specimen out and measure its electrical performance after leaving for $1\sim 2$ hours under the referee condition. (in accordance with MIL-STD-883F : 1004.7)						
10.4 Temperature Cycle Test	The specimen is measured for its frequency and resistance before the test . Subject the specimen to the 100 cycles of temperature ranges stated below . High temp . + $125 \pm 3 \degree C$ ($15\pm 3 \min$). $2 \sim 3 \min$. $2 \sim 3 \min$. Low temp $55 \pm 3 \degree C$ ($15\pm 3 \min$). Measure its electrical performance after leaving it for $1 \sim 2$ hours under the referee condition . (in accordance with MIL-STD-883F : 1010.8)						