# APPROVAL SHEET

| Customer Name    | :    |                 |     |
|------------------|------|-----------------|-----|
| Customer P/N     | :    |                 |     |
| Frequency        | :    | 16.000000       | MHz |
| Aker Approved P/ | ′N : | CXA-016000-7B6A | 60  |
| Aker MPN         | :    | CXA-016000-7B6A | 60  |
| Rev.             | :    | 1               |     |
| ISSUE DATE       | :    | Jan.25.2019     |     |

| APPROVED        | CHECKED | PREPARED |
|-----------------|---------|----------|
| (in             |         | Kiku     |
| APPROVED BY CUS | STOMER  |          |
|                 |         |          |
|                 |         |          |

# AKER TECHNOLOGY CO., LTD.

ADDRESS : NO 11-3, Jianguo Rd., T.E.P.Z , Tanzi Dist., Taichung City 427, Taiwan.

TEL: 886-4-25335978 FAX: 886-4-25336011

Web: www.aker.com.tw

**RoHS compliant** 

| CUST. P/N :         |                             |  |
|---------------------|-----------------------------|--|
| Aker Approved P/N : | CXA-01600                   |  |
|                     | Tin                         | SHEET : 1 of 9   |
| PREPARED :          | Kiku                        | <b>REV</b> . : 1   |
|                     |                             |  |
|                     |                             |  |
| ser                 | Revise conten               | te   |
|                     |                             |  |
|                     | Initial Release             | 20   |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
|                     |                             |  |
| i                   | Aker Approved P/N:APPROVED: | Aker Approved P/N : CXA-01600   APPROVED : Tin   PREPARED : Kiku   ser Revise conten |



| CUST. P/N :         |           |                |
|---------------------|-----------|----------------|
| Aker Approved P/N : | CXA-01600 | 0-7B6A60       |
| APPROVED :          | Tin       | SHEET : 2 of 9 |
| PREPARED :          | Kiku      | REV. : 1       |

# **SMD CRYSTAL SPECIFICATION**

#### **1. ELECTRICAL CHARACTERISTICS**

■ Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions for making measurement and tests are as follow :

Ambient temperature : 25±5 ℃

Relative humidity : 40%~70%

If there is any doubt about the results, measurement shall be made within the following limits:

Ambient temperature : 25±3 °C


Relative humidity : 40%~70%


- AKER Model : CXA-751
- Oscillation Model : Fundamental
- Cutting Model : AT CUT
- Measurement Equipment : 350A(Measured FL)
- Insulation Resistance : More than 500M ohms at DC 100V

|                           |        | Electrical Spec |          |      |        |                                   |
|---------------------------|--------|-----------------|----------|------|--------|-----------------------------------|
| Parameters                | Symbol | Min.            | Тур.     | Max. | Units. | Notes                             |
| Nominal Frequency         | FL     | 1               | 6.000000 | )    | MHz    |                                   |
| Frequency Tolerance       |        |                 | ± 50     |      | ppm    | at $25^{\circ}$ C ± $3^{\circ}$ C |
| Frequency Stability       |        |                 | ± 100    |      | ppm    | Operating Temp (Refer 25°C)       |
| Load Capacitance          | CL     |                 | 18       |      | pF     |                                   |
| Aging                     |        |                 | ± 3      |      | ppm    | First Year                        |
| Operating Temperature     |        | -40             | $\sim$   | 125  | °C     |                                   |
| Storage Temperature Range |        | -55             | $\sim$   | 125  | °C     |                                   |
| Drive Level               | DL     |                 |          | 100  | uW     |                                   |
| Effective Resistance Rr   | Rr     |                 |          | 45   | Ω      |                                   |
| Shunt Capacitance         | C0     |                 |          | 7    | pF     |                                   |

| Accurate Kinetic Energy | CUST. P/N :         |           |                |
|-------------------------|---------------------|-----------|----------------|
|                         | Aker Approved P/N : | CXA-01600 | 0-7B6A60       |
|                         | APPROVED :          | Tin       | SHEET : 3 of 9 |
|                         | PREPARED :          | Kiku      | REV. : 1       |

2. MARKING :








| CUST. P/N :         |           |               |
|---------------------|-----------|---------------|
| Aker Approved P/N : | CXA-01600 | 0-7B6A60      |
| APPROVED :          | Tin       | SHEET: 4 of 9 |
| PREPARED :          | Kiku      | REV. : 1      |


### 4. STRUCTURE ILLUSTRATION




|   | COMPONENTS          | MATERIALS                      | CO | MPONENTS  | MATERIALS |
|---|---------------------|--------------------------------|----|-----------|-----------|
| А | Base (Package)      | Ceramic(Al2O3)+Kovar(Fe/Co/Ni) | D  | Electrode | Cr / Ag   |
| В | Conductive adhesive | Ag / Silicon resin             | Е  | Lid       | Fe/Co/Ni  |
| С | Crystal blank       | SiO2                           |    |           |           |

|                         | CUST. P/N           | : |                   |                |
|-------------------------|---------------------|---|-------------------|----------------|
|                         | Aker Approved P/N : |   | CXA-016000-7B6A60 |                |
|                         | APPROVED            | : | Tin               | SHEET : 5 of 9 |
| Accurate Kinetic Energy | PREPARED            | : | Kiku              | REV. : 1       |

#### 5. PACKING : TAPE SPECIFICATION








A-A SECTION

OUTLINE DIMENSION

(Unit:mm)







SMD product packs 32 BOX = The outside box packs (1000 PCS \* 32 BOX = 32000 PCS)(MAX)



| CUST. P/N       | :    |           |               |
|-----------------|------|-----------|---------------|
| Aker Approved P | /N : | CXA-01600 | 0-7B6A60      |
| APPROVED        | :    | Tin       | SHEET: 8 of 9 |
| PREPARED        | :    | Kiku      | REV. : 1      |

#### 9. MECHANICAL PERFORMANCE

| TEST ITEMS                          | TEST METHODS AND TEST CONDITION   | PERFORMANCE  |
|-------------------------------------|---|--|
| 9.1 Drop Test                       | The specimen is measured for its frequency and<br>resistance before the test. It is then dropped from<br>a hight of 100 cm or more as a free fall object onto<br>a hard wooden plate of 30mm or more in thickness.<br>( in accordance with JIS-C0044 )  |  |
| 9.2 Vibration Test                  | The specimen is measured for its frequency<br>and resistance before the test. Most them into<br>X,Y and Z axes, respectively, for the vibration test.<br>Vibration condition:<br>Frequency range ; 20 $\sim$ 2000HZ<br>Peak to peak amplitude : 1.52 mm<br>Peak acceleration : 20G<br>Sweep time : 20 minute / axis<br>Pendicular total test time : 4 hours   | To satisfy the electrical performance .                        |
| 9.3 Resistance to<br>Soldering Test | ( in accordance with MIL-STD-883F : 2007.3 )<br>The specimen is measured for its frequency and<br>resistance before the test. Place the specimen on<br>the belt of the converynace and let it pass through<br>the reflow with the presetted temperature condition.<br>After passing twice the reflow place, the specimen<br>under the referee condition for -~2 hours and then<br>measure its electrical performance.<br>Temperature Condition of IR Simulation:<br>The temperature range of the preheated section<br>is setted at 150 $^{\sim}$ 180°C for 60~120 sec. For the next<br>section the temperature range is setted at 217~260°C<br>for 45~90 sec. and within this time range the specimen<br>should be able to sustain at the peak temperature,<br>260+/-3°C , for 10 sec long.<br>( in accordance with JESD22-B106-B ) |  |
| 9.4 Fine Leak<br>Test               | Place the specimen in a pressurized container and<br>pressurize it with the detection gas (mixed gas<br>consisting of 95% or more helium) for at least 2 hours.<br>Complete the measurement of the concentration of<br>helium within 30 min after taking it out from the<br>pressurized container.<br>( in accordance with MIL-STD-883F : 1014.11 )   | Less than<br>1.0 * 10 <sup>-8</sup> atm .c.c. / sec,<br>Helium |
|                                     | The referee condition .<br>Temperature $25 \pm 2$ °C<br>Humidity $44 \ 55 \%$<br>Pressure $86 \ 106$ kPa<br>( in accordance with MIL-STD-883E : 1014. 9 )   |  |



| CUST. P/N         | : |            |                |
|-------------------|---|------------|----------------|
| Aker Approved P/N | : | CXA-016000 | D-7B6A60       |
| APPROVED          | : | Tin        | SHEET : 9 of 9 |
| PREPARED          | : | Kiku       | REV. : 1       |

# 10. CLIMATIC RESISTANCE

| IU. CLIMATIC RESISTANCE                    |   |   |
|--|---|---|
| TEST ITEMS                                 | TEST METHODS AND TEST CONDITION   | PERFORMANCE                             |
| 10.1 Low Temp<br>Exposure Test             | The specimen is measured for its frequency and<br>resistance before the test .<br>Place the specimen in the chamber and kept it<br>at the temperature of $-40 \pm 3^{\circ}$ C for $168 \pm 6$ hours .<br>Take the specimen out of the chamber<br>and measure itselectrical performance after<br>leaving 1 ~ 2 hours under the referee condition.<br>( in accordance with JIS-C0020 )   |   |
| 10.2 Aging Test                            | The specimen is measured for its frequency and resistance before the test .<br>Place the specimen in the testing chamber and keep it at the temperature of $+ 125 \pm 3^{\circ}$ C for 720 $\pm 48$ hours.<br>And then take the specimen out of the chamber and measure its electrical performance after leaving for 1 ~ 2 hours under the referee condition .<br>( in accordance with JIS-C0021 )  | To satisfy the electrical performance . |
| 10.3 High<br>Temperature &<br>High Humidty | The specimen is measured for its frequency<br>and resistance before the test .<br>Place the specimen in the testing chamber and<br>kept it at the temperature of $+85 \pm 5$ °C and<br>humidity of $85 \pm 5$ % for $168 \pm 6$ hours.and<br>then take the specimen out and measure its<br>electrical performance after leaving for 1 ~ 2<br>hours under the referee condition.<br>( in accordance with MIL-STD-883F : 1004.7 )                               |   |
| 10.4 Temperature<br>Cycle Test             | The specimen is measured for its frequency<br>and resistance before the test .<br>Subject the specimen to the 100 cycles of<br>temperature ranges stated below .<br>High temp . + $125 \pm 3 \degree C$ ( $15\pm 3 \min$ ).<br>$2 \sim 3 \min$ .<br>Low temp $55 \pm 3 \degree C$ ( $15\pm 3 \min$ ).<br>Measure its electrical performance after leaving it<br>for 1 ~ 2 hours under the referee condition .<br>( in accordance with MIL-STD-883F : 1010.8 ) |   |