High operation force satisfies the needs in automotive applications. Wide stem & good mountability





Typical Specifications		
Items	Specifications	
Rating (max.)	50mA 16V DC	
Rating (min.)	10µA 1V DC	
Initial contact resistance	500mΩ max.	
Travel (mm)	0.2	

Product Line

Product No. Operating force		Operating direction	Operating life	Stem color	Minimum order unit (pcs.)		
TTOUGETNO.	Operating force	Operating direction	(5mA 5V DC)	Otern Color	Japan	Export	
SKRPABE010	1.57N		100,000 cycles	Natural	4.000	4.000	
SKRPACE010	2.55N	Top push	50,000 cycles				
SKRPADE010	4N		100,000 cycles	Black	4,000	4,000	
SKRPARE010	5N		100,000 cycles	DIACK			

Packing Specifications

For reels of 330mm diameter, please inquire.


Taping

Note


Number of packages (pcs.)			Tape width	Export package	
1 reel	1 case / Japan	1 case / export packing	(mm)	measurements (mm)	
4,000	40,000	40,000	12	395×395×205	

Reel size

Dimensions



Circuit Diagram





Soft

Mount Type

234

TACT Switch[™] List of Varieties

	Туре					arp Feeling T				
	Series	SKRK	SKTH	SKRP	SKQM	Surface Mou	SKSU	SKST	SKRA	SKHM
		ORTIK		onn		ondr	UK00	OROT	ORTIA	
	Photo		Starts				A AND	Contraction of the second	No.	N.C.
	Features	Compact size Low-profile	Compact size	High operation force Compact size	Compa	act size		Middle trave	1	_
	Water-proof	-	—	_	_	_	•	_	0	_
	Dust-proof	_	•	_	_	_	•	_	0	_
	IP standard	_	_	_	_	_	67 equivalency		67 equivalency	_
Operatir	Top push	•	•	•	٠	•	•	•	•	•
directio		_	_	_	_	_	_	_	_	_
	W	3.9	3.5	4.2	6	6.1	5.3	8.5	□6.2	6.2
Dimensio (mm)	D D	2.9	3.2	3.2	3.5	3.7	5.4	0.0	0.2	6.5
	Н	1.5/2	1.8/2.5	2.5	4.3/5	2.5	3.85	3.95	3.5/5.2	3.1
Operatio force coverag	2N to 3N	Ţ		^	Ţ	Ţ	\$	\$	Ţ	Ţ
	Travel (mm)	0.13	0.12	0.2	0.	25	0.7	0.9	See the relevant pages for respective product descriptions	0.25
G	round terminal	_		_		0				•
Operatin	ng temperature range	-40°C to +85°C		11	_	40°C to +9(วาว		1	−40°C to +85
A	utomotive use	_	•	•	•	•	•	•	0	_
	Life Cycle		¥2	*3			*3	2	**3	*3
	Rating (max.) (Resistive load)	50mA 12V DC	25mA 16V 50mA 16V 50mA 12V DC 50mA 16V DC 50mA 12V				12V DC			
Electrical	Rating (min.) (Resistive load)		10µA 1V DC							
performance	Insulation resistance		100MΩ min. 100V DC 1min.							
	Voltage proof	250V AC 1min.	2 100V AC 250V AC 1min.							
Durchilite	Vibration		10	to 55 to 10H in the 3 d	lz/min., the a direction of >	amplitude is K, Y and Z fo	1.5mm for all t or 2 hours resp	the frequenc	cies,	
Durability	Lifetime		Shall be in accordance with individual specifications.							
	Cold	-40%	0°C 96h -40°C -40°C 96h -40°C 1,000h -40°C					-40℃ 96		
Environmental performance	Dry heat	90°C	96h	90°C 1,000h 90°C 96h 90°C 1,000h			٦	90°C 96h		
	Damp heat	60°C, 90 to 95%RH 96h 60°C, 90 to 95%RH 60°C, 90 to 95%RH 60°C, 90 to 95%RH			1 1,000h	60°C, 90 to 95%RH 96				
	Page	230	232	234	235	236	238	239	240	241

H : Height. The minimum dimension if there are variances.

 TACT Switch[™] Soldering Conditions
 265

 TACT Switch[™] Cautions
 266

Notes

1. The automotive operating temperature range to be individually discussed upon request.

2. Indicates applicability to all products in the series, while \bigcirc indicates applicability to some products in the series.


Soft Feeling



Condition for Reflow

Available for Surface Mount Type.

- 1. Temperature measurement: Thermocouple ϕ 0.1 to 0.2 CA (K) or CC (T) at solder joints (copper foil surface). A heat resistive tape should be used to fix thermocouple.
- 2. Temperature profile



Notes

- The above temperature shall be measured of the top of switch. There are cases where the PC board's temperature greatly differs from that of the switch, depending on the material, size, thickness of PC boards and others. The above-stated conditions shall also apply to switch surface temperatures.
- Soldering conditions differ depending on reflow soldering machines.
- Prior verification of soldering condition is highly recommended.

Conditions for Auto-dip

Available for Snap-in Type and Radial Type.

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100°C max.
Preheating time	60s max.
Soldering temperature	260°C max.
Duration of immersion	Бs max.
Number of soldering	2times max.

SKHH, SKPD Series

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 110°C max.
Preheating time	60s max.
Soldering temperature	260°C max.
Duration of immersion	5s max.
Number of soldering	2times max.

SKQJ, SKQK, SKEG Series

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100°C max.
Preheating time	45s max.
Soldering temperature	255°C max.
Duration of immersion	5s max.
Number of soldering	2times max.

Notes

1. Prevent flux penetration from the top side of the TACT Switch[™].

- 2. Switch terminals and a PC board should not be coated with flux prior to soldering.
- 3. The second soldering should be done after the switch is stable with normal temperature.
- 4. Use the flux with a specific gravity of min 0.81.
- (EC-19S-8 by TAMURA Corporation, or equivalents.)

Manual Soldering

	<u> </u>
Items	Condition
Soldering temperature	350°C max.
Duration of soldering	Зs max.
Capacity of soldering iron	60W max.

SKHH, SKHW, SKRG, SKPD Series

Items	Condition
Soldering temperature	360°C max.
Duration of soldering	Зs max.
Capacity of soldering iron	60W max.

SKTD, SKTG, SKQJ, SKQK, SKEG Series

Items	Condition
Soldering temperature	350°C max.
Duration of soldering	Зs max.
Capacity of soldering iron	20W max.