


Lever and Push Operation Type SLLB5 Series


Number of operating shafts			Single-shaft		
Shaft material			Resin		
Actuator configuration			Mounting knob		
Push-on switch			With		
Operating force	Lever po	rtion	0.65±0.3N		
	Push por	Push portion		2.5±1N	
Travel (Center push)			0.7mm		
Location lug			Without		
Contact resistance			1Ω max.		
Operating temperature range			-10℃ to +60℃		
Ratings (max.)/(m	nin.) (Resistive load)		10mA 5V DC/50μ	IA 3V DC	
Electrical performance	Output voltage		⊕5	V KΩ Measuring terminal	
	Directional resolution		2-direction		
	Insulation resistance		100MΩ min. 100V DC		
	Voltage proof		100V AC for 1 minute		
Mechanical performance	Terminal strength		3N for 1 minute		
	Actuator strength	Push/pull directions	50N		
		Operating direction	10N		
Durability	Operating life without load		100,000 cycles		
	Operating life with load (Load: as ratings)		100,000 cycles (1	L0mA 5V DC)	
Environmental	Cold		-20±2℃ for 96h		

performance	Dry heat		85±2℃ for 96h	
	Damp he	at	40±2℃, 90 to 95%RH for 96h	
Minimum order unit (pcs.)		Japan	1,500	
		Export	6,000	

Dimensions




Land Dimensions




Viewed from mounting face.

Circuit Diagram




Push portion.

Code Table



Packing Specifications

Taping



Number of package (pcs.)	es 1 reel	1,500
(1)	1 case / Japan	3,000
	1 case / export packing	6,000
Tape width (mm)		24
Export package measurements (mm)		428×413×172

Soldering Condition

Example of Reflow Soldering Condition


1. Heating method:

Double heating method with infrared heater.

2. Temperature measurement:

Thermocouple 0.1 to 0.2 Φ CA (K) or CC (T) at solder joints (copper foil surface). A heat resisting tape should be used to fix thermocouple.

3. Temperature profile



- (1) The condition mentioned above is the temperature on the mounting surface of a PC board. There are cases where the PC board's temperature greatly differs from that of the switch, depending on the PC board's material, size, thickness, etc. The above-stated conditions shall also apply to switch surface temperatures.
- (2) Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

Reference for Hand Soldering

Tip temperature	350±5℃
Soldering time	3s max.
No. of solders	1 time

Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. Please place purchase orders for taping products per minimum order unit (1 reel or a case).
- 3. Products other than those listed in the above chart are also available. Please contact us for details.
- 4. Please contact us for automotive use products.