



This document is the property of Amphenol Corporation and is returned in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose its use or information in this document.



RECOMMENDED P.C.B LAYOUT
TOLERANCE: +/ - 0.05mm



Customer drawing


REVISIONS			DATE	APPROVED
S/N	ECN	DESCRIPTION		
1	HK--	First Release Drawing	20/Aug/13	JP

D-SUB TECHNICAL DATA

SHELL : SPCC, 100u" min tin over 50u" min nickel over 50u" copper
 BODY : PBT, UL 94V-0, Color:Black.
 CONTACTS : Copper Alloy
 Gold flash plated over 50u" nickel on mating area
 100u" tin plated over 50u" nickel on solder area
 BRACKET : Zinc Alloy, Nickel plated
 BOARDLOCK: Copper Alloy, Tin plated
 ELECTRICAL : Voltage rating 250V AC(RMS)
 Current rating 3A
 Withstanding Voltage >1000 V AC(RMS)
 Insulation resistance >1000 M Ohms
 Contact resistance 25 mOhms max.

PRODUCT CODE

L17H3DD0130



UNLESS OTHERWISE SPECIFIED		APPROVAL		DATE	
TOLERANCES	U.S.	DECIMAL	FRACTIONAL	DD/MY/YY	DD/MY/YY
X	±	0.50	1/2		
XX	±	0.30	3/16		
XXX	±	0.20	1/8		
ANGLES	±	5°			

FOR MATERIALS AND FINISHES SEE REMOVE SHARP EDGES DIMENSIONS THICKNES

DRAWING FILE :

ANGLE OF PROJECTION

Amphenol
Amphenol East Asia Limited

SIZE DRAWING NO. A4
SCALE NONE

SIZE DRAWING NO. C L17H3DD0130
SHEET 1 OF 1