

Single Stage Buck PFC Regulator for LED Lighting

Features

- Internal 600V Power MOSFET
- Valley turn-on of the MOSFET to achieve low switching losses
- 0.3V current sense reference voltage leads to a lower sense resistance thus a lower conduction loss
- Low start up current: 15µA typical
- Reliable short LED and Open LED protection
- Power factor >0.9
- Compact package: SOIC-8

Applications

- Tube lamp & PAR lamp
- Down light & Bulb lamp

Descriptions

The DIO8804 consists of an integrated single stage Buck & PFC Regulator and 600V power MOSFET, specifically designed for a high performance non-isolated converter with minimal external components targeting at LED lighting applications.

The DIO8804 drives the Buck converter in the quasi-resonant mode to achieve higher efficiency and keeps the Buck converter inconstant on time operation to achieve high power factor.

This chip adopts special design to achieve reliable protection for safety requirement.

Block Diagram




Figure1 Block Diagram



Ordering Information

Order Part Number	Top Marking		T _A	Package	
DIO8804CS8	DIO8804	Green	-40 to +125°C	SOIC-8	Tape & Reel, 2500

Pin Assignments




Figure 2 Pin Assignment (Top View)

Pin Definitions

Pin Name	Description
	Current sense pin. Connect this pin to the source of the primary switch. Connect the sense resistor
	across the source of the primary switch and the GND pin.
CS	(current sense resister Resistor: $Rs = \frac{1}{2} \times \frac{Vref}{Iout}$)
	Also this pin used to detect transformer and secondary is short or not.
NC	Not Connect.
Drain	Power MOSFET Drain Pin. The Drain pin is connected to the primary lead of the transformer.
VIN	Power supply pin. This pin also provides output over voltage protection along with ZCS pin.
GND	Ground pin
COMP	Loop compensation pin. Connect a RC network across this pin and ground to stabilize the control
COMP	loop.
	Inductor current zero-crossing detection pin. This pin receives the auxiliary winding voltage by a
	resister divider and detects the inductor current zero crossing point. This pin also provides over
ZCS	voltage protection and line regulation modification function simultaneously. If the voltage on this pin
	is above V _{ZCS,OVP} , the IC would enter overvoltage protection mode. Good line regulation can be
	achieved by adjusting the upper resistor of the divider.



Absolute Maximum Ratings

Stresses beyond those listed under "Absolute Maximum Rating" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other condition beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maxim rating conditions for extended periods may affect device reliability.

Pai	rameter	Rating	Unit
VIN		-0.3 to 19	V
Drain	Drain		V
Supply Current I _{VIN}		15	mA
ZCS	-0.3 to VIN+0.3	V	
CS, COMP	-0.3 to 5	V	
Power Dissipation, P _D @ T _A = 25°C, SOIC-8		1.1	W
Package Thermal Resistance,	ӨдА	100	2000
SOIC-8	Өлс	50	- °C/W
Storage Temperature Range		-65 to 150	°C
Junction Temperature Range		150	°C
Lead Temperature Range		260	°C
500	HBM, JEDEC: JESD22-A114	2000	.,,
ESD	MM, JEDEC: JESD22-A115	200	- V

Recommend Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended Operating conditions are specified to ensure optimal performance to the datasheet specifications. DIOO does not Recommend exceeding them or designing to Absolute Maximum Ratings.

Parameter	Rating	Unit	
Supply Voltage	9.5 to 15.4	V	
Ambient Temperature Range	-40 to 125	°C	



Electrical Characteristics

V _{IN} = 12V, T _A = 25°C, unless otherwise specified.						
Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
$V_{\text{VIN,ON}}$	VIN turn-on threshold			16		٧
$V_{\text{VIN},\text{OFF}}$	VIN turn-off threshold			7.3		V
$V_{VIN,OVP}$	VIN OVP voltage			17.8		V
I _{ST}	Start up Current	V _{VIN} < V _{IN,OFF}		15		μA
I _{VIN_OVP}	Shunt current in OVP mode	After V _{VIN} >V _{VIN,OVP} , then set VIN=15V		2		mA
IQ	Quiescent Current	No switching		0.26		mA
I _{VIN} .	Operation current	C _L =100pF,f=15kHz		0.36		mA
Error Amplifier Se	ection			l	1	
V_{REF}	Internal reference voltage		0.294	0.3	0.306	V
ZCS pin Section				l	1	
V _{ZCS} , OVP	ZCS pin OVP voltage threshold			1.5		V
V _{FAST_ST}	Fast start up threshold			0.55		V
Current Sense Se	ction(Source PIN of integrated MOSF	ET)				
$V_{\text{CS.LMT}}$	Current limit reference voltage			0.75		V
K ₂	CC Feed forward coefficient			0.1		
R _{K2}	CC Feed forward resistor R _{K2}			1020		Ω
PWM Section				I		
T _{ON.MAX}	Max on time	COMP high clamp		16		μs
T _{LEB}	Leading edge blanking time			350		ns
$T_{OFF,MAX}$	Max OFF time			68		μs
T _{LEB.ZCD}	ZCD Blanking Time	After turn off		2		μs
f _{MAX}	Maximum switching frequency			115		kHz
Power MOSFET S	Section			1		1
V _{BVDSS}	Break-down Voltage	I _{DS} =250μA, T _J =25℃	600	630		V
I _{DSS}	Off-state drain current	V _{DS} =600V, V _{GS} =0V, T _J =25°C			1	μA
Thermal Section	•	•				
T_{SD}	Thermal Shutdown Temperature			150		°C






Figure 3 Typical Application



Application Information

Start up

After AC or DC supply is powered on, the capacitor C_{VIN} across VIN and GND pin is charged up by BUS voltage through a start up resistor R_{ST} . Once V_{VIN} rises up to V_{VIN-ON} , the internal blocks start to work and PWM output is enabled.

Shut down

After AC supply or DC BUS is powered off, the energy stored in the BUS capacitor will be discharged. When the auxiliary winding of transformer can't supply enough energy to VIN pin, V_{VIN} will drop down. Once V_{VIN} is below $V_{VIN-OFF}$, the IC will stop working and V_{COMP} will be discharged to zero.

Quasi-Resonant Operation

QR mode operation provides low turn-on switching losses for Buck converter.

Over Voltage Protection (OVP) & Open LED Protection (OLP)


The output voltage is reflected by the auxiliary winding voltage of the transformer, and both ZCS pin and VIN pin provide over voltage protection function. When the load is null or large transient happens, the output voltage will exceed the rated value. When V_{VIN} exceeds $V_{VIN,OVP}$ or V_{ZCS} exceeds $V_{ZCS,OVP}$, the over voltage protection is triggered and the IC will discharge V_{VIN} by an internal current source $I_{VIN,OVP}$. Once V_{VIN} is below $V_{VIN,OFF}$, the IC will shut down and be charged again by BUS voltage through start up resistor. If the overvoltage condition still exists, the system will operate in hiccup mode.


Short Circuit Protection (SCP)

When the output is shorted, the output voltage is clamped to zero. The voltage of the auxiliary winding is proportional to the output winding, so V_{VIN} will drop down without auxiliary winding supply. Once V_{VIN} is below $V_{VIN,OFF}$, the IC will shut down and be charged again by the BUS voltage through the start up resistor. If the short circuit condition still exists, the system will operate in hiccup mode. In order to guarantee SCP function not effected by voltage spike of auxiliary winding, a filter resistor is needed (10 Ω typically).




Physical Dimensions: SOIC-8






COMMON DIMENSIONS



(UNITS OF MEASURE=MILLIMETER)				
Symbol	MIN	NOM	MAX	
Α	1.35	1.55	1.75	
A1	0.10	0.15	0.25	
A2	1.25	1.40	1.65	
А3	0.50	0.60	0.70	
b	0.38	-	0.51	
b1	0.37	0.42	0.47	
С	0.17	-	0.25	
c1	0.17	0.20	0.23	
D	4.80	4.90	5.00	
E	5.80	6.00	6.20	
E1	3.80	3.90	4.00	
е		1.27BSC		
L	0.40 0.60 0.80			
L1		1.04REF		
L2		0.25BSC		
R	0.07	-	-	
R1	0.07	-	II	
h	0.30	0.40	0.50	
Θ	0°	-	8°	
Θ1	15°	17°	19°	
Θ2	11°	13°	15°	
Θ3	15°	17°	19°	
Θ4	11°	13°	15°	





CONTACT US

Dioo is a professional design and sales corporation for high-quality and performance analog semiconductors. The company focuses on industry markets, such as, cell phone, handheld products, laptop, and medical equipment and so on. Dioo's product families include analog signal processing and amplifying, LED drivers and charger IC. Go to http://www.dioo.com for a complete list of Dioo product families.

For additional product information, or full datasheet, please contact with our Sales Department or Representatives.