

SPECIFICATION FOR APPROVAL

Customer.				
Description.	DC FAN			
Customer Part No		REV.		
Delta Model No.	AFB0612EHYJW	REV. 02		
Sample Issue No.				
Sample Issue Date	JAN-23-2017			
PLEASE SEND ONE COPY OF THIS SPECIFICATION BACK AFTER YOU SIGNED APPROVAL FOR PRODUCTION PRE-ARRANGEMENT.				
APPROVED BY :				
DATE:				

Delta Electronics, Inc.

HeTianXia High-Tech Industrial Park.

Shi Jie Town, Dong Guan City.

Guangdong Province, China. P. R. C.

TEL: 86-769-86329008 FAX: 86-769-86631589 Delta Electronics, Inc. HeTianXia High-Tech Industrial Park. Shi Jie Town, Dong Guan City. Guangdong Province, China. P. R. C.

TEL: 86-769-86329008 FAX: 86-769-86631589

✓ NONE		
DESCRIPTION:		

Delta Electronics, Inc.

HeTianXia High-Tech Industrial Park.

Shi Jie Town, Dong Guan City.

Guangdong Province, China. P. R. C.

TEL: 86-769-86329008 FAX: 86-769-86631589

SPECIFICATION FOR APPROVAL

Customer:

Description: DC FAN

Customer P/N: REV:

Delta Model NO.: AFB0612EHYJW Delta safety model NO.: AFB0612EH

Smaple Rev: 02 Issue N0:

Sample Issue Date: JAN-23-2017 Quantity:

1. SCOPE:

THIS SPECIFICATION DEFINES THE ELECTRICAL AND MECHANICAL CHARACTERISTICS OF THE DC BRUSHLESS AXIAL FLOW FAN. THE FAN

2. CHARACTERS:

ITEM	DESCRIPTION		
RATED VOLTAGE	12 VDC		
OPERATION VOLTAGE	10.8 - 13.2 VDC		
START VOLTAGE	10.8 VDC		
INPUT CURRENT	0.38 (MAX. 0.48) A		
 	SAFETY CURRENT ON LABEL: 0.48 A		
INPUT POWER	4.56 (MAX. 5.76) W		
SPEED	6800±8% R.P.M.		
MAX. AIR FLOW 1.086 (MIN. 0.977) M ³ /(AT ZERO STATIC PRESSURE) 38.35 (MIN. 34.50) CFM			
MAX. AIR PRESSURE (AT ZERO AIRFLOW)	$\begin{array}{c} 13.81 \; (\mathrm{MIN.} \; 11.18 \;) \; \mathrm{mmH_20} \\ 0.544 \; (\mathrm{MIN.} \; 0.441 \;) \; \mathrm{inchH_20} \end{array}$		
ACOUSTICAL NOISE (AVG.)	46.5 (MAX. 50.5) dB-A		
INSULATION TYPE	UL: CLASS A		


(continued)

PART NO: AFB0612EHYJW DELTA MODEL:

ı 	
INSULATION STRENGTH	10 MEG OHM MIN. AT 500 VDC (BETWEEN FRAME AND (+) TERMINAL)
DIELECTRIC STRENGTH	5 mA MAX. AT 500 VAC 50/60 Hz ONE MINUTE, (BETWEEN FRAME AND (+) TERMINAL)
LIFE EXPECTANCE (L10) (AT LABEL VOLTAGE)	70,000 HOURS CONTINUOUS OPERATION AT 40 °C WITH 15 ~ 65 %RH.
ROTATION	CLOCKWISE VIEW FROM NAME PLATE SIDE
OVER CURRENT SHUT DOWN	THE CURRENT WILL SHUT DOWN WHEN LOCKING ROTOR.

- NOTES: 1. ALL READINGS ARE MEASURED AFTER STABLY WARMING UP
 - THROUGH 2 MINUTES.

 2. STANDARD AIR PROPERTY IS AIR AT (Td) 25°C TEMPERATURE, (RH) 65% RELATIVE HUMIDITY, AND (Pb) 760 mmHg BAROMETRIC PRESSURE.
 - 3. THE VALUES WRITTEN IN PARENS, (), ARE LIMITED SPEC.
 - 4. ACOUSTICAL NOISE MEASURING CONDITION:



NOISE IS MEASURED AT RATED VOLTAGE IN FREE AIR IN ANECHOIC CHAMBER WITH B & K SOUND LEVEL METER WITH MICROPHONE AT A DISTANCE OF ONE METER FROM THE FAN INTAKE.

page: 2

PART 1	NO:								
DELTA		AFB0612EHYJV	V						
3. ME(CHANICAL:								
3-1	. DIMENSIONS			SE	E DIME	NSION	S DRA	AWI NG	ŗ
3-2	FRAME				PL	ASTIC	UL: 9	94V−C)
3-3	. IMPELLER				PL	ASTIC	UL: 9	94V−C)
3-4	. BEARING SY	STEM			TW	O BAL	L BE	ARING	ſ
3-5	. WEIGHT					80 GR	AMS ((REF.))
4. ENV	IRONMENTAL:								
4-1	. OPERATING	TEMPERATURE			-10 T) +70	DEGI	REE C	1
4-2	. STORAGE TE	MPERATURE			-40 To) +75	DEGI	REE C	,
4-3	. OPERATING	HUMIDITY				5 T(90	% RF	I
4-4	. STORAGE HU	JMIDITY				5 T(95	% RF	ſ

5. PROTECTION:

5-1. LOCKED ROTOR PROTECTION

IMPEDANCE OF MOTOR WINDING PROTECTS MOTOR FROM FIRE IN 96 HOURS OF LOCKED ROTOR CONDITION AT THE RATED VOLTAGE.

5-2. POLARITY PROTECTION


BE CAPABLE OF WITHSTANDING IF REVERSE CONNECTION FOR POSITIVE AND NEGATIVE LEADS.

- 6. RE OZONE DEPLETING SUBSTANCES:
 - 6-1. NO CONTAINING PBBs, PBB0s, CFCs, PBBEs, PBDPEs AND HCFCs.
- 7. PRODUCTION LOCATION
 - 7-1. PRODUCTS WILL BE PRODUCED IN CHINA OR THAILAND.

PART NO:

DELTA MODEL: AFB0612EHYJW

8. P & Q CURVE:



* TEST CONDITION: INPUT VOLTAGE ----- OPERATION VOLTAGE TEMPERATURE ----- ROOM TEMPERATURE HUMIDITY ----- 65%RH

page: 4


PART NO:

DELTA MODEL: AFB0612EHYJW

9. DIMENSION DRAWING:

LABEL:





NOTES:

1.LEAD WIRE:UL 1061 -F- AWG #24 PIN1. BLACK WIRE ----(-)

PIN2. RED WIRE ----(+)

2.LEAD WIRE:UL 1061 -F- AWG #26 PIN3. YELLOW WIRE----(-F00) PIN4. BLUE WIRE----(-PWM)

- 3. HOUSING: JWT A2508H00-4P OR EQUIVALENT.
- 4. TERMINAL: JWT A2543TOP-2 OR EQUIVALENT.
- 5. THIS PRODUCT IS ROHS COMPLIANT.

A00


UNIT: mm(INCH)

PART NO:
DELTA MODEL:

AFB0612EHYJW

10. FREQUENCY GENERATOR (FG) SIGNAL:

1. OUTPUT CIRCUIT - OPEN COLLECTOR MODE:



CAUTION:

THE LEAD WIRE OF FG SIGNAL CAN NOT TOUCH THE LEAD WIRE OF POSITIVE OR NEGATIVE.

2. SPECIFICATION:


 V_{CE} (sat)=0.5V MAX.


 $V_{FG}=13.2V$ MAX.

 $I_c = 5 \text{mA MAX}.$

 $R \ge V_{FG} / I_{C}$

3. FREQUENCY GENERATOR WAVEFORM:





N-R.P.MTS=60/N(SEC)


*VOLTAGE LEVEL AFTER BLADE LOCKED

*4 POLES

PART NO:

DELTA MODEL: AFB0612EHYJW

11. PWM CONTROL SIGNAL:




- THE PREFERRED OPERATING POINT FOR THE FAN IS 25K HZ.
- AT 100% DUTY CYCLE, THE ROTOR WILL SPIN AT MAXIMUM SPEED.
- AT 0% DUTY CYCLE, THE ROTOR WILL SPIN AT MINIMUM SPEED.
- WITH CONTROL SIGNAL LEAD DISCONNECTED, THE FAN WILL SPIN AT MAXIMUM SPEED.
- AT RATED VOLTAGE, 25K HZ, 30% DUTY CYCLE, THE FAN WILL BE ABLE TO START FROM A DEAD STOP.

12. SPEED VS PWM CONTROL SIGNAL: (AT RATED VOLTAGE & PWM FREQUENCY=25K HZ)

DUTY CYCLE (%)	SPEED R.P.M. (REF.)	CURRENT (A) TYP.
100	6800 ± 8%	0.38
40	4000 ± 10%	0.11
0	1500 +200/-250	0.03

13. PWM CONTROL LEAD WIRE INPUT IMPEDANCE:



13-1. THE FAN SPEED WILL DEFAULT TO MAXIMUM WHEN THE SPEED CONTROL INPUT IS LEFT UNCONNECTED.

page: 7


PART NO:

DELTA MODEL: AFB0612EHYJW

REMARKS: THIS PAGE IS FOR REFERENCE ONLY.

14. DUTY CYCLE VS. SPEED CURVE:

(AT 25°C, RATED VOLTAGE & PWM FREQUENCY=25KHZ)



page: 8 A00



Application Notice

- 1. Delta will not guarantee the performance of the products if the application condition falls outside the parameters set forth in the specification.
- 2. A written request should be submitted to Delta prior to approval if deviation from this specification is required.
- 3. Please exercise caution when handling fans. Damage may be caused when pressure is applied to the impeller, if the fans are handled by the lead wires, or if the fan was hard-dropped to the production floor.
- 4. Except as pertains to some special designs, there is no guarantee that the products will be free from any such safety problems or failures as caused by the introduction of powder, droplets of water or encroachment of insect into the hub.
- 5. The above-mentioned conditions are representative of some unique examples and viewed as the first point of reference prior to all other information.
- 6. It is very important to establish the correct polarity before connecting the fan to the power source. Positive (+) and Negative (-). Damage may be caused to the fans if connection is with reverse polarity, if there is no foolproof method to protect against such error specifically mentioned in this spec.
- 7. Delta fans without special protection are not suitable where any corrosive fluids are introduced to their environment.
- 8. Please ensure all fans are stored according to the storage temperature limits specified. Do not store fans in a high humidity environment. We highly recommend performance testing is conducted before shipping, if the fans have been stored over 6 months.
- 9. Not all fans are provided with the Lock Rotor Protection feature. If you impair the rotation of the impeller for the fans that do not have this function, the performance of those fans will lead to failure.
- 10. Please be cautious when mounting the fan. Incorrect mounting of fans may cause excess resonance, vibration and subsequent noise.
- 11. It is important to consider safety when testing the fans. A suitable fan guard should be fitted to the fan to guard against any potential for personal injury.
- 12. Except where specifically stated, all tests are carried out at room (ambient) temperature and relative humidity conditions of 25°C, 65% RH. The test value is only for fan performance itself.
- 13. Be certain to connect an "4.7μF or greater" capacitor to the fan externally when the application calls for using multiple fans in parallel, to avoid any unstable power.

Doc. No: FMBG-ES Form 001 Rev. 0001 Date: June 24, 2009