

SPECIFICATION FOR APPROVAL

| Customer: | |
|---|----------|
| Description : DC FAN | |
| Customer Part No. : Delta Model No. : EFB1524SHGCGJ Sample Issue No. : Sample Issue Date : OCT.12 2016 | REV.: 00 |
| | |
| PLEASE SEND ONE COPY OF THIS SPEC YOU SIGNED APPROVAL FOR PRODUCT | |
| APPROVED BY: | |
| DATE : | |
| | |

DELTA ELECTRONICS, INC.
TAOYUAN PLANT
252, SHANG YING ROAD, KUEI SAN INDUSTRIAL ZONE
TAOYUAN SHIEN, TAIWAN, R.O.C.

TEL:886-(0)3-3591968

FAX:886-(0)3-3591991

*** SAMPLE HISTORY ***

CUSTOMER: 錢龍電子

CUSTOMER P/N:

DELTA MODEL: EFB1524SHGCGJ

| REV. | DESCRIPTION | DRAWN | CHECKED | | | APPROVED | ISSUE |
|--------|-------------|-----------------|-----------------|-----------------|----|------------------------|----------|
| INE V. | | | ME | EE | CE | | DATE |
| 00 | ISSUE SPEC | 黄浩宏 10/06'16 | 黄浩宏 10/06'16 | 林玉晟 10/11'16 | | 李健銘 謝清森 10/12'16 | 10/12'16 |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |

Delta Electronics, Inc. No.252, Shanying Rd., Guishan Dist., Taoyuan City 333, Taiwan (R.O.C.)

STATEMENT OF DEVIATION

TEL: 886-(0)3-3591968

FAX: 886-(0)3-3591991

| ■ NONE □ DESCRIPTION: | | |
|------------------------|--|--|
| | | |
| | | |
| | | |
| | | |
| | | |
| | | |
| | | |

Delta Electronics, Inc. No.252, Shanying Rd., Guishan Dist., Taoyuan City 333, Taiwan (R.O.C.)

Specification For Approval

TEL: 886-(0)3-3591968

FAX: 886-(0)3-3591991

| Customer: | 風酷電子 | |
|-------------------|-----------------|------------------------------------|
| Description : | DC FAN | |
| Customer P/N : | | rev.: |
| Delta model no. : | EFB1524SHGCGJ | Delta Safety Model No.: EFB1524SHG |
| Sample revision. | : 00 | Issue no.: |
| Sample issue dat | e : OCT.12 2016 | Quantity : |

1. SCOPE:

THIS SPECIFICATION DEFINES THE ELECTRICAL AND MECHANICAL CHARACTERISTICS OF THE DC BRUSHLESS AXIAL FLOW FAN.

2. CHARACTERS:

| ITEM | DESCRIPTION |
|--|--|
| RATED VOLTAGE | 24.0 VDC |
| OPERATION VOLTAGE | 12.0 - 28.0 VDC |
| INPUT CURRENT (AVG.) | 1.17 (MAX. 2.10) A (SAFETY CURRENT ON LABEL: 2.10 A) |
| INPUT POWER | 28.08 (MAX. 50.40) W |
| SPEED | 4300 ±10% R.P.M. |
| MAX. AIR FLOW (AT ZERO STATIC PRESSURE) | 9.203 (MIN. 8.280) M ³ /MIN. 325.00 (MIN. 292.40) CFM |
| MAX. AIR PRESSURE (AT ZERO AIRFLOW) | 27.50 (MIN. 22.30) mmH ₂ O 1.083 (MIN. 0.878) inchH ₂ O |
| ACOUSTICAL NOISE (AVG.) | 63.0 (MAX. 66.0) dB-A |
| INSULATION TYPE | UL: CLASS A |
| INSULATION STRENGTH | 10 MEG OHM MIN. AT 500 VDC (BETWEEN FRAME AND (+) TERMINAL) |
| DIELECTRIC STRENGTH | 5 mA MAX. AT 500 VAC 50/60 Hz ONE MINUTE, (BETWEEN FRAME AND (+) TERMINAL) |


(continued) PAGE 1

DELTA MODEL: EFB1524SHGCGJ

| EXTERNAL COVER | OPEN TYPE |
|---|--|
| LIFE EXPECTANCE (L10) (AT LABEL VOLTAGE) | 80,000 HOURS CONTINOUS OPERATION AT 40 ℃ WITH 15 ~ 65 %RH. |
| ROTATION | COUNTER CLOCKWISE VIEW FROM NAME PLATE SIDE |
| LOCKED CURRENT SHUT DOWN | THE CURRENT WILL SHUT DOWN WHEN ROTOR LOCKED AND FIXED. |

NOTES:

- 1. ALL READINGS ARE MEASURED AFTER STABLY WARMING UP THROUGH 10 MINUTES.
- 2. STANDARD AIR PROPERTY IS AIR AT (Td) 25℃ TEMPER ATURE, (RH) 65% RELATIVE HUMIDITY, AND (Pb) 760 mmHg BAROMETRIC PRESSURE.
- 3. THE VALUES WRITTEN IN PARENS , (), ARE LIMITED SPEC.
- 4. ACOUSTICAL NOISE MEASURING CONDITION:



NOISE IS MEASURED AT RATED VOLTAGE IN FREE AIR IN ANECHOIC CHAMBER WITH B & K SOUND LEVEL METER WITH MICROPHONE AT A DISTANCE OF ONE METER FROM THE FAN INTAKE.

DELTA MODEL: EFB1524SHGCGJ

3. MECHANICAL:

| 3-1. DIMENSIONS | - SEE DIMENSIONS DRAWING |
|---------------------------|---------------------------|
| 3-2. FRAME | DIE-CAST ALUMINUM |
| 3-3. IMPELLER | PLASTIC UL: 94V-0 |
| 3-4. BEARING SYSTEM | TWO BALL BEARINGS |
| 3-5. WEIGHT | 840 GRAMS |
| 3-5-1. ROTOR WEIGHT | 270 GRAMS |
| 3-6. CORROSION PROTECTION | - ADD GLUE ON PAD OF PCBA |
| | |

4. ENVIRONMENTAL:

| 4-1. OPERATING TEMPER | RATURE | -10 TO + | -70 DEGREE C |
|-----------------------|--------|----------|--------------|
| 4-2. STORAGE TEMPERA | TURE | -40 TO + | 75 DEGREE C |
| 4-3. OPERATING HUMIDI | TY | | 5 TO 90 % RH |
| 4-4. STORAGE HUMIDITY | , | | 5 TO 95 % RH |

5. PROTECTION:

5-1. LOCKED ROTOR PROTECTION

IMPEDANCE OF MOTOR WINDING PROTECTS MOTOR FROM FIRE IN 96 HOURS OF LOCKED ROTOR CONDITION AT THE RATED VOLTAGE.

5-2. POLARITY PROTECTION


BE CAPABLE OF WITHSTANDING IF REVERSE CONNECTION FOR POSITIVE AND NEGATIVE LEADS.

- 6. RE OZONE DEPLETING SUBSTANCES:
 - 6-1. NO CONTAINING PBBs, PBBOs, CFCs, PBBEs, PBDPEs AND HCFCs.
- 7. PRODUCTION LOCATION
 - 7-1. PRODUCTS WILL BE PRODUCED IN CHINA OR THAILAND.

PAGE 3

DELTA MODEL: EFB1524SHGCGJ

8. P & Q CURVE:



* TEST CONDITION: INPUT VOLTAGE ----- OPERATION VOLTAGE TEMPERATURE ----- ROOM TEMPERATURE HUMIDITY ----- 65%RH

DELTA MODEL: EFB1524SHGCGJ

DIMENSIONS DRAWING LABEL:




0R



0R





NOTES:

- 1. LEAD WIRE: UL 1007 -F- AWG #24 BLACK WIRE NEGATIVE----(-) RED WIRE POSITIVE----(+)
- 2. ADD COATING MATERIAL ON PWB AND ADD GLUE ON PWB PAD.
- 3. THIS PRODUCT IS RoHS COMPLIANT



Application Notice

- 1. Delta will not guarantee the performance of the products if the application condition falls outside the parameters set forth in the specification.
- 2. A written request should be submitted to Delta prior to approval if deviation from this specification is required.
- 3. Please exercise caution when handling fans. Damage may be caused when pressure is applied to the impeller, if the fans are handled by the lead wires, or if the fan was hard-dropped to the production floor.
- 4. Except as pertains to some special designs, there is no guarantee that the products will be free from any such safety problems or failures as caused by the introduction of powder, droplets of water or encroachment of insect into the hub.
- 5. The above-mentioned conditions are representative of some unique examples and viewed as the first point of reference prior to all other information.
- 6. It is very important to establish the correct polarity before connecting the fan to the power source. Positive (+) and Negative (-). Damage may be caused to the fans if connection is with reverse polarity, if there is no foolproof method to protect against such error specifically mentioned in this spec.
- 7. Delta fans without special protection are not suitable where any corrosive fluids are introduced to their environment.
- 8. Please ensure all fans are stored according to the storage temperature limits specified. Do not store fans in a high humidity environment. We highly recommend performance testing is conducted before shipping, if the fans have been stored over 6 months.
- 9. Not all fans are provided with the Lock Rotor Protection feature. If you impair the rotation of the impeller for the fans that do not have this function, the performance of those fans will lead to failure.
- 10. Please be cautious when mounting the fan. Incorrect mounting of fans may cause excess resonance, vibration and subsequent noise.
- 11. It is important to consider safety when testing the fans. A suitable fan guard should be fitted to the fan to guard against any potential for personal injury.
- 12. Except where specifically stated, all tests are carried out at room (ambient) temperature and relative humidity conditions of 25°C, 65% RH. The test value is only for fan performance itself.
- 13. Be certain to connect an " $4.7\mu F$ or greater" capacitor to the fan externally when the application calls for using multiple fans in parallel, to avoid any unstable power.

Doc. No: FMBG-ES Form 001 Rev. 0001 Date: June 24, 2009