


## 150N06Y


150 Amps, 60 Volts N-CHANNEL MOSFET

### FEATURE

- 150A,60V, $R_{DS(ON)MAX}=6m\Omega$  @ $V_{GS}=10V/30A$
- Low gate charge
- Low  $C_{iss}$
- Fast switching
- 100% avalanche tested
- Improved dv/dt capability



TO-247



### Absolute Maximum Ratings ( $T_c=25^\circ C$ , unless otherwise noted)

Parameter	Symbol	150N06Y	UNIT
Drain-Source Voltage	$V_{DSS}$	60	V
Gate-Source Voltage	$V_{GSS}$	$\pm 30$	
Continuous Drain Current	$I_D$	150	A
Pulsed Drain Current(Note 1)	$I_{DM}$	450	
Single Pulse Avalanche Energy (Note 2)	$E_{AS}$	450	mJ
Avalanche Current(Note 1)	$I_{AR}$	30	A
Reverse Diode dV/dt (Note 3)	dV/dt	5.5	V/ns
Operating Junction and Storage Temperature Range	$T_J, T_{STG}$	-55 to +150	°C
Maximum lead temperature for soldering purposes, 1/8" from case for 5 seconds	$T_L$	260	°C
Mounting Torque	6-32 or M3 screw	10	lbf • in
		1.1	N • m

### Thermal Characteristics

Parameter	Symbol	TO-247	Units
Thermal resistance , Junction to Case	$R_{th(J-C)}$	0.8	°C/W
Maximum Power Dissipation	$T_c=25^\circ C$	156	W

**Electrical Characteristics (T<sub>c</sub>=25°C,unless otherwise noted)**

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
<b>Off Characteristics</b>						
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	V <sub>GS</sub> =0V,I <sub>D</sub> =250uA	60	—	—	V
Breakdown Temperature Coefficient /ΔT <sub>J</sub>	ΔBV <sub>DSS</sub>	Reference to 25°C, I <sub>D</sub> =250uA	—	0.6	—	V/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> =60V,V <sub>GS</sub> =0V	—	—	1	μ A
Gate-Body Leakage Current,Forward	I <sub>GSSF</sub>	V <sub>GS</sub> =20V,V <sub>DS</sub> =0V	—	—	100	nA
Gate-Body Leakage Current,Reverse	I <sub>GSSR</sub>	V <sub>GS</sub> =-20V,V <sub>DS</sub> =0V	—	—	-100	nA
<b>On Characteristics</b>						
Gate-Source Threshold Voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> =10V,I <sub>D</sub> =250uA	2	—	4	V
Drain-Source On-State Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> =10V,I <sub>D</sub> =30A	—	4.5	6.0	mΩ
<b>Dynamic Characteristics</b>						
Input Capacitance	C <sub>iss</sub>	V <sub>DS</sub> =30V,V <sub>GS</sub> =0V, f=1.0MHZ	—	4550	—	pF
Output Capacitance	C <sub>oss</sub>		—	625	—	pF
Reverse Transfer Capacitance	C <sub>rss</sub>		—	360	—	pF
<b>Switching Characteristics</b>						
Turn-On Delay Time	t <sub>d(on)</sub>	V <sub>DD</sub> =30V,I <sub>D</sub> =30A, R <sub>G</sub> =0.4Ω (Note4,5)	—	78	—	ns
Turn-On Rise Time	t <sub>r</sub>		—	119	—	ns
Turn-Off Delay Time	t <sub>d(off)</sub>		—	692	—	ns
Turn-Off Fall Time	t <sub>f</sub>		—	310	—	ns
Total Gate Charge	Q <sub>g</sub>	V <sub>DS</sub> =30V,I <sub>D</sub> =30A, V <sub>GS</sub> =10V, (Note4,5)	—	217	—	nC
Gate-Source Charge	Q <sub>gs</sub>		—	45	—	nC
Gate-Drain Charge	Q <sub>gd</sub>		—	30	—	nC
<b>Drain-Source Body Diode Characteristics and Maximum Ratings</b>						
Continuous Diode Forward Current	I <sub>S</sub>		—	—	150	A
Pulsed Diode Forward Current	I <sub>SM</sub>		—	—	450	A
Diode Forward Voltage	V <sub>SD</sub>	I <sub>S</sub> =30A,V <sub>GS</sub> =0V	—	—	1.3	V
Reverse Recovery Time	t <sub>rr</sub>	V <sub>GS</sub> =0V,I <sub>S</sub> =30A, dI <sub>F</sub> /dt=100A/us, (Note4)	—	37	—	ns
Reverse Recovery Charge	Q <sub>rr</sub>		—	23	—	uC

**Notes**

1. Repetitive Rating:pulse width limited by maximum junction temperature.
2. L=0.1mH,R<sub>g</sub>=25 Ω ,I<sub>AS</sub>=100A , starling T<sub>J</sub>=25°C.
3. I<sub>SD</sub>≤I<sub>D</sub>,dI/dt=200A/us,V<sub>DD</sub>≤BV<sub>DSS</sub>,starting T<sub>J</sub>=25 °C.
4. Pulse width≤300us;duty cycle≤2%.
5. Repetitive rating; pulse width limited by maximum junction temperature.


## RATING AND CHARACTERISTIC CURVES




Peak Diode Recovery dv/dt Test Circuit




Peak Diode Recovery dv/dt Waveforms




Switching Test Circuit




Switching Waveforms




Gate Charge Test Circuit



Gate Charge Waveform














Unclamped Inductive Switching Test Circuit



Unclamped Inductive Switching Waveforms


## RATING AND CHARACTERISTIC CURVES





**PACKAGE OUTLINE DIMENSIONS**

TO-247



Dim	Min	Max
A	20.0	22.0
B	15.5	16.0
C	5.7	6.3
D	4.0	4.4
E	19.0	21.0
F	1.1	1.3
G	3.5	3.8
H	18.3	20.2
I	4.9	5.2
J	2.3	2.5
K	0.55	0.65
L	39.0	42.0
P	10.7	10.9
F1	1.9	2.1
F2	2.9	3.1
mm		