

ABF206 THRU ABF210


SINGLE PHASE 2.0AMPS. GLASS PASSIVATED BRIDGE RECTIFIERS

FEATURE

- . Glass passivated junction.
- . Ideal for printed circuit board.
- . Reliable low cost construction utilizing molded plastic technique.
- . High surge current capability.
- . High temperature soldering guaranteed: 260°C/10 seconds at terminals.
- . UL Recognized File # E338195.

MECHANICAL DATA

- . Case Material: "Green" Molding compound, UL flammability classification rating 94V-0, "Free halogen"
- . Moisture sensitivity level: level 2a, per J-STD-020
- . Polarity: Polarity as marked on the body
- . Weight: 0.10g (approximately)



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.
Single phase, half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%

Type Number	SYM BOL	ABF206	ABF208	ABF210	units
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	600	800	1000	V
Maximum RMS Voltage	V_{RMS}	420	560	700	V
Maximum DC blocking Voltage	V_{DC}	600	800	1000	V
Maximum Average Forward rectified Current	$I_{F(AV)}$	2.0			A
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rate load (JEDEC method)	I_{FSM}	50			A
Maximum Instantaneous Forward Voltage @ $I_F = 2.0A$ DC @ $I_F = 0.8A$ DC	V_F	1.1 0.95			V
Maximum DC Reverse Current @ $T_J = 25^\circ C$ at rated DC blocking voltage @ $T_J = 125^\circ C$	I_R	5.0 100.0			μA
I^2t Rating for Fusing ($t < 8.3ms$)	I^2t	12.5			A^2Sec
Typical Junction Capacitance Per Leg (Note1)	C_J	16			pF
Typical Thermal Resistance (Note2)	R_{JC} R_{JA}	25 80			$^\circ C / W$
Storage Temperature	T_{STG}	-55 to +150			$^\circ C$
Operating Junction Temperature	T_J	-55 to +150			$^\circ C$

Note:

1. Measured at 1.0 MHz and applied reverse voltage of 4.0Vdc
2. Thermal resistance junction to case, lead and ambient in accordance with JESD-51.
Unit mounted on glass-epoxy substrate with 1oz/ft² 20x20 mm copper pad per pin with heatsink

RATING AND CHARACTERISTIC CURVES (ABF206 THRU ABF210)

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG.3-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT






FIG.4-TYPICAL REVERSE CHARACTERISTICS




Marking and packaging illustration

1、Marking



SYMBOL	Explanation
A	Product Name
B	Date Code
C	Trademark

2、Packaging



SPECIFICATIONS mm(inch)		PACKAGE	
SYMBOL	ITEM	ABF	
Carrier width		A	5.45(0.215)Max
Carrier length	B	7.0(0.276)Max	
Sprocket hole	d	ø1.55(0.061)Typ	
Reel outer diameter	D	330.0(13.0)Typ	
Reel inner diameter	D1	50.0(2.913)Min	
Feed hole diameter	D2	13.0(0.512)Typ	
Sprocket hole position	J	1.75(0.069)Typ	
Punch hole position	H	5.50(0.217)Typ	
Carrier depth	K	1.60(0.063)Typ	
Punch hole pitch	P	8.00(0.315)Typ	
Sprocket hole pitch	P0	4.00(0.157)Typ	
Embossment center	P1	2.00(0.079)Typ	
Overall tape thickness	T	0.30(0.012)Typ	
Tape width	W	12.0(0.472)Typ	
Reel width	W1	12.4(0.488)Min	