EVERLIGHT EVERLIGHT ELECTRONICS CO.,LTD.

Technical Data Sheet

0805 Package Chip LED(1.0mm Height)

17-21/Y2C-CP2Q2B/3T

Features

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS complaint version

Descriptions

- The 17-21 SMD Taping is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- Backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

Device Selection Guide

Part No.	Chip	Emitted Color	Resin Color	
	Material	Emitted Color		
17-21/Y2C-CP2Q2B/3T	AlGaInP	Brilliant Yellow	Water Clear	

Everlight Electronics Co., Ltd.

: 1 LifecyclePhase:正式發行

Revision

http://www.everlight.com

Prepared date:07-Jun-2007

Rev. 1 Page: 1 of 10 Prepared by: Zhang Qiang

Release Date: 2008-09-20 00:16:10.0


Expired Period: Forever



Device No:SZDSE-171-Y06



Package Outline Dimensions



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Everlight Electronics Co., Ltd. Device No:SZDSE-171-Y06

Prepared date:07-Jun-2007

http://www.everlight.com

Prepared by: ZhangQiang lease Date: 2008-09-20 00:16:10.

Page: 2 of 10

LifecyclePhase:正式發行

: 1

Revision

Release Date:2008-09-20 00:16:10.0 Expired Period: Forever



Absolute Maximum Ratings (Ta=25

Parameter	Symbol	Rating	Unit
Reverse Voltage	V_{R}	5	V
Forward Current	I_{F}	25	mA
Peak Forward Current (Duty 1/10 @1KHz)	I_{FP}	60	mA
Power Dissipation	P_d	60	mW
ElectrostaticDischarge (HBM)	ESD	2000	V
Operating Temperature	Topr	-40 ~ +85	
Storage Temperature	Tstg	-40~ +90	
Soldering Temperature	Tsol	Reflow Soldering:260 Hand Soldering:350	for 10 sec for 3 sec

Electro-Optical Characteristics (Ta=25)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	I_{V}	57.0	M-M	112.0	mcd	
Viewing Angle	2 1/2		140	1	deg	
Peak Wavelength	p	14- N	591		nm	
Dominant Wavelength	d	585.5		5915	nm	I _F =20mA
Spectrum Radiation Bandwidth			15		nm	
Forward Voltage	V_{F}	1.75		2.35	V	
Reverse Current	I_R			10	μА	V _R =5V

Notes:

- 1. Tolerance of Luminous Intensity ±11%
- 2. Tolerance of Dominant Wavelength ±1nm
- 3. Tolerance of Forward Voltage ±0.1V

Everlight Electronics Co., Ltd.

http://www.everlight.com

Device No:SZDSE-171-Y06

Prepared by: ZhangQiang

Page: 3 of 10

: 1 LifecyclePhase:正式發行

Revision

Prepared date:07-Jun-2007 Release Date:2008-09-20 00:16:10.0

Expired Period: Forever



Bin Range Of Dom. Wavelength

Group	Bin	Min	Max	Unit	Condition
С	D3	585.5	588.5		T 20 A
	D4	588.5	591.5	nm	$I_F=20\text{mA}$

Bin Range Of Luminous Intensity

Bin	Min	Max	Unit	Condition
P2	57.0	72.0		
Q1	72.0	90.0	mcd	I _F =20mA
Q2	90.0	112.0		

Bin Range Of Forward Voltage

Group	Bin	Min	Max	Unit	Condition
	0	1.75	1.95		- 1
В	1	1.95	2.15	V	I _F =20mA
	2	2.15	2.35		

Notes:

- 1. Tolerance of Luminous Intensity ±11%
- 2.Tolerance of Dominant Wavelength ±1nm
- 3. Tolerance of Forward Voltage ±0.1V

Everlight Electronics Co., Ltd.

Prepared date:07-Jun-2007

http://www.everlight.com

Device No:SZDSE-171-Y06
Revision : 1


LifecyclePhase:正式發行


Prepared by: ZhangQiang Release Date:2008-09-20 00:16:10.0


Page: 4 of 10


Expired Period: Forever


Typical Electro-Optical Characteristics Curves

















http://www.everlight.com

Label explanation

CAT: Luminous Intensity Rank


HUE: Dom. Wavelength Rank

REF: Forward Voltage Rank



Reel Dimensions





Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Everlight Electronics Co., Ltd.

Device No:SZDSE-171-Y06

Revision: 1

LifecyclePhase:正式發行

http://www.everlight.com

Prepared date:07-Jun-2007

Rev. 1 Pag


Page: 6 of 10

Prepared by: ZhangQiang Release Date:2008-09-20 00:16:10.0

Expired Period: Forever




Carrier Tape Dimensions: Loaded quantity 3000 PCS per reel



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Moisture Resistant Packaging



Everlight Electronics Co., Ltd.

Device No:SZDSE-171-Y06

Revision: 1

LifecyclePhase:正式發行

http://www.everlight.com

Prepared date:07-Jun-2007

Rev. 1

Page: 7 of 10

Prepared by: ZhangQiang Release Date:2008-09-20 00:16:10.0

Expired Period: Forever



Reliability Test Items And Conditions

The reliability of products shall be satisfied with items listed below.

Confidence level: 90%

LTPD: 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp.: 260 ±5 Min. 5sec.	6 Min.	22 PCS.	0/1
2	Temperature Cycle	H: +100 15min 5 min L: -40 15min	300 Cycles	22 PCS.	0/1
3	Thermal Shock	H: +100 5min 10 sec L: -10 5min	300 Cycles	22 PCS.	0/1
4	High Temperature Storage	Temp.: 100	1000 Hrs.	22 PCS.	0/1
5	Low Temperature Storage	Temp. : -40	1000 Hrs.	22 PCS.	0/1
6	DC Operating Life	$I_F = 20 \text{ mA}$	1000 Hrs.	22 PCS.	0/1
7	Hig <mark>h Temperatu</mark> re / Hig <mark>h H</mark> umidity	85 / 85%RH	1000 Hrs.	22 PCS.	0/1

http://www.everlight.com

Everlight Electronics Co., Ltd.

Device No:SZDSE-171-Y06 Prepared date:07-Jun-2007

Revision : 1

LifecyclePhase:正式發行

Expired Period: Forever

Prepared by: ZhangQiang

Release Date:2008-09-20 00:16:10.0

Rev. 1


Page: 8 of 10

Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
 - 2.2 Before opening the package, the LEDs should be kept at 30 or less and 90%RH or less.
 - 2.3 After opening the package: The LED's floor life is 1 year under 30 or less and 60% RH orless. If unused LEDs remain, it should be stored in moisture proof packages.
 - 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions. Baking treatment: 60±5 for 24 hours.
- 3. Soldering Condition
 - 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

Page: 9 of 10

Revision




4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350 for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



EVERLIGHT ELECTRONICS CO., LTD.

Office: No 25, Lane 76, Sec 3, Chung Yang Rd, Tucheng, Taipei 236, Taiwan, R.O.C Tel: 886-2-2267-2000, 2267-9936

Fax: 886-2267-6244, 2267-6189, 2267-6306

http://www.everlight.com

Everlight Electronics Co., Ltd.

http://www.everlight.com

Rev. 1 Page: 10 of 10

Device No:SZDSE-171-Y06
Revision: 1

Prepared date:07-Jun-2007

Prepared by: ZhangQiang Release Date:2008-09-20 00:16:10.0

Expired Period: Forever

LifecyclePhase:正式發行