



PINGWEI ENTERPRISE

SR320/SB320 THRU SR3200/SB3200


3.0AMPS. SCHOTTKY BARRIER RECTIFIERS

FEATURE

- . High current capability
- . Low forward voltage drop
- . Low power loss, high efficiency
- . High surge capability
- . High temperature soldering guaranteed
260°C /10sec/ 0.375" lead length at 5 lbs tension

MECHANICAL DATA

- . Terminal: Plated axial leads solderable per
MIL-STD 202E, method 208C
- . Case: Molded with UL-94 Class V-0 recognized
Flame Retardant Epoxy
- . Polarity: color band denotes cathode
- . Mounting position: any

DO-27/DO-201AD

Dimensions in inches and (millimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	SYM	SR 320	SR 330	SR 340	SR 350	SR 360	SR 380	SR 390	SR 3100	SR 3150	SR 3200	units						
	BOL	SB 320	SB 330	SB 340	SB 350	SB 360	SB 380	SB 390	SB 3100	SB 3150	SB 3200							
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	20	30	40	50	60	80	90	100	150	200	V						
Maximum RMS Voltage	V_{RMS}	14	21	28	35	42	56	63	70	105	140	V						
Maximum DC blocking Voltage	V_{DC}	20	30	40	50	60	80	90	100	150	200	V						
Maximum Average Forward Rectified Current .375"(9.5mm) lead length at $T_L = 90^\circ C$	$I_{F(AV)}$	3.0										A						
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load (JEDEC method)	I_{FSM}	80.0										A						
Maximum Forward Voltage at 3.0A DC	V_F	0.45	0.55	0.70			0.85			0.95		V						
Maximum DC Reverse Current @ $T_A = 25^\circ C$ at rated DC blocking voltage @ $T_A = 100^\circ C$	I_R	0.5 40.0				0.1 10.0						mA						
Typical Junction Capacitance (Note 1)	C_J	300				72						pF						
Typical Thermal Resistance (Note 2)	$R_{(JA)}$	40										°C/W						
Storage Temperature	T_{STG}	-55 to +150										°C						
Operation Junction Temperature	T_J	-55 to +125				-55 to +150						°C						

Note:

1. Measured at 1.0 MHz and applied reverse voltage of 4.0Vdc
2. Thermal Resistance from Junction to Ambient at 0.375" (9.5mm) lead length, vertical P.C. Board Mounted.

RATING AND CHARACTERISTIC CURVES (SR320/SB320 THRU SR3200/SB3200)

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG.3-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.4-TYPICAL REVERSE CHARACTERISTICS

