



# P 沟道增强型场效应晶体管

## P-CHANNEL MOSFET

### FHU9540C/FHD9540C

#### 主要参数 MAIN CHARACTERISTICS

ID	-35 A
VDSS	-100 V
Rdson-typ (@Vgs=10V)	32mΩ
Rdson-typ (@Vgs=4.5V)	36mΩ
Qg-typ	66nC


#### 产品特性 FEATURES

低栅极电荷	Low gate charge
低 Crss (典型值 190pF)	Low Crss (typical 190pF )
开关速度快	Fast switching
100%经过雪崩测试	100% avalanche tested
高抗 dv/dt 能力	Improved dv/dt capability
RoHS 产品	RoHS product


#### 用途 APPLICATIONS

负载开关	Load switch
------	-------------

#### 封装形式 Package




TO-251  
FHU series



TO-252  
FHD series

#### 等效电路 Equivalent Circuit



#### 绝对最大额定值 ABSOLUTE RATINGS (Tc=25°C)

项目 Parameter	符号 Symbol	数值 Value		单位 Unit
		FHU9540C	FHD9540C	
最高漏极—源极直流电压 Drain-Source Voltage	VDS	-100		V
连续漏极电流* Drain Current -continuous *	ID (Tc=25°C)	-35		A
	Id (Tc=100°C)	-25		A
最大脉冲漏极电流 (注 1) Drain Current – pulse (note 1)	IMD	-140		A
最高栅源电压 Gate-Source Voltage	VGS	±20		V
单脉冲雪崩能量 (注 2) Single Pulsed Avalanche Energy (note 2)	EAS	480		mJ
雪崩电流 (注 1) Avalanche Current (note 1)	IA	17		A
重复雪崩能量 (注 1) Repetitive Avalanche Current (note 1)	EAR	16		mJ
二极管反向恢复最大电压变化速率 (注 3) Peak Diode Recovery dv/dt (note 3)	dv/dt	5.0		V/ns
耗散功率 Power Dissipation	PD (TC=25°C)	105		W
	-Derate above 25°C	0.71		W/°C
最高结温及存储温度 Operating and Storage Temperature Range	TJ, TSTG	-55~+150		°C
引线最高焊接温度 Maximum Lead Temperature for Soldering Purposes	TL	300		°C

\*漏极电流由最高结温限制

\*Drain current limited by maximum junction temperature

## 电特性 ELECTRICAL CHARACTERISTICS

项目 <b>Parameter</b>	符号 <b>Symbol</b>	测试条件 <b>Tests conditions</b>	最小 <b>Min</b>	典型 <b>Typ</b>	最大 <b>Max</b>	单位 <b>Units</b>	
<b>关态特性 Off -Characteristics</b>							
漏—源击穿电压 Drain-Source Voltage	BVDSS	Id=-250μA, VGS=0V	-100	-	-	V	
击穿电压温度特性 Breakdown Voltage Temperature Coefficient	ΔBVdss/Δ TJ	Id=-250μA, referenced to 25°C	-	-0.1	-	V/°C	
零栅压下漏极漏电流 Zero Gate Voltage Drain Current	Idss	VDS=-100V, VGS=0V, Tc=25°C	-	-	-1	μA	
		VDS=-80V, Tc=125°C	-	-	-10	μA	
栅极体漏电流 Gate-body leakage current	IGSS (F/R)	VDS=0V, VGS =±20V	-	-	±100	nA	
<b>通态特性 On-Characteristics</b>							
阈值电压 Gate Threshold Voltage	VGS(th)	VDS = VGS , Id=-250μA	-1.3	-1.95	-2.5	V	
静态导通电阻 Static Drain-Source On-Resistance	RDS(ON)	VGS =-10V , Id=-15A	-	32	38	mΩ	
		VGS =-4.5V , Id=-10A	-	36	45		
正向跨导 Forward Transconductance	gfs	VDS = -5V, Id=-12A (note 4)	-	28	-	S	
<b>动态特性 Dynamic Characteristics</b>							
栅电阻 Gate Resistance	Rg	f=1.0MHz, VDS OPEN	-	1.5	-	Ω	
输入电容 Input capacitance	Ciss	VDS=-25V, VGS =0V, f=1.0MHz	-	3100	-	pF	
输出电容 Output capacitance	Coss		-	360	-		
反向传输电容 Reverse transfer capacitance	Crss		-	190	-		
<b>开关特性 Switching Characteristics</b>							
延迟时间 Turn-On delay time	td(on)	VDS=-50V, Id=-35A, RG=4.7Ω VGS =-10V (note 4, 5)	-	15	-	ns	
上升时间 Turn-On rise time	tr		-	17	-	ns	
延迟时间 Turn-Off delay time	td(off)		-	31	-	ns	
下降时间 Turn-Off Fall time	tf		-	53	-	ns	
栅极电荷总量 Total Gate Charge	Qg	VDS =-80V , Id=-35A , VGS =-10V (note 4, 5)	-	66	-	nC	
栅—源电荷 Gate-Source charge	Qgs		-	17	-	nC	
栅—漏电荷 Gate-Drain charge	Qgd		-	23	-	nC	
<b>漏—源二极管特性及最大额定值 Drain-Source Diode Characteristics and Maximum Ratings</b>							
正向最大连续电流 Maximum Continuous Drain -Source Diode Forward Current	Is		-	-	-35	A	
正向最大脉冲电流 Maximum Pulsed Drain-Source Diode Forward Current	ISM		-	-	-140	A	
正向压降 Drain-Source Diode Forward Voltage	VSD	VGS=0V, Is=-35A	-	-0.82	-1.3	V	
反向恢复时间 Reverse recovery time	trr	VGS=0V, Is=-35A ,dI/dt=100A/μs (note 4)	-	52	-	ns	
反向恢复电荷 Reverse recovery charge	Qrr		-	96	-	nC	

## 热特性 THERMAL CHARACTERISTIC

项目 Parameter	符号 Symbol	最大值 Max	单位 Unit
结到管壳的热阻 Thermal Resistance, Junction to Case	R <sub>th(j-c)</sub>	1.45	°C/W
结到环境的热阻 Thermal Resistance, Junction to Ambient	R <sub>th(j-A)</sub>	110	°C/W

注释:


- 1: 脉冲宽度由最高结温限制
- 2: L=1mH, I<sub>AS</sub>=-17A, V<sub>DD</sub>=-48V, R<sub>G</sub>=25 Ω,起始结温 T<sub>J</sub>=25°C
- 3: I<sub>SD</sub> ≤25A,di/dt ≤300A/μs,V<sub>DD</sub>≤BV<sub>DSS</sub>,起始结温 T<sub>J</sub>=25°C
- 4: 脉冲测试: 脉冲宽度 ≤300μs,占空比≤2%
- 5: 基本与工作温度无关

Notes:


- 1: Pulse width limited by maximum junction temperature
- 2: L=1mH, I<sub>AS</sub>=-17A, V<sub>DD</sub>=-48V, R<sub>G</sub>=25 Ω,Starting T<sub>J</sub>=25°C
- 3: I<sub>SD</sub> ≤25A,di/dt ≤300A/μs,V<sub>DD</sub>≤BV<sub>DSS</sub>, Starting T<sub>J</sub>=25°C
- 4: Pulse Test: Pulse Width ≤300μs,Duty Cycle≤2%
- 5: Essentially independent of operating temperature

## Typical Characteristics


**Power Dissipation**




**Drain Current**




**Safe Operation Area**









**Drain Current**




**Thermal Transient Impedance**




## Typical Characteristics









**Gate Charge Test Circuit & Waveform**



**Resistive Switching Test Circuit & Waveforms**





**Unclamped Inductive Switching Test Circuit & Waveforms**



Peak Diode Recovery  $dv/dt$  Test Circuit & Waveforms

---


**印记 Marking:**



外形尺寸:

Package Dimension:

TO-251




DIM	MILLIMETERS
A	5.34±0.30
B	6.00±0.30
C	1.05±0.30
D	11.31±0.30
E	0.76±0.15
F	2.28±0.15
G	2.30±0.30
H	1.06±0.30
I	(4-10)°
J	0.51±0.15
K	0.52±0.15
L	0.80±0.30
M	60°
N	0.75±0.30
O	1.80±0.30
P	6.60±0.30
Q	4.85±0.30
R	(4-8.5)°
S	5.30±0.30
T	6.90±0.30
U	0.05±0.05
V	0.05±0.05
W	1.15±0.25
Y	0.85±0.25

(Unit: mm)

外形尺寸:

Package Dimension:

TO-252



DIM	MILLIMETERS
A	5.34±0.30
B	6.00±0.30
C	1.05±0.30
D	9.95±0.30
E	0.76±0.15
F	2.28±0.15
G	2.30±0.30
H	1.06±0.30
I	(4-10)°
J	0.51±0.15
K	0.52±0.15
L	0.80±0.30
M	60°
N	(0-10)°
O	0.05±0.05
P	6.60±0.30
Q	25°
R	(4-8.5)°
S	R0.40
T	R0.40
U	0.05±0.05
V	0.05±0.05
W	0.90±0.30
a	1.80±0.30
b	0.75±0.30
c	4.85±0.30
d	5.30±0.30
e	6.90±0.30

(Units: mm)