Serial No.: AL190801004-00

Specifications for Approval

PRODUCT TYPE	Crystal Oscillator HSO751S				
NOMINAL FREQUENCY		33.333000MHz			
H.ELE. SAMPLE O/N	EOS-J70469-2				
H.ELE. P/N		SSR03333313CH			
RELEASE DATE	2019/08/01				
VERSION	00				
MSL		Level 1			
PRODUCT STD.	✓ Pb free ✓ RoHS 2.0 Compliant✓ HF-Halogen free ✓ REACH Compliant				
	☐ AEC-Q100 ☐ AEC-Q200	(Grade □0 □1 □2 □3□4)			
CUSTOMER P/N					
APPLICATION & MODEL					
APPROVED BY CUSTOME	₹				
		(DATE)	<u>) </u>		
			_		

Harmony	Electronic	s Corp.		
			Country of Origin:	Kaohsiung, Taiwan
F. S. TSAI	C. H. WENG	U. F. CHEN		Ratchaburi, Thailand
(APPROVE)	(CHECK)	(PREPARE)		Shenzhen, China
				Dongguan, China



REV. No.	DATE	REASON	REVISE CONTENTS
0	2019/08/01	New	



Contents

ITEM	PAGE
1. CRYSTAL OSCILLATOR SPECIFICATION	3-4
2. DIMENSIONS	4
3. MARKING	5
4. INSIDE STRUCTURE	5
5. HANDLING SUGGESTIONS	5-6
6. EMBOSS CARRIER TAPE&REEL	7-8
7. PACKAGE	8
8. MECHANICAL PERFORMANCE	9
9. ENVIRONMENTAL PERFORMANCE	9
10. APPENDIX	

2



1. CRYSTAL OSCILLATOR SPECIFICATION

■ Electrical Specifications

		Ele	ctrical Sp	ec.		Condition
Items	Symbol	Min	Туре	Max	Unit	
Output Frequency	(FL)		33.333000)	MHz	
Mode of Oscillation		Fι	undament	al		
Frequency Stability	Δf/F	-50	-	+50	ppm	@3.3±0.3V/-10~70°C
Operating temp. range	Topr	-10	25	+70	°C	
Supply voltage	Vdd	3.0	3.3	3.6	V	
Pin #1 options				`	YES .	
Output load		C-1	MOS CL	=15pF (Id	d1, Idd2 tes	st at No Load)
Current consumption 1 (#1 pin: open or "H")	ldd1	-	-	25	mA	
Current consumption 2 (#1 pin: "L" level)	Idd2	-	-	0.02	mA	
Low level output voltage	Vol	-	-	0.1xVdd	V	
High level output voltage	Voh	0.9xVdd	-	-	V	
Symmetry	Duty	40	50	60	%	
Rise & Fall time	Tr & Tf	-	-	10	ns	
Low level input current	lil	-	-	-100	uA	@3.3V/ 25±3°C
High Level input current	lih	-	-	100	uA	
Low level input voltage	Vil	-	-	Vddx0.3	V	
High level input voltage	Vih	Vddx0.7	-	-	V	
Output disable time	Tplz	-	-	100	nsec	
Output enable time	Tpzl	-	-	100	nsec	
Aging	-	-5	-	5	ppm/year	
Start-up time		-	-	10	ms	
Jitter, Phase	RMS(1-σ)	-	-	1	ps	12KHz~20MHz Frequency Band

Note: Storage Temperature is only for the product itself.


■ Absolute Maximum Ratings

Item	Symbol	Value	Unit
Vdd terminal voltage	Vdd	-0.5 ~ 7.0	V
Input terminal voltage	Vcont	-0.5 ~ Vdd+0.5	V
Output terminal voltage	Vout	-0.5 ~ Vdd+0.5	V
Output terminal current	lout	15	mA
Storage temp. range	Tstr	-55 ~ 12 5	deg.C

3




■ TEST Circuit




CL = Include jig & probe capacitance (Refer to 4)

Switch	Out term.
Н	Oscillation out
Open	Oscillation out
L	High Z

■ Output Wave Form





■ Input and Output Condition



2. DIMENSION


TOP VIEW





BOTTOM VIEW

TOP VIEW Land Pattern Layout




Pin	Connections
#1	OE(Output Enable)
#2	GND
#3	Output
#4	Vdd

Tolerance: ±0.2 Unit: mm

^{*} Note: The Index mark was defined by the BASE suppliers.



3. MARKING




Note:

- 1. Laser marking.
- 2. Date Code:

V V224	2010	2011	2012	2013	2014	2015	2016	2017	2018	2019
Y= Year	2020	2021	2022	2023	2024	2025	2026	2027	2028	2029
Code	0	1	2	3	4	5	6	7	8	9

M= Month	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
Code	Α	В	С	D	Е	F	G	Н	J	K	L	М

4. INSIDE STRUCTURE



Reference	drawing
Mererence	urawing

terence drawing								
No.	Component	Material	Note					
1	Base-Ceramic	Ceramic	Al_2O_3					
2	Lid	Metal	Fe- Ni -Co					
3	Kovar	Metal	Fe-Ni-Co					
4	Crystal Blank	Silicon	SiO₂ Rectangular At-Cut					
5	Electrode	Metal	-					
6	Connective Adhesive	Silver Powder	Ag					
7	Bonding Wire	Metal	Au					
8	IC	Silicon	Si, Al					
9	Pad	Metal	W Ni-Plating Au-Plating					

※The use prohibition chemistry substance of Table 1 of DHE-0204-1 (HE-QA-24) is not included in this item.

5. HANDLING SUGGESTION


■ Reflow Condition

Please stay with our proposed reflow condition and do soldering within 2 times.

	<u> </u>				
(1)	Preheat	160~180d	eg.C	120 sec.	
(2)	Primary heat	>=220 de	eg.C	100±20 sec.	
(3)	Peak	260±5 d	eg.C	10 sec. Max.	

■ Manual Solder iron (Example)

Bit temp.: 350°C max., Time: 3sec max., Each terminal only should be soldered once.





■ Mounting Conditions

Our products are suitable for most automated SMT processes. However, we strongly advise all our customers to conduct SMT sampling prior to mass production in order to make sure production processes will not affect the properties and specifications of our product. Seal welding and mounting procedures involving the use of ultra-sonic processes are not recommended and will affect and/or damage the internal properties of our product. Excessive shock during the mounting process will also affect the product and we strongly recommend setting SMT conditions to minimize such conditions.

If a possibility of the PCB being warped exists we strongly advise to ensure the degree of warping will not affect the product.

Please also ensure the operating characteristics and or soldering conditions are all within the specifications of use for our product.

Ultimately the worst case scenario of all the above will lead to cases of non-oscillation but other negative effects are also likely should our products be used in an inappropriate way. Please note such cases of misuse and its related quality issues are not included in our product warranty.

■ Cleansing Conditions

General cleaning solutions may be used to clean our products but we always recommend testing to be performed prior to mass production processes. Ultrasonic cleaning procedures are not recommended and we strongly advise other forms of cleansing to be evaluated first. Unsuitable cleansing may lead to a number of negative effects such as damage to the product surface, discoloration of the product, corrosion of the package, package contamination, illegible marking, etc. Please note cases of unadvised treatment and its related quality issues are not included in our product warranty.

■ Storage Conditions

Please ensure our products are preserved appropriately in their original packaging. Irregular environmental instances of moisture will affect our product's stability and may cause problems such as frequency instability, soldering ability and conditions, package defects, and other problems. It is essential to keep our products in a clean dust-free environment out of direct sunlight.

Our products' storage conditions should at least meet the following condition:

Environmental Temperature: + 40 degrees Celsius Maximum


Relative Humidity: 80% Maximum

Please note storage instances which do not conform to our guidelines and the related quality issues produced as an outcome are not included in our product warranty.




6. EMBOSS CARRIER TAPE AND REEL


■ Carrier Tape



User Direction of feed



■ Reel



■ Material of The Tape

Таре	Material	
Carrier tape	PS Conductive	
Top tape	Polyester	

■ Joint of tape

The carrier-tape and top cover-tape should not be jointed.




■ Release strength of cover tape

The force should be controlled between 0.1N to 0.7N under following condition.

Pulling direction: 165° to 180°

Speed: 300mm/min.


Otherwise unless specified.



Label Contents


Other standards shall be based on JIS C 0806-1990.

7. PACKAGE



One reel quantity: [1000pcs]&[3000pcs]

- SPEC. No.: Parts No.: Lot No .: FREQ .: MHz RoHS 2.0+HF HARMONY ELECTRONICS CORP.
 - The label will be stickled on all reels.
- 1)Top and bottom with 2.3cm thickness foam-rubber cushion for protection.
- ②Carton's Q'TY:1~15 pcs.
- 3Carton Type=A,B,C use 4 trigon pillar to fasten the Reel.





8. MECHANICAL PERFORMANCE

Item		Test Methods	Specifications Code
1	Shock	Dropping from 50 cm height 3 times on 30mm Concrete Floor. Refer to: JIS C 60068-2-32	Α
2	Vibration	Frequency 10-55Hz, Sine Wave full amplitude of 0.8mm to X, Y and Z 3 axes, Duration of 2 hours to each axis. Refer to: JIS C 60068-2-6/MIL-HDBK-781A 6.5.2	А
3	Leakage Test	Leak Rate 1.0x10 ⁻⁹ Pa-m³/sec. Max. Measured by Helium leak detector. Refer to: JIS C 60068-2-17	
4	Solder ability	After applying ROSIN Flux, dipping in solder bath at 245deg.C +/- 5deg.C for 3+/-0.5 sec. Refer to: JIS C 60068-2-20/C 60068-2-58	В

9. ENVIRONMENT PERFORMANCE

ltem		Test Methods	Specifications Code
1	Resistance of Soldering Heat	Performing as the following reflow: Refer to: JIS C 60068-2-58	А
2	Humidity	Temperature 60° C+/- 2° C, RH 90~95%, Duration of 240 hours. Back to the room temperature first, then check the component after 1~2 hours. Refer to: JIS C 60068-2-3	А
3	Storage in Low Temperature	-40deg.C +/-2deg.C, Duration of 240 hours. Back to the room temperature first, then check the component after 1~2 hours. Refer to: JIS C 60068-2-1	А
4	Storage in High Temperature	+85deg.C +/-2deg.C, Duration of 240 hours. Back to the room temperature first, then check the component after 1^2 hours. Refer to: JIS C 60068-2-2	А
5	Thermal shock	-40deg.C +/-2deg.C (30min) ↔ +85deg.C +/-2deg.C (30min) 25 cycles. And Temperature Increasing/reducing time ≦ 3mins. Back to the room temperature first, then check the component after 1~2 hours. Refer to: JIS C 0025	

Specifications code	Specifications	
Α	Frequency variation shall be within +/-5ppm	
В	More than 90% of lead shall be covered by new solder.	

FACTORY LOCATION HEAD OFFICE/TAIWAN FACTORY

NO.39, HUADONG RD., DALIAO DIST., DAFA INDUSTRIAL PARK, KAOHSIUNG CITY 831.

CHINA FACTORY

SHEN ZHEN

JU YUAN INDUSTRIAL PARK, QIAO TANG ROAD, TANG WEI COMMUNITY, FUYONG, BAOAN DISTRICT, SHEN ZHEN CITY (Post Code:518103).

DONGGUAN

BUILDING A1, HUAZHI INDUSTRIAL PARK, NO.38, JINGFU EAST ROAD, DALANG TOWN, DONGGUAN CITY.

THAILAND FACTORY

66MOO 5, KAONGU-BEOKPRAI RD., T.BEOKPRAI, A. BANPONG, RATCHABURI PROVINCE 70110.

SERVICE CENTER TAIPEI OFFICE

2F., NO.409, SEC.2, TIDING BLVD., NEIHU DISTRICT, TAIPEI CITY 114, TAIWAN TEL: 886-2-26588883 FAX: 886-2-26588683

CONTACT INFORMATION

E-MAIL: contactus@hele.com.tw

