

Technical Data Sheet

0805 Package Chip LED (0.8mm Height)

17-215/GPC -AL1M2L/3T

Features

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version

Descriptions

- The 17-215 SMD Taping is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- Automotive: backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.
- Indoor signboard use.


Device Selection Guide


D. AN.		T 0.1	
Part No.	Material	Emitted Color	Lens Color
17-215/GPC-AL1M2L/3T	AlGaInP	Pale Green	Water Clear




Everlight Electronics Co., Ltd. http://www.everlight.com Rev.1 Page: 1 of 10


Package Outline Dimensions








For reflow soldering (propose)





Note: The tolerances unless mentioned are ± 0.1 mm, Unit = mm

Everlight Electronics Co., Ltd.

Device No.: SZDSE-175-G12

http://www.everlight.com

Prepared date: 10-Jun-2006

Rev.1

Page: 2 of 10

Prepared by: Wu xiaowei



Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit	
Reverse Voltage	V_R	5	V	
Forward Current	I F	25	mA	
Operating Temperature	Topr	-40 ~ +85	$^{\circ}\!\mathbb{C}$	
Storage Temperature	Tstg	-40 ~ +90	$^{\circ}\!\mathbb{C}$	
Electrostatic Discharge(HBM)	ESD	2000	V	
Power Dissipation	Pd	60	mW	
Peak Forward Current (Duty 1/10 @1KHz)	Īfp	60	mA	
Soldering Temperature	Tsol	Reflow Soldering : 260 $^{\circ}$ C for 10 sec. Hand Soldering : 350 $^{\circ}$ C for 3 sec.		

Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	Iv	11.5		28.5	mcd	
Peak Wavelength	λp		561		nm	
Dominant Wavelength	λd	557.5		567.5	nm	
Spectrum Radiation Bandwidth	Δλ		20		nm	I _F =20mA
Viewing Angle	2 \theta 1/2		130		deg	
Forward Voltage	VF	1.70		2.30	V	
Reverse Current	Ir			10	μΑ	V _R =5V

Notes:

- 1.Tolerance of Luminous Intensity ±10%
- 2.Tolerance of Dominant Wavelength ±1nm
- 3.Tolerance of Forward Voltage ±0.05V

Everlight Electronics Co., Ltd. http://www.everlight.com Rev.1 Page: 3 of 10



Bin Range Of Dom. Wavelength

Group	Bin	Min	Max	Unit	Condition
	C10	557.5	559.5		
	C11	559.5	561.5		
A	C12	561.5	563.5	nm	$I_F = 20 \text{mA}$
	C13	563.5	565.5		
	C14	565.5	567.5		

Bin Range Of Luminous Intensity

			1	
Bin	Min	Max	Unit	Condition
L1	11.5	14.5	mcd	I _F =20mA
L2	14.5	18.0		
M1	18.0	22.5		
M2	22.5	28.5		

Bin Range Of Luminous Voltage

Group	Bin	Min	Max	Unit	Condition	
L	19	1.70	1.80			
	20	1.80	1.90	V	I _F =20mA	
	21	1.90	2.00			
	22	2.00	2.10			
	23	2.10	2.20			
	24	2.20	2.30			

Notes:

1.Tolerance of Luminous Intensity ±10%

2.Tolerance of Dominant Wavelength ±1nm


3.Tolerance of Forward Voltage ±0.05V


Everlight Electronics Co., Ltd. http://www.everlight.com Rev.1 Page: 4 of 10


EVERLIGHT ELECTRONICS CO.,LTD.

17-215/GPC-AL1M2L/3T


Typical Electro-Optical Characteristics Curves









Device No.: SZDSE-175-G12







Prepared by: Wu xiaowei

Everlight Electronics Co., Ltd. Page: 5 of 10 http://www.everlight.com Rev.1 Prepared date: 10-Jun-2006

Label explanation


CAT: Luminous Intensity Rank

HUE: Dom. Wavelength Rank

REF: Forward Voltage Rank




Reel Dimensions



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm


Everlight Electronics Co., Ltd. http://www.everlight.com Rev.1 Page: 6 of 10

Carrier Tape Dimensions: Loaded quantity 3000PCS per reel



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Moisture Resistant Packaging



Everlight Electronics Co., Ltd. Device No. : SZDSE-175-G12 http://www.everlight.com

Prepared date: 10-Jun-2006

Rev.1

Page: 7 of 10

Prepared by: Wu xiaowei



Reliability Test Items And Conditions

The reliability of products shall be satisfied with items listed below.

Confidence level: 90%

LTPD: 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp. : 260°C±5°C Min. 5sec.	6 Min.	22 PCS.	0/1
2	Temperature Cycle	$H: +100^{\circ}\mathbb{C}$ 15min $\int 5 \text{ min}$ $L: -40^{\circ}\mathbb{C}$ 15min	300 Cycles	22 PCS.	0/1
3	Thermal Shock	$H: +100^{\circ}\mathbb{C}$ 5min $\int 10 \sec$ $L: -10^{\circ}\mathbb{C}$ 5min	300 Cycles	22 PCS.	0/1
4	High Temperature Storage	Temp. : 100°C	1000 Hrs.	22 PCS.	0/1
5	Low Temperature Storage	Temp. : -40°€	1000 Hrs.	22 PCS.	0/1
6	DC Operating Life	$I_F = 20 \text{ mA}$	1000 Hrs.	22 PCS.	0/1
7	High Temperature / High Humidity	85°C / 85% RH	1000 Hrs.	22 PCS.	0/1

Everlight Electronics Co., Ltd. http://www.everlight.com Rev.1 Page: 8 of 10

Precautions For Use


1. Over-current-proof

Customer must apply resistors for protection , otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
 - 2.2 Before opening the package, the LEDs should be kept at 30°C or less and 90%RH or less.
 - 2.3 The LEDs should be used within a year.
 - 2.4 After opening the package, the LEDs should be kept at 30° C or less and 60° RH or less.
 - 2.5 The LEDs should be used within 168 hours (7 days) after opening the package.
 - 2.6 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

Baking treatment : $60\pm5^{\circ}$ C for 24 hours.

- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.
- 4.Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350°C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.


Everlight Electronics Co., Ltd. http://www.everlight.com Rev.1 Page: 9 of 10

Device No.: SZDSE-175-G12 Prepared date: 10-Jun-2006 Prepared by: Wu xiaowei



5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



EVERLIGHT ELECTRONICS CO., LTD.

Office: No 25, Lane 76, Sec 3, Chung Yang Rd, Tucheng, Taipei 236, Taiwan, R.O.C Tel: 886-2-2267-2000, 2267-9936

Fax: 886-2267-6244, 2267-6189, 2267-6306

http://www.everlight.com

Everlight Electronics Co., Ltd. http://www.everlight.com Rev.1 Page: 10 of 10