


DATASHEET

SMD B

19-223/R6GHC-C01/2T(XY)



Features

- Package in 8mm tape on 7" diameter reel.
- · Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version.
- Compliance with EU REACH.
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm)

Description

- The 19-223 SMD LED is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- Backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.

Š.

www.everlight.com



- Flat backlight for LCD, switch and symbol.
- General use.





Device Selection Guide

Device Selection Guide							
Code	Chip Materials		Emitted Color		Resin Color		
R6	AlGalnP		Brilliant		Water Class		
GH	InGaN		Brilliant		— Water Clear		
Absolute Maximum Ratings (Ta=25)							
Parameter	Symbol	Code		Rating	Unit		
Reverse Voltage	V_R			5	V		
Forward Current		R6		25			
	l _F	GH		25	mA		
eak Forward Current (Duty 1/10 @1KHz)	I _{FP}	R6		60			
		GH		95	mA		
Power Dissipation	Pd	R6	1	60			
		GH		100	mW		
Electrostatic Discharge	ESD _{HBM}	R6		2000			
		GH		150	V		
Operating Temperature	T_{opr}			-40 ~ +85			
Storage Temperature	Tstg			-40 ~ +90			
Soldering Temperature	Tsol			Reflow Solderin	=		



Electro-Optical Characteristics (Ta=25)

Parameter	Symbol	Code	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	lv	R6	14.5		36.0	- mcd	
		GH	45.0		112.0		
Viewing Angle	2θ _{1/2}			130		deg	_
Peak Wavelength	р	R6		632		– nm	- I _F =5mA -
		GH		518		- nm	
Dominant Wavelength	d	R6	617.5		629.5	- nm	
		GH	520.0		535.0		
Spectrum Radiation Bandwidth		R6		20		- nm	
		GH		35			
Forward Voltage	V _F	R6	1.60	1.90	2.30	- V	
		GH	2.70	3.3 0	3.70		
Reverse Current	I _R	R6			10	- μΑ	V _R =5V
		GH			50		v _R -5v

Note:

1. Tolerance of Luminous Intensity: ±11%

2. Tolerance of Dominant Wavelength ±1nm

3. Tolerance of Forward Voltage: ±0.1V



R6

Bin Range of Luminous Intensity

Bin Code	Min.	Max.	Unit	Condition			
LA	14.5	22.5		J. 5A			
MA	22.5	36.0	mcd	I _F =5mA			
Bin Range Of Dom. Wavelength							
Bin Code	Min.	Max.	Unit	Condition			
E4	617.5	621.5					
E5	621.5	625.5	nm	I _F =5mA			
E6	625.5	629.5					

GH

Bin Range Of Forward Voltage

Bin Code	Min.	Max.	Unit	Condition
P1	45.0	57.0		
P2	57.0	72.0	mcd	I _F =5mA
Q1	72.0	90.0	med	IF -SITIA
Q2	90.0	112.0		

Bin Range Of Dom. Wavelength

Bin Code	Min.	Max.	Unit	Condition
X	520.0	525.0		
Υ	525.0	530.0	nm	I _F =5mA
Z	530.0	535.0		

Note:


1.Tolerance of Luminous Intensity: ±11%


2. Tolerance of Dominant Wavelength ±1nm


₹ 5





Typical Electro-Optical Characteristics Curves R6





















GH Typical Electro-Optical Characteristics Curves

















Package Dimension




Suggested pad dimension is just for reference only. Please modify the pad dimension based on individual need.

Note: Tolerances unless mentioned ±0.1mm. Unit = mm



Moisture Resistant Packing Materials Label Explanation



· CPN: Customer's Product Number

• P/N: Product Number

· QTY: Packing Quantity

· CAT: Luminous Intensity Rank


• HUE: Chromaticity Coordinates & Dom.

Wavelength Rank

• REF: Forward Voltage Rank

· LOT No: Lot Number


Reel Dimensions



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm




Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel



Note: The tolerances unless mentioned is ± 0.1 mm ,Unit = mm

Moisture Resistant Packaging





Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).


- 2. Storage
- 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package: The LEDs should be kept at 30 or less and 90%RH or less.
- 2.3 After opening the package: The LED's floor life is 1 year under 30 or less and 60% RH or less.

If unused LEDs remain, it should be stored in moisture proof packages

2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

Baking treatment: 60±5 for 24 hours.

- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

Approved

4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350 for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.


5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.

₹ 1

LifecyclePhase:

www.everlight.com







Application Restrictions

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.

