



# RCY CONNECTOR

**Disconnectable Crimp style Wire-to-wire connectors** 



The RCY connector is a compact, 2.5 mm pitch wire-to-wire connector for use with a variety of circuits, from signal circuits to power supply circuits, in electrical equipment which is becoming more and more compact. The employment of a free spring contact method ensures stable contact performance, and superb working efficiency of insertion and removal.



### Features —

# • Use of a free spring contact for superb creep characteristics

The contact section features a free spring contact construction, which effectively minimizes stress (creep) caused by repeated insertion and removal at high temperatures. Connector insertion and removal is also smooth, ensuring stable connection performance.

### Compact design

The RCY connector is designed to be compact. When mated, its overall length is just 23.3 mm and its thickness is 4.0 mm.

### Housing lock

Because a lock is provided inside the housing, external force is not applied to the lock.

### Specifications -

Current rating: 3 A AC, DC max.
Voltage rating: 250 V AC, DC max.
Temperature range: -25°C to +85°C

(including temperature rise in applying

electrical current)

• Contact resistance: Initial value/ 10 m $\Omega$  max.

After environmental tests/ 20 m $\Omega$  max.

• Insulation resistance:  $500~M\Omega$  min • Withstanding voltage: 1,500 VAC/minute • Applicable wire: AWG #28 to #22

0.08 to 0.33 mm<sup>2</sup>

- \* In using the products, refer to "Handling Precaution for Terminal and Connector" described on our website (Technical documents of Product information page).
- \* Contact JST for details.
- \* RoHS2 compliance.

Note: The current rating varies depending on the wire size used in each connector.

The table below lists the current rating as a function of the wire size.

Current unit: A


Circuits	Wire size (AWG)			
	#22	#24	#26	#28
2	3	2	1	0.5

#### Standards -

Recognized E60389

# **RCY** CONNECTOR

### Contact-




Mode	el No.	Applicable wire		Q´ty/reel		
Pin contact	Socket contact	mm²	AWG #	Insulation O.D. (mm)	Pin contact	Socket contact
SYM-001T-P0.6	SYF-001T-P0.6	0.08 to 0.33	28 to 22	1.2 to 1.8	8,500	7,500

#### Material and Finish

Phosphor bronze, tin-plated (reflow treatment)

RoHS2 compliance SYF-001T-P0.6 displays (LF)(SN) on a label. Note: Contact JST for brass products.


## Housing -



Circuits -	Model No.		Material and Finish	O'tu/bog
	Receptacle housing	Plug housing	iviaterial and Fillish	Q'ty/bag
2	SYR-02T	SYP-02T-1	PA 66, UL94V-2, red	1,000
	SYR-02TV	SYP-02TV-1	PA 66, UL94V-0, white (natural)	1,000

RoHS2 compliance

### Assembly layout-



# Crimping machine, Applicator -

Contact	Crimping machine	Applicator			
		Crimp applicator	Dies	Crimp applicator with dies	
SYM-001T-P0.6	- AP-K2N	MKS-L	MK/SYM-001-06	APLMK SYM001-06	
		*MKS-SC	SC/SYM-001-06	APLSC SYM001-06	
SYF-001T-P0.6		MKS-L	MK/SYF-001-06	APLMK SYF001-06	
		-	-	-	

Note: \*Strip-crimp applicator