

GENERAL DESCRIPTION

The HV8549 is a 2-channel low saturation voltage forward/reverse motor driver IC. It is optimal for motor drive in 12V and 24V system products and can drive a stepper motor in Full-step.

The output driver block of each H-bridge consists of N-channel power MOSFETs configured as a H-bridge to drive the motor windings. Each H-bridge includes circuitry to regulate or limit the winding current.

Internal shutdown functions are provided for undervoltage lockout, and over temperature. A low-power sleep mode is also provided.

The HV8549 is available in a compact SOIC-10 package.


FEATURES

- DMOS output transistor adoption (upper and lower total Rdson = 0.65 Ω Typ.).
- VCC Max = 28V, IO Max = 1.2A, IO RMS = 0.8A.
- 4V to 28V operating supply voltage range (The control system power supply is unnecessary.).
- The compact package (SOIC-10) is adopted.
- Current consumption 0 when standby mode.

TYPICAL APPLICATIONS

- Stage Lighting
- Refrigerator
- Flatbed Scanner, Document Scanner
- POS Printer, Label Printer
- PoE Point of Sales Terminal
- Clothes Dryer
- Vacuum Cleaner
- Time Recorder

TYPICAL APPLICATION CIRCUIT





PIN CONFIGURATION

Package	Pin Configuration (Top View)		
SOIC-10	V _{CC} 1 ENA 2 IN1 3 IN2 4 NC 5	O HV8549	10 OUT1 9 OUT2 8 OUT3 7 OUT4 6 GND

PIN DESCRIPTION

No.	Pin	Description			
1	Vcc	Power-supply voltage pin. A 10-uF (minimum) ceramic bypass capacitor to GND is recommended.			
2	ENA	Motor drive control enable pin. "0" stand-by current when ENA=L. Output is corresponding to input control logic when ENA=H.			
3	IN1	Logic input pin of OUT1 and OUT2. Internal pull-down.			
4	IN2	Logic input pin of OUT3 and OUT4. Internal pull-down.			
5	NC	No connection.			
6	GND	Device ground.			
7	OUT4	Driving output pin. Motor coil is connected between terminal OUT3 (pin8).			
8	OUT3	Driving output pin. Motor coil is connected between terminal OUT4 (pin7).			
9	OUT2	Driving output pin. Motor coil is connected between terminal OUT1 (pin10).			
10	OUT1	Driving output pin. Motor coil is connected between terminal OUT2 (pin9).			


ORDERING INFORMATION

Industrial Range: -40°C to +125°C

Order Part No.	Package	QTY
HV8549MC-AH HV8549CC-13GTR	SOIC-10, Pb-Free SOIC-10, Pb-Free	4000/Reel 4000/Reel
HV8549CC-GT	SOIC-10, Pb-Free	100/Tube



FUNCTIONAL BLOCK DIAGRAM





ABSOLUTE MAXIMUM RATINGS

Symbol	Definition		Min.	Max.	Units
V _{CC} Max	Maximum power supply voltage	(Vcc)	-0.3	+30	
Vouт	Output voltage (OUT1, OUT2, OUT	3, OUT4)	-0.3	+30	V
V_{IN}	Input voltage (EN, IN1, IN2)	-0.3	+6	
I _{GND}	Maximum GND pin sink/source o	Maximum GND pin sink/source current			
P_{D}	Package power dissipation @ T _A ≤ SOIC-10			1.0	W
Rth _{JA}	Thermal resistance, junction to ambient		80	°C/W	
TJ	Junction temperature		150		
Ts	Storage temperature	-55	150	°C	
TL	Lead temperature (soldering, 10 se	econds)		300	

Note:

Absolute maximum ratings indicate sustained limits beyond which damage to the device may occur. All voltage parameters are absolute voltages referenced to COM. The thermal resistance and power dissipation ratings are measured under board mounted and still air conditions.

RECOMMENDED OPERATION CONDITIONS

Symbol	Definition	Min.	Max.	Units
Vcc	Power supply voltage (Vcc)	4.0	28	
ViH	Logic "1" input voltage (EN, IN1, IN2)	1.8	5.5	V
V _{IL}	Logic "0" input voltage (EN, IN1, IN2)	-0.3	+0.7	V
V _{LO}	Low-side output voltage	0	Vcc	
TA	Ambient temperature	- 40	125	°C

Note:

The input/output logic timing diagram is shown in Fig. 1. For proper operation the device should be used within the recommended conditions. The V_S offset rating is tested with all supplies biased at a 15 V differential.

HV8549 Rev1.4 KEYSEMI CORPORATION 4



DYNAMIC ELECTRICAL CHARACTERISTICS

 V_{CC} = 12 V and T_A = 25°C unless otherwise specified.

Symbol	Parameter	Condition	Min.	Тур.	Max.	Unit
t _{on}	Turn-on propagation delay	V _{CC} = 12 / 24 V	170	200	230	
t _{off}	Turn-off propagation delay	Vcc = 12 / 24 V	80	100	120	
tr	Turn-on rise time	V _{CC} = 12 / 24 V, 16Ω to GND, 10% to 90% V _{CC}	160	200	240	ns
t _f	Turn-off fall time	V _{CC} = 12 / 24 V, 16Ω to GND, 90% to 10% V _{CC}	220	260	300	
DT	Deadtime, LS turn-off to HS turn-on & HS turn-on to LS turn-off	Vcc = 12 / 24 V	220	270	320	

STATIC ELECTRICAL CHARACTERISTICS

 V_{CC} = 12 V and T_A = 25°C unless otherwise specified.

Symbol	Parameter	Condition	Min.	Тур.	Max.	Unit
Vcc	Power supply voltage		4.0		28	V
Vccuv+	V _{CC} supply undervoltage positive going threshold		3.5	3.7	3.95	
Vccuv-	V _{CC} supply undervoltage negative going threshold	V _{CC} = 12 / 24 V	3.1	3.3	3.6	V
V _{IH}	Logic "1" input voltage		1.8			
VIL	Logic "0" input voltage				0.7	
I _{CC0}	Quiescent current (standby mode)	V _{CC} = 12 / 24 V, EN = "0"			1	μΑ
I _{CC1}	Operating current (no load)	V _{CC} = 12 / 24 V, EN = "1"		1.5	2.3	mA
I _{IN}	Input current	V _{CC} = 12 / 24 V, V _{IN} = 5V	40	56	65	μA
T _{SD}	Thermal shutdown temperature		150	160	170	°C
T _{SD_HYS}	Thermal shutdown hysteresis			25		°C
R _{DSON}	Output ON resistance (high-side and low-side total)	I _{OUT} = 0.8A	550	650	900	mΩ
IOLEAK	Output leakage current	V _O = 30V			10	μΑ
V _D	Diode forward voltage	I _D = 0.8A		1.0	1.2	V



APPLICATION INFORMATION

STM Output Control Logic

Input			Output				State	
ENA	IN1	IN2	OUT1	OUT2	OUT3	OUT4	State	
L	-	-	OFF	OFF	OFF	OFF	Stand-by	
	L	L	Н	L	Н	L	Step 1	
н	Н	L	L	Н	Н	L	Step2	
"	Н	Н	L	Н	L	Н	Step3	
	L	Н	Н	L	L	Н	Step4	

Figure 3 Control Logic

Timing

About the switch time from the stand-by state to the state of operation, this IC has completely stopped operating when ENA pin is logic "0". After the time of reset of about 7µs of and internal setting, it shifts to a prescribed output status corresponding to the state of the input when ENA pin is logic "1".

During reset time, all output TR OFF is maintained.




Figure 4 Control Timing

Current Waveforms




Figure 5 Full-step Mode

Thermal Shutdown

The thermal shutdown circuit is incorporated and the output is turned off when junction temperature exceeds 160°C. As the temperature falls by hysteresis, the output turned on again.

The thermal shutdown circuit doesn't guarantee the protection of the final product because it operates when the temperature exceed the junction temperature of T_{imax}=150°C.

$$T_{SD} = 160^{\circ}C \text{ (TYP)}$$

$$T_{SD_HYS} = 25^{\circ}C (TYP)$$



CLASSIFICATION REFLOW PROFILES

Profile Feature	Pb-Free Assembly
Preheat & Soak Temperature min (Tsmin) Temperature max (Tsmax) Time (Tsmin to Tsmax) (ts)	150°C 200°C 60-120 seconds
Average ramp-up rate (Tsmax to Tp) Liquidous temperature (TL)	3°C/second max.
Time at liquidous (tL) Peak package body temperature (Tp)* Time (tp)** within 5°C of the specified	60-150 seconds Max 260°C
classification temperature (Tc) Average ramp-down rate (Tp to Tsmax)	Max 30 seconds 6°C/second max.
Time 25°C to peak temperature	8 minutes max.





Figure 2 Classification Profile

HV8549 Rev1.4 KEYSEMI CORPORATION 7



PACKAGE CASE OUTLINES



- NOTES: 1. DMENSIONING AND TOLERANCING PER
- NOTES.

 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.

 2. CONTROLLING DIMENSION: MILLIMETERS.

 3. DIMENSIONS DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE PROTRUSION SHALL BE 0.10mm TOTAL IN EXCESS OF 'b' AT MAXIMUM MATERIAL CONDITION.

 4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEEDD. 15mm PER SIDE. DIMENSIONS D AND E ARE DETERMINED AT DATUM F.

 5. DIMENSIONS A AND B ARE TO BE DETERMINED AT DATUM F.

 6. AL IS DEFINED AS THE VERTICAL DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.

	MILLIMETERS					
DIM	MIN	MAX				
А	1.25	1.75				
A1	0.10	0.25				
A3	0.17	0.25				
ь	0.31	0.51				
D	4.80	5.00				
Е	3.80	4.00				
е	1.00	BSC				
Н	5.80	6.20				
h	0.37 REF					
L	0.40	1.27				
L2	0.25 BSC					
M	0.0	80				

RECOMMENDED SOLDERING FOOTPRINT

